



Quam

LOUDSPEAKER ASSEMBLIES

8C10FECO/H70/WS

CEILING MOUNTED

8" O.D. Coaxial Loudspeaker with Foam-Edge Surround,
10 Oz. Magnet, 10W-70V Transformer

GENERAL DESCRIPTION

The 8C10FECO/H70/WS is a complete loudspeaker assembly consisting of an 8C10FECO - 8" O.D. foam edge surround, coaxial loudspeaker with a 10 oz. magnet and a TCH70 - 10W-70V, low-loss transformer mounted on a BR8WS - round, steel, stud mount baffle finished in white powder coat.

INTENDED USE - Indoor Environment


Program Material	Signal Tones, Voice and Music
------------------	-------------------------------

AUDIO SPECIFICATIONS

Average Sensitivity	95 dB SPL, 1W/ 1M
Loudspeaker Power Rating	20W RMS, EIA 426A Standard
Calculated Output	105 dB SPL, 10W/ 1M
Magnet Type & Weight	BeFe Ceramic, 10 oz. Nominal
Frequency Response	40 Hz - 20 kHz EIA 426A Standard
Nominal Coverage Angle	90° Included Angle, -6 dB / 2 kHz, Half space
Audio Connection	7" Color Coded Leads

RECOMMENDED QUAM ACCESSORIES

Enclosure	ERD-8, ERD8U
Mounting Support	SSB-2, SSB-3, SSB-7



Recommended construction sequences, installation instructions, and A&E Specifications are available in various formats in the QUAM Architects' and Engineers' Resources section on the web at:
www.QuamSpeakers.com

© 2013 Quam-Nichols Company reserves the right to make changes and/or improvements to its products at any time and without notice.



QUAM-NICHOLS COMPANY, INC.
234 East Marquette Rd.
Chicago, IL. 60637
Tel: 1-800-NEED-NOW (800-633-3669)
Fax: 1-888-NEED-NOW (888-633-3669)
e-mail: NeedNow@QNC.com
www.QuamSpeakers.com