

Sentry Switched CDU

Key Features

- > **Remote Power Management:** Power cycle individual power outlets, or groups of power outlets, to remotely reboot servers and network devices, anywhere in the world. Or, power-off unused power receptacles
- > **High Power Distribution:** 208V, 3-Phase, Delta 50A or 60A, Wye 60A input power options
- > **High Density:** Single power input feed; 48 outlets (42xC13 + 6xC19) per enclosure
- > **IP Access & Security:** Web interface, SSL, SSH, Telnet, SNMP, FTP, SNTp, Syslog, RADIUS, LDAP, LDAPS, TACACS and RS-232 access
- > **Add an Expansion Module:** Connect the Switched Expansion CDU (SEV) to a Master unit (STV) for power management of separate power circuits from a single IP address
- > **Environmental Monitoring:** Each Switched CDU supports two temperature & humidity probes and reports conditions thru the user interface without the need for additional IP addresses
- > **SNMP Traps:** Provide automated alerts for power and environmental conditions
- > **Input Current Monitor:** Precisely measure the aggregate current draw (in amps) on each phase. On-site verification of the input current with the LED digital display. Remote verification via browser or serial screen.
- > **Power-up Sequencing:** Prevent an in-rush power overload

Switched 48-Outlet (50A/60A 3-phase 42xC13 + 6xC19) PIPS/POPS

High-Density Power Distribution

The Switched CDU's combine remote configuration and management with power distribution and power and environmental monitoring. Reboot a single or dual-power server with one command. Receive SNMP or email based alerts when power or environmental conditions exceed thresholds. Assign users specific access rights to designated outlets or groups.

Only the Switched CDU products provide the flexibility needed for all data centers and remote sites, including power requirements for high-amp, high voltage; UL 60950-1 branch circuit protection; SSL & SSH security; and SNMP-based input current monitoring.

Additional Benefits:



POPS™ (Per Outlet Power Sensing)

Monitor Current Load (A), Voltage (V), Power (W), Apparent Power (VA), Crest Factor and Power Factor per outlet at an accuracy of ±2%.



Branch Circuit Protection

The Sentry CDU Family meets the UL 60950-1 requirement for Branch Circuit Protections
> UL-489 rated circuit breakers



PIPS - Per Input Power Sensing

Accurately measures Active Power, Apparent Power, Energy k-Wh, Power Capacity, Reactance, and Power Capacity Used using the network interface. See the aggregate current draw, in Amps, locally using the onboard LED.



Temperature and Humidity

The Switched CDU supports two external probes. Each of these probes measure both temperature and humidity. Receive SNMP-based alert notifications when conditions exceed defined thresholds.



Linking for Switched CDU (Expansion Modules)

The Switched CDU family has the capability to daisy chain units together. The Expansion Module provides the ability to link two power circuits under one IP address.



Model	Available Input Voltages	Amperage	Available Input Cord	Outlets	Dimensions (L x W x D)
STV-6301D SEV-6301D*	208V 3-phase Delta, 50/60Hz	60A	IEC Blue 9hr 3P+G Plug, 10'(3m), Top Cord Entry	(42) IEC 60320/C13 (6) IEC 60320/C19	69.0 x 3.25 x 3.50 in. (1753 x 83 x 89 mm)
STV-6301V SEV-6301V*	208V 3-Phase Delta, 50/60Hz	50A	CS8365 Plug, 10'(3m), Top Cord Entry	(42) IEC 60320/C13 (6) IEC 60320/C19	69.0 x 3.25 x 3.50 in. (1753 x 83 x 89 mm)
STV-6301Y SEV-6301Y*	208V 3-Phase Wye, 50/60Hz	60A	IEC Blue 9hr 3P+N+G Plug, 10'(3m), Top Cord Entry	(42) IEC 60320/C13 (6) IEC 60320/C19	69.0 x 3.25 x 3.50 in. (1753 x 83 x 89 mm)

*SEV part number refers to the expansion CDU

Additional Features and Specifications

Agency Approvals

- > US & Canada (cTUVus Mark) to UL 60950-1:2007 and CAN/CSA 22.2 No. 60950-1-07
- > FCC Class A, Part 15
- > EMC to EN 55022 Class A, EN 55024, CISPR 22 Class A

Communications and Security

- > 10/100 BaseT Ethernet
- > HTTP/HTTPS
- > SSLv3/TLSv1
- > SNMPv2/v3
- > SSHv2
- > Telnet
- > RADIUS
- > LDAPv3
- > LDAPS
- > TACACS+
- > RS-232 (Serial)
- > IPv4 and IPv6

Branch Circuit Protection

- > Compliant to UL 60950-1

Accessories

- > Optional Temperature & Humidity Probe
 - EMTH-1-1 Temperature & Humidity Probe, 10 ft (3m)
- > Environmental Monitor
 - EMCU-1-1B allows up to (2) additional temperature & humidity probes, (1) water sensor, (4) dry contact closures, (1) analog-to-digital contact sensor. Includes (1) temperature/humidity probe with unit.
- > SPM (Sentry Power Manager):
 - Monitor and Manage multiple Sentry CDU's
 - Monitor and Manage all alarm conditions
 - Reporting and Trending
 - Group or Cluster outlets for reboot and power information
 - Optional Appliance or virtual version
 - SPM v5.1+ is VMware READY



VMware and VMware Ready is a registered trademark or trademark of VMware, Inc. in the United States and/or other jurisdictions

1U SPM Appliance



Expansion Module
Model Numbers

- > SEV-6301D*
- > SEV-6301V*
- > SEV-6301Y*


Server Technology

HEADQUARTERS - NORTH AMERICA

Server Technology, Inc.
1040 Sandhill Drive
Reno, NV 89521
United States
1.775.284.2000 Tel
1.775.284.2065 Fax
sales@servertech.com
www.servertech.com
www.servertechblog.com

Western Europe, Middle East and Africa

Fountain Court
2 Victoria Square
Victoria Street
St. Albans
AL1 3TF
United Kingdom
+44 (0) 1727 884676 Tel
+44 (0) 1727 220815 Fax
salesint@servertech.com

Central Europe, Eastern Europe and Russia

Niederlassung Deutschland
Server Technology LLC
42119 Wuppertal
Germany
Tel: + 49 202 693917 x 0
Fax: + 49 202 693917-10
salesint@servertech.com

APAC

37th Floor
Singapore Land Tower
50 Raffles Place
Singapore 048623
Phone: +65 9739.0396
Fax: +65 6234.4574
salesint@servertech.com