

Basic Rack PDU


Overview

The American Power Conversion[®] Basic Rack PDU distributes power to devices in the rack.

Outlets. The Rack PDU has twenty (20) IEC-320-C13 outlet, and four (4) IEC-320-C19 outlets.

Power cord. The 10-foot (3.05-meter) power cord terminates with a NEMA L6-20 connector.

AP7540



Specifications for AP7540

Electrical

Input connector	NEMA L6-20 plug
Output connectors	(20) IEC-320-C13 (4) IEC-320-C19 outlets
Nominal input voltage	200 – 240 VAC
Acceptable input voltage	± 10% of nominal voltage
Input frequency	47– 63 Hz

Physical

Dimensions (H × W × D)	63.75 × 2.19 × 1.73 in (161.92 × 5.56 × 4.39 cm)
Shipping dimensions (H × W × D)	84.00 × 6.00 × 5.00 in (213.36 × 15.24 × 12.7 cm)
Weight	10 lb (4.54 kg)
Shipping weight	17 lb (7.71 kg)

Environmental

Maximum elevation (above MSL)	
Operating	15,000 ft (4500 m)
Storage	50,000 ft (15 000 m)
Temperature	
Operating	–5 to 45° C (23 to 115° F)
Storage	–25 to 65° C (–13 to 149° F)
Humidity	
Operating	5 – 95% RH non-condensing
Storage	5 – 95% RH non-condensing

Compliance

Safety verification	UL/cUL 60950 Listed
---------------------	---------------------

