



by **Schneider** Electric

Basic Rack PDU


Overview

The American Power Conversion (APC®) Basic Rack Power Distribution Unit (PDU) distributes power to devices in the rack.

Outlets. The Rack PDU has ten (10) IEC-320-C13 outlets.

Power cord. The 12-foot (3.65-meter) power cord terminates with a NEMA L6-30 connector.

AP9571A



Specifications

Electrical

Input connector	NEMA L6-30 plug
Output connectors	10 – IEC-320-C13 outlets
Nominal input voltage	200–240 VAC
Acceptable input voltage	± 10% of normal voltage
Input frequency	50/60 Hz
Maximum total current draw	30 A (24 A UL (C-UL) derated)
Overcurrent protection (internal)	(2) 20 A, 2-pole circuit breakers

Physical

Size (H × W × D)	17.5 × 1.7 × 3.03 in (44.5 × 4.4 × 7.69 cm)
Shipping Dimensions (H × W × D)	6.75 × 19.00 × 6.875 in (17.14 × 48.26 × 17.46 cm)
Weight	5.6 lb (2.5 kg)
Shipping weight	8.0 lb (3.6 kg)

Environmental

Elevation (above MSL)	
Operating	0–10,000 ft (0–3000 m)
Storage	0–50,000 ft (0–15 000 m)
Temperature	
Operating	–5 to 45° C (23 to 115° F)
Storage	–25 to 65° C (–13 to 149° F)
Humidity	
Operating	5–95% RH non-condensing
Storage	5–95% RH non-condensing

Compliance

Safety verification	UL (C-UL) listed
---------------------	------------------

Customer support and warranty information is available at the APC Web site, www.apc.com.

© 2009 APC by Schneider Electric. All trademarks are owned by Schneider Electric Industries S.A.S., American Power Conversion Corporation, or their affiliated companies.



990-3612
04/2009

