



Quam

LOUDSPEAKER ASSEMBLIES

FM4X1/70

FOREGROUND MUSIC

2-Way - 4" O.D. LF Speaker & 3/4" HF,
70V Rotary Select Transformer with 8Ω Tap, Black Finish

GENERAL DESCRIPTION

The **FM4X1/70** is complete 2-way loudspeaker with a 4" O.D. Woofer, 3/4" dome tweeter, 20W-70V low loss, extended frequency response rotary select transformer with an 8 Ohm position in a black finish. Multiple position "U" bracket included.

INTENDED USE - Indoor Environment


Program Material	Signal tones, voice, and music
Installation	Horizontal or Vertical Surface Mount

AUDIO SPECIFICATIONS

Average Sensitivity	89 dB SPL, 1W/ 1M
Loudspeaker Power Rating	20W RMS, EIA 426A Standard
8 Ohm Tap Output	89 dB SPL, 1W/ 1M
Calculated Output	102 dB SPL, 5W/ 1M
Frequency Response	80Hz - 20kHz EIA 426A Standard
Nominal Coverage Angle	90° Included Angle, -6 dB / 2 kHz, half space
Audio Connection	Binding Screw

SYSTEM COMPONENTS

Loudspeaker	4" O.D. Woofer
Tweeter	3/4" Dome
Transformer	Integral to Unit 20W-70V or 8 Ohm, 5 tap (20W, 10W, 5W, 2.5W, 1.25W)



Recommended construction sequences, installation instructions, and A&E Specifications are available in various formats in the QUAM Architects' and Engineers' Resources section on the web at:
www.QuamSpeakers.com

© 2013 Quam-Nichols Company reserves the right to make changes and/or improvements to its products at any time and without notice.



QUAM-NICHOLS COMPANY, INC.
234 East Marquette Rd.
Chicago, IL. 60637
Tel: 1-800-NEED-NOW (800-633-3669)
Fax: 1-888-NEED-NOW (888-633-3669)
e-mail: NeedNow@QNC.com
www.QuamSpeakers.com