



SAFETY DATA SHEET
INDUSTRIAL CLEANER RAPID DRYING SPRAY

Page: 1

Compilation date: 09/09/2014

Revision No: 9

Section 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product name: INDUSTRIAL CLEANER RAPID DRYING SPRAY

1.2. Relevant identified uses of the substance or mixture and uses advised against

Use of substance / mixture: Solvent cleaner.

1.3. Details of the supplier of the safety data sheet

Company name: ROCOL

ROCOL House

Swillington

Leeds

West Yorkshire

LS26 8BS

ENGLAND

Tel: +44 (0) 113 232 2700

Fax: +44 (0) 113 232 2740

Email: customer-service@rocol.com

1.4. Emergency telephone number

Emergency tel: +44 (0) 113 232 2600

Section 2: Hazards identification

2.1. Classification of the substance or mixture

Classification under CLP: STOT SE 3: H336; Aquatic Chronic 2: H411; Eye Irrit. 2: H319; Flam. Aerosol 1: H222;
Skin Irrit. 2: H315; -: H229

Most important adverse effects: Extremely flammable aerosol. Pressurised container: May burst if heated. Causes skin irritation. Causes serious eye irritation. May cause drowsiness or dizziness. Toxic to aquatic life with long lasting effects.

2.2. Label elements

Label elements:

Hazard statements: H222: Extremely flammable aerosol.

H229: Pressurised container: May burst if heated

H315: Causes skin irritation.

H319: Causes serious eye irritation.

H336: May cause drowsiness or dizziness.

H411: Toxic to aquatic life with long lasting effects.

Hazard pictograms: GHS02: Flame

[cont...]

SAFETY DATA SHEET

INDUSTRIAL CLEANER RAPID DRYING SPRAY

Page: 2

GHS07: Exclamation mark

GHS09: Environmental



Signal words: Danger

Precautionary statements: P410+412: Protect from sunlight. Do not expose to temperatures exceeding 50 °C.

P251: Do not pierce or burn, even after use.

P210: Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.

P211: Do not spray on an open flame or other ignition source.

P285: In case of inadequate ventilation wear respiratory protection.

P261: Avoid breathing dust/fumes/gas/mist/vapours/spray.

P271: Use only outdoors or in a well-ventilated area.

P273: Avoid release to the environment.

P280: Wear protective gloves/protective clothing/eye protection/face protection.

P304+340: IF INHALED: Remove person to fresh air and keep comfortable for breathing.

P305+351+338: IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

P312: Call a POISON CENTER/doctor//if you feel unwell.

P501: Dispose of contents/container to local/national regulations.

2.3. Other hazards

PBT: This product is not identified as a PBT/vPvB substance.

Section 3: Composition/information on ingredients

3.2. Mixtures

Hazardous ingredients:

PROPAN-2-OL

EINECS	CAS	PBT / WEL	CLP Classification	Percent
200-661-7	67-63-0	-	Flam. Liq. 2: H225; Eye Irrit. 2: H319; STOT SE 3: H336	30-50%

HYDROCARBONS C7-C9, ISOALKANES - REACH registered number(s): 01-2119471305-42-0000

921-728-3	-	-	Flam. Liq. 2: H225; Skin Irrit. 2: H315; Aquatic Chronic 2: H411; STOT SE 3: H336; Asp. Tox. 1: H304	30-50%
-----------	---	---	--	--------

[cont...]

SAFETY DATA SHEET
INDUSTRIAL CLEANER RAPID DRYING SPRAY

Page: 3

CARBON DIOXIDE AEROSOL PROPELLANT

204-696-9	124-38-9	Substance with a Community workplace exposure limit.	Press. Gas: H280	2-10%
-----------	----------	--	------------------	-------

Section 4: First aid measures

4.1. Description of first aid measures

Skin contact: Wash immediately with plenty of soap and water.

Eye contact: Bathe the eye with running water for 15 minutes. Consult a doctor.

Ingestion: Wash out mouth with water. Do not induce vomiting. Consult a doctor.

Inhalation: Remove casualty from exposure ensuring one's own safety whilst doing so. Consult a doctor.

4.2. Most important symptoms and effects, both acute and delayed

Skin contact: There may be irritation and redness at the site of contact.

Eye contact: There may be irritation and redness. The eyes may water profusely.

Ingestion: There may be soreness and redness of the mouth and throat. May cause dizziness.

Inhalation: There may be irritation of the throat with a feeling of tightness in the chest. Drowsiness or mental confusion may occur.

Delayed / immediate effects: No data available.

4.3. Indication of any immediate medical attention and special treatment needed

Immediate / special treatment: No data available.

Section 5: Fire-fighting measures

5.1. Extinguishing media

Extinguishing media: Do not use water. Alcohol resistant foam. Carbon dioxide. Dry chemical powder. Use water spray to cool containers.

5.2. Special hazards arising from the substance or mixture

Exposure hazards: Highly flammable. Forms explosive air-vapour mixture. In combustion emits toxic fumes of carbon dioxide / carbon monoxide.

5.3. Advice for fire-fighters

Advice for fire-fighters: Wear self-contained breathing apparatus. Wear protective clothing to prevent contact with skin and eyes.

Section 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Personal precautions: Refer to section 8 of SDS for personal protection details. Eliminate all sources of ignition.

[cont...]

SAFETY DATA SHEET

INDUSTRIAL CLEANER RAPID DRYING SPRAY

Page: 4

6.2. Environmental precautions

Environmental precautions: Do not discharge into drains or rivers.

6.3. Methods and material for containment and cleaning up

Clean-up procedures: Do not use equipment in clean-up procedure which may produce sparks. Mix with sand or vermiculite. Transfer to a closable, labelled salvage container for disposal by an appropriate method.

6.4. Reference to other sections

Reference to other sections: Refer to section 13 of SDS.

Section 7: Handling and storage

7.1. Precautions for safe handling

Handling requirements: Ensure there is sufficient ventilation of the area. Do not handle in a confined space.
Smoking is forbidden.

7.2. Conditions for safe storage, including any incompatibilities

Storage conditions: Store in a cool, well ventilated area. Keep away from sources of ignition. Keep away from direct sunlight. Ensure lighting and electrical equipment are not a source of ignition.

Suitable packaging: Must only be kept in original packaging.

7.3. Specific end use(s)

Specific end use(s): No data available.

Section 8: Exposure controls/personal protection

8.1. Control parameters

Hazardous ingredients:

PROPAN-2-OL

Workplace exposure limits:

Respirable dust

State	8 hour TWA	15 min. STEL	8 hour TWA	15 min. STEL
UK	400 ppm, 999 mg/m ³	500 ppm, 1250 mg/m ³	-	-

HYDROCARBONS C7-C9, ISOALKANES

UK	1400 mg/m ³ RCP TWA	-	-	-
----	--------------------------------	---	---	---

CARBON DIOXIDE AEROSOL PROPELLANT

UK	5000ppm 9150mg/m ³	15000ppm 27400mg/m ³	-	-
----	-------------------------------	---------------------------------	---	---

DNEL/PNEC Values

DNEL / PNEC No data available.

[cont...]

SAFETY DATA SHEET

INDUSTRIAL CLEANER RAPID DRYING SPRAY

Page: 5

8.2. Exposure controls

Engineering measures: Ensure there is sufficient ventilation of the area. Ensure lighting and electrical equipment are not a source of ignition. The floor of the storage room must be impermeable to prevent the escape of liquids.

Respiratory protection: Respiratory protection not normally required.

Hand protection: Nitrile gloves.

Eye protection: Safety glasses with side-shields.

Skin protection: Protective clothing.

Environmental: No data available

Section 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

State: Aerosol

Colour: Colourless

Odour: Characteristic odour

Evaporation rate: Fast

Oxidising: Non-oxidising (by EC criteria)

Solubility in water: Not miscible

Viscosity: Non-viscous

Boiling point/range°C: >80

Melting point/range°C: <0

Flammability limits %: lower: 1

upper: 12

Flash point°C: < 0°C

Autoflammability°C: >200

Vapour pressure: >4

Relative density: <1

VOC g/l: 710

9.2. Other information

Other information: No data available.

Section 10: Stability and reactivity

10.1. Reactivity

Reactivity: Stable under recommended transport or storage conditions.

10.2. Chemical stability

Chemical stability: Stable under normal conditions.

10.3. Possibility of hazardous reactions

Hazardous reactions: No data available.

10.4. Conditions to avoid

Conditions to avoid: Direct sunlight. Heat. Sources of ignition.

[cont...]

SAFETY DATA SHEET
INDUSTRIAL CLEANER RAPID DRYING SPRAY

Page: 6

10.5. Incompatible materials

Materials to avoid: Strong oxidising agents. Strong reducing agents.

10.6. Hazardous decomposition products

Haz. decomp. products: In combustion emits toxic fumes of carbon dioxide / carbon monoxide.

Section 11: Toxicological information

11.1. Information on toxicological effects

Hazardous ingredients:

PROPAN-2-OL

IVN	RAT	LD50	1088	mg/kg
ORL	MUS	LD50	3600	mg/kg
ORL	RAT	LD50	5045	mg/kg
SCU	MUS	LDLO	6	gm/kg

Relevant hazards for product:

Hazard	Route	Basis
Skin corrosion/irritation	DRM	Hazardous: calculated
Serious eye damage/irritation	OPT	Hazardous: calculated
STOT-single exposure	-	Hazardous: calculated

Symptoms / routes of exposure

Skin contact: There may be irritation and redness at the site of contact.

Eye contact: There may be irritation and redness. The eyes may water profusely.

Ingestion: There may be soreness and redness of the mouth and throat. May cause dizziness.

Inhalation: There may be irritation of the throat with a feeling of tightness in the chest. Drowsiness or mental confusion may occur.

Delayed / immediate effects: No data available.

Section 12: Ecological information

12.1. Toxicity

Hazardous ingredients:

HYDROCARBONS C7-C9, ISOALKANES

Daphnia magna	48H EC50	2.4	mg/l
Pseudokirchneriella	72H ErC50	6.3	mg/l
RAINBOW TROUT (Oncorhynchus mykiss)	96H ErC50	18.4	mg/l

12.2. Persistence and degradability

Persistence and degradability: Only slightly biodegradable.

[cont...]

SAFETY DATA SHEET
INDUSTRIAL CLEANER RAPID DRYING SPRAY

Page: 7

12.3. Bioaccumulative potential

Bioaccumulative potential: No bioaccumulation potential.

12.4. Mobility in soil

Mobility: Highly volatile. Soluble in water.

12.5. Results of PBT and vPvB assessment

PBT identification: This product is not identified as a PBT/vPvB substance.

12.6. Other adverse effects

Other adverse effects: Toxic to aquatic organisms.

Section 13: Disposal considerations

13.1. Waste treatment methods

Disposal operations: Specially engineered landfill (e.g. placement into lined discrete cells which are capped and isolated from one another and the environment, etc.).

Recovery operations: Use principally as a fuel or other means to generate energy.

Waste code number: 16 05 06

Disposal of packaging: Dispose of in a regulated landfill site or other method for hazardous or toxic wastes.

NB: The user's attention is drawn to the possible existence of regional or national regulations regarding disposal.

Section 14: Transport information

14.1. UN number

UN number: UN1950

14.2. UN proper shipping name

Shipping name: AEROSOLS, FLAMMABLE

14.3. Transport hazard class(es)

Transport class: 2.1

14.4. Packing group

Packing group: n/a

14.5. Environmental hazards

Environmentally hazardous: Yes

Marine pollutant: Yes

14.6. Special precautions for user

Special precautions: No data available

14.7. Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code

Transport in bulk: No data available.

[cont...]

SAFETY DATA SHEET
INDUSTRIAL CLEANER RAPID DRYING SPRAY

Page: 8

Section 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

Specific regulations: No data available

15.2. Chemical Safety Assessment

Chemical safety assessment: A chemical safety assessment has not been carried out for the substance or the mixture by the supplier.

Section 16: Other information

Other information

Other information: Contains only FDA listed ingredients. NSF K1 registered.

EC Directive 94/1/EC adapting some technicalities of Council Directive 75/324/EEC on the approximation of the laws of Member States relating to aerosol dispensers.

This safety data sheet is prepared in accordance with Commission Regulation (EU) No 453/2010.

Compiled in accordance with REACH.

Phrases used in s.2 and s.3: H222: Extremely flammable aerosol.

H225: Highly flammable liquid and vapour.

H229: Pressurised container: May burst if heated

H280: Contains gas under pressure; may explode if heated.

H304: May be fatal if swallowed and enters airways.

H315: Causes skin irritation.

H319: Causes serious eye irritation.

H336: May cause drowsiness or dizziness.

H411: Toxic to aquatic life with long lasting effects.

Legal disclaimer: The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. This company shall not be held liable for any damage resulting from handling or from contact with the above product.