



SAFETY DATA SHEET

RTD COMPOUND

Page: 1

Compilation date: 22/05/2014

Revision No: 11

Section 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product name: RTD COMPOUND

1.2. Relevant identified uses of the substance or mixture and uses advised against

Use of substance / mixture: Lubricant for reaming, tapping and drilling.

1.3. Details of the supplier of the safety data sheet

Company name: ROCOL

ROCOL House

Swillington

Leeds

West Yorkshire

LS26 8BS

ENGLAND

Tel: +44 (0) 113 232 2700

Fax: +44 (0) 113 232 2740

Email: customer-service@rocol.com

1.4. Emergency telephone number

Emergency tel: +44 (0) 113 232 2600

Section 2: Hazards identification

2.1. Classification of the substance or mixture

Classification under CLP: Lact.: H362; Aquatic Acute 1: H400; Aquatic Chronic 1: H410; -: EUH066; -: EUH208

Most important adverse effects: Repeated exposure may cause skin dryness or cracking. Contains pine oil. May produce an allergic reaction. May cause harm to breast-fed children. Very toxic to aquatic life. Very toxic to aquatic life with long lasting effects.

2.2. Label elements

Label elements:

Hazard statements: EUH066: Repeated exposure may cause skin dryness or cracking.

EUH208: Contains pine oil. May produce an allergic reaction.

H362: May cause harm to breast-fed children.

H400: Very toxic to aquatic life.

H410: Very toxic to aquatic life with long lasting effects.

Hazard pictograms: GHS09: Environmental



[cont...]

SAFETY DATA SHEET

RTD COMPOUND

Page: 2

Signal words: Warning

Precautionary statements: P260: Do not breathe dust/fumes/gas/mist/vapours/spray.
P263: Avoid contact during pregnancy.
P264: Wash hands thoroughly after handling.
P270: Do not eat, drink or smoke when using this product.
P273: Avoid release to the environment.
P308+313: IF exposed or concerned: Get medical advice/attention.
P391: Collect spillage.
P501: Dispose of contents/container to local/national regulations.

2.3. Other hazards

PBT: This product is not identified as a PBT/vPvB substance.

Section 3: Composition/information on ingredients

3.2. Mixtures

Hazardous ingredients:

C14-C17 CHLORINATED PARAFFIN - REACH registered number(s): 01-2119519269-33-XXXX

EINECS	CAS	PBT / WEL	CLP Classification	Percent
287-477-0	85535-85-9	-	Lact.: H362; Aquatic Chronic 1: H410; Aquatic Acute 1: H400; -: EUH066	50-70%

PINE OIL

304-455-9	94266-48-5	-	Flam. Liq. 3: H226; Aquatic Chronic 2: H411; Eye Irrit. 2: H319; Skin Irrit. 2: H315; Skin Sens. 1: H317	<2%
-----------	------------	---	--	-----

Contains: Mineral oil contains <3% (w/w) DMSO extractable according to IP346

Section 4: First aid measures

4.1. Description of first aid measures

Skin contact: Wash immediately with plenty of soap and water.

Eye contact: Bathe the eye with running water for 15 minutes.

Ingestion: Wash out mouth with water.

Inhalation: Remove casualty from exposure ensuring one's own safety whilst doing so.

4.2. Most important symptoms and effects, both acute and delayed

Skin contact: There may be mild irritation at the site of contact.

Eye contact: There may be irritation and redness.

Ingestion: There may be irritation of the throat.

Inhalation: There may be irritation of the throat with a feeling of tightness in the chest.

Delayed / immediate effects: No data available.

[cont...]

SAFETY DATA SHEET

RTD COMPOUND

Page: 3

4.3. Indication of any immediate medical attention and special treatment needed

Immediate / special treatment: Not applicable.

Section 5: Fire-fighting measures

5.1. Extinguishing media

Extinguishing media: Suitable extinguishing media for the surrounding fire should be used.

5.2. Special hazards arising from the substance or mixture

Exposure hazards: In combustion emits toxic fumes.

5.3. Advice for fire-fighters

Advice for fire-fighters: Wear self-contained breathing apparatus. Wear protective clothing to prevent contact with skin and eyes.

Section 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Personal precautions: Refer to section 8 of SDS for personal protection details. Mark out the contaminated area with signs and prevent access to unauthorised personnel.

6.2. Environmental precautions

Environmental precautions: Do not discharge into drains or rivers.

6.3. Methods and material for containment and cleaning up

Clean-up procedures: Transfer to a closable, labelled salvage container for disposal by an appropriate method.

6.4. Reference to other sections

Reference to other sections: Refer to section 8 of SDS.

Section 7: Handling and storage

7.1. Precautions for safe handling

Handling requirements: Avoid direct contact with the substance.

7.2. Conditions for safe storage, including any incompatibilities

Storage conditions: Store in a cool, well ventilated area. Keep container tightly closed.

Suitable packaging: Must only be kept in original packaging.

7.3. Specific end use(s)

Specific end use(s): No data available.

Section 8: Exposure controls/personal protection

8.1. Control parameters

[cont...]

SAFETY DATA SHEET

RTD COMPOUND

Page: 4

Hazardous ingredients:

PINE OIL

Workplace exposure limits:

Respirable dust

State	8 hour TWA	15 min. STEL	8 hour TWA	15 min. STEL
UK	100 ppm, 566 mg/m ³	150 ppm, 850 mg/m ³	-	-

DNEL/PNEC Values

DNEL / PNEC No data available.

8.2. Exposure controls

Engineering measures: Ensure there is sufficient ventilation of the area.

Respiratory protection: Respiratory protective device with particle filter.

Hand protection: Protective gloves.

Eye protection: Safety glasses. Ensure eye bath is to hand.

Skin protection: Protective clothing.

Environmental: No special requirement.

Section 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

State: Paste

Colour: Brown

Odour: Characteristic odour

Evaporation rate: Negligible

Oxidising: Non-oxidising (by EC criteria)

Solubility in water: Insoluble

Viscosity: No data available.

Boiling point/range°C: No data available.

Melting point/range°C: No data available.

Flammability limits %: lower: No data available.

upper: No data available.

Flash point°C: >100

Part.coeff. n-octanol/water: No data available.

Autoflammability°C: >200

Vapour pressure: No data available.

Relative density: 1.17

pH: No data available.

VOC g/l: No data available.

9.2. Other information

Other information: No data available.

Section 10: Stability and reactivity

10.1. Reactivity

Reactivity: Stable under recommended transport or storage conditions.

[cont...]

SAFETY DATA SHEET

RTD COMPOUND

Page: 5

10.2. Chemical stability

Chemical stability: Stable under normal conditions.

10.3. Possibility of hazardous reactions

Hazardous reactions: Hazardous reactions will not occur under normal transport or storage conditions.
Decomposition may occur on exposure to conditions or materials listed below.

10.4. Conditions to avoid

Conditions to avoid: Heat.

10.5. Incompatible materials

Materials to avoid: Strong oxidising agents. Strong acids.

10.6. Hazardous decomposition products

Haz. decomp. products: In combustion emits toxic fumes.

Section 11: Toxicological information

11.1. Information on toxicological effects

Hazardous ingredients:

C14-C17 CHLORINATED PARAFFIN

ORAL	RAT	LD50	> 2000	mg/kg
------	-----	------	--------	-------

PINE OIL

DERMAL	RBT	LD50	> 5000	mg/kg
ORAL	RAT	LD50	> 3200	mg/kg

Toxicity values: No data available.

Symptoms / routes of exposure

Skin contact: There may be mild irritation at the site of contact.

Eye contact: There may be irritation and redness.

Ingestion: There may be irritation of the throat.

Inhalation: There may be irritation of the throat with a feeling of tightness in the chest.

Delayed / immediate effects: No data available.

Other information: May cause harm to breastfed babies.

Section 12: Ecological information

12.1. Toxicity

[cont...]

SAFETY DATA SHEET

RTD COMPOUND

Page: 6

Ecotoxicity values:

Species	Test	Value	Units
Daphnia magna	48H EC50	0.006	mg/l
FISH	96H LC50	>5000	mg/l
ALGAE	96H ErC50	>3.2	mg/l

Hazardous ingredients:

C14-C17 CHLORINATED PARAFFIN

ALGAE	96H ErC50	>3.2	mg/l
Daphnia magna	48H EC50	0.006	mg/l
FISH	96H LC50	>5000	mg/l

PINE OIL

ALGAE	96H ErC50	> 1.81	mg/l
FISH	96H LC50	0.221	mg/l

12.2. Persistence and degradability

Persistence and degradability: Not biodegradable.

12.3. Bioaccumulative potential

Bioaccumulative potential: Bioaccumulation potential.

12.4. Mobility in soil

Mobility: Non-volatile. Absorbed only slowly into soil.

12.5. Results of PBT and vPvB assessment

PBT identification: This product is not identified as a PBT/vPvB substance.

12.6. Other adverse effects

Other adverse effects: Toxic to aquatic organisms. Toxic to soil organisms.

Section 13: Disposal considerations

13.1. Waste treatment methods

Disposal operations: Transfer to a suitable container and arrange for collection by specialised disposal company.

Recovery operations: No data available

Waste code number: 12 01 99

Disposal of packaging: Dispose of in a regulated landfill site or other method for hazardous or toxic wastes.

NB: The user's attention is drawn to the possible existence of regional or national regulations regarding disposal.

[cont...]

SAFETY DATA SHEET

RTD COMPOUND

Page: 7

Section 14: Transport information

14.1. UN number

UN number: UN3077

14.2. UN proper shipping name

Shipping name: ENVIRONMENTALLY HAZARDOUS SUBSTANCE, SOLID, N.O.S
(C14-C17 CHLORINATED PARAFFIN)

14.3. Transport hazard class(es)

Transport class: 9

14.4. Packing group

Packing group: III

14.5. Environmental hazards

Environmentally hazardous: Yes

Marine pollutant: Yes

14.6. Special precautions for user

Special precautions: No special precautions.

Tunnel code: E

Transport category: 3

14.7. Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code

Transport in bulk: No data available.

Section 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

Specific regulations: Not applicable.

15.2. Chemical Safety Assessment

Chemical safety assessment: A chemical safety assessment has not been carried out for the substance or the mixture by the supplier.

Section 16: Other information

Other information

Other information: This safety data sheet is prepared in accordance with Commission Regulation (EU) No 453/2010.

Phrases used in s.2 and s.3: EUH066: Repeated exposure may cause skin dryness or cracking.
EUH208: Contains <name of sensitising substance>. May produce an allergic reaction.
H226: Flammable liquid and vapour.
H315: Causes skin irritation.
H317: May cause an allergic skin reaction.
H319: Causes serious eye irritation.

[cont...]

SAFETY DATA SHEET

RTD COMPOUND

Page: 8

H362: May cause harm to breast-fed children.

H400: Very toxic to aquatic life.

H410: Very toxic to aquatic life with long lasting effects.

H411: Toxic to aquatic life with long lasting effects.

Legal disclaimer: The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. This company shall not be held liable for any damage resulting from handling or from contact with the above product.