

AXIS Q1614-E Network Camera

Outdoor-ready with outstanding HDTV 720p video in 50/60 fps

The outdoor-ready AXIS Q1614-E supports Wide Dynamic Range - Dynamic Capture, providing homogeneous images without too dark or too bright parts. Remote back focus enables fine-tuning of the focus from a computer, and the pixel counter helps verifying the pixel resolution of an object or face. Leveling assistance guides the camera to the correct level, and auto rotation flips the image to the right orientation. The IP66- and NEMA 4X-rated AXIS Q1614-E offers a robust aluminum casing with an included sunshield and wall bracket. Arctic Temperature Control ensures safe start-up in extreme cold.

- > Arctic Temperature Control, -40 °C to 50 °C (-40 °F to 122 °F)
- > HDTV 720p at 50/60 fps
- > Wide Dynamic Range - Dynamic Capture and Lightfinder
- > Auto rotation and leveling assistance
- > Shock detection



AXIS Q1614-E Network Camera

Camera		Event actions
Image sensor	Progressive scan RGB CMOS 1/3"	File upload: FTP, SFTP, HTTP, HTTPS, network share and email, Send video clip Notification: email, HTTP, HTTPS and TCP Overlay text, Send SNMP Trap Video and audio recording to edge storage Pre- and post-alarm video buffering External output activation, Day/night vision mode, Play audio clip, Status LED, WDR mode
Lens	Varifocal, IR corrected, CS-mount, Megapixel resolution P-Iris 2.8-8 mm, F1.2 Horizontal angle of view: 80°-34°	
Day and night	Automatically removable infrared-cut filter	
Minimum illumination	Extended D1: Color: 0.05 lux, B/W: 0.008 lux, F1.2 HDTV 720p 25/30 fps: Color: 0.1 lux, B/W: 0.02 lux, F1.2 With WDR-Dynamic Capture: Color: 0.4 lux, B/W: 0.06 lux, F1.2 HDTV 720p 50/60 fps: Color: 0.2 lux, B/W: 0.04 lux, F1.2	Data streaming Event data
Shutter time	1/43500 to 2 s	Built-in installation aids Focus assistant, Pixel counter, Remote back focus Leveling assistant, Auto rotation
Pan/Tilt/Zoom	Digital PTZ, Uploadable PTZ driver (Pelco D pre-installed)	
Video		General
Video compression	H.264 (MPEG-4 Part 10/AVC), Main and Baseline Profile, Motion JPEG	Casing Camera: Metal (zinc) Color: White NCS S 1002-B IP66- and NEMA 4X-rated, IK10 impact resistant aluminum enclosure
Resolutions	Extended D1: 768x576 to 160x90 HDTV 720p 50/60 fps: 1280x720 to 160x90 HDTV 720p 25/30 fps: 1280x960 ^a to 160x90	Memory 256 MB RAM, 128 MB Flash
Frame rate	50/60 fps (no WDR)	Power Power over Ethernet IEEE 802.3af/802.3at Type 1 Class 3, max. 12.95 W or High PoE: max. 25.5 W
Video streaming	Multiple, individually configurable streams in H.264/Motion JPEG, Controllable frame rate and bandwidth VBR H.264	Connectors RJ45 10BASE-T/100BASE-TX PoE, 3.5 mm mic/line in, 3.5 mm line out RS485/RS422, Terminal block for two configurable inputs/outputs (12 V DC output, max. load 50 mA)
Image settings	Compression, Color, Brightness, Sharpness, Contrast, White balance, Exposure control, Exposure zone, Backlight compensation, Fine tuning of behavior at low light, Text and image overlay, Privacy mask, Mirroring of images Rotation: Auto, 0°, 90°, 180°, 270° including Corridor Format WDR-Dynamic Capture: Up to 120 dB depending on scene, Day/Night shift level, Shadow and highlight recovery Auto-rotation	Edge storage Support for microSD/microSDHC/microSDXC card Support for recording to dedicated network-attached storage (NAS) For SD card and NAS recommendations see www.axis.com
Audio		Operating conditions -30 °C to 50 °C (-22 °F to 122 °F) with PoE down to -40 °C (-40 °F) with Axis High PoE Midspan, max. 30 W Humidity 10-100% RH (condensing)
Audio streaming	Two-way	Approvals EN 55022 Class B, EN 61000-3-2, EN 61000-3-3, EN 55024, EN 61000-6-1, EN 61000-6-2, FCC Part 15 Subpart B Class B, ICES-003 Class B, VCCI Class B, C-tick AS/NZS CISPR 22 Class B, IEC/EN/UL 60950-1 KCC KN22 Class B, KN24 EN 50121-4, IEC 62236-4, IEC/EN/UL 60950-22, IEC/EN 60529 IP66, NEMA 250 Type 4X, IEC 60068-2-6, IEC 60068-2-27, IEC/EN 62262 IK10
Audio compression	AAC-LC 8/16/32 kHz, G.711 PCM 8 kHz, G.726 ADPCM 8 kHz Configurable bit rate	Dimensions 161 x 142 x 404 mm (6 5/16 x 5 9/16 x 15 15/16 in)
Audio input/output	External microphone, input or line input, line output External balanced/unbalanced microphone or line input, line output	Weight AXIS Q1614-E: 3525 g (7.7 lb)
Network		Included accessories Stand, Connector kit, Resistorx T20 tool, Installation Guide, Windows decoder 1-user license AXIS T94Q01A Wall Mount, Sunshield
Security	Password protection, IP address filtering, HTTPS ^b encryption, IEEE 802.1X ^b network access control, Digest authentication, User access log, Centralized Certificate Management	Optional accessories AXIS T91A47 Pole Mount, AXIS T94R01P Conduit Back Box, VT Corner Mount WCWA, VT Column Mount Ball Joint WFWCA, AXIS T98A16-VE Surveillance Cabinet, Axis Optional Lenses, AXIS T90B Illuminators, Axis network cable couplers, AXIS T8120 Midspan 15 W 1-port, AXIS T8133 Midspan 30 W 1-port, AXIS T8129 PoE Extender, AXIS Surveillance microSDXC™ Card 64 GB
Supported protocols	IPv4/v6, HTTP, HTTPS ^b , SSL/TLS ^b , QoS Layer 3 DiffServ, FTP, CIFS/SMB, SMTP, Bonjour, UPnP™, SNMPv1/v2c/v3 (MIB-II), DNS, DynDNS, NTP, RTP, SFTP, TCP, UDP, IGMP, RTCP, ICMP, DHCP, ARP, SOCKS, SSH	Video management software AXIS Camera Companion, AXIS Camera Station, Video management software from Axis' Application Development Partners available on www.axis.com/techsup/software
System integration		Languages German, French, Spanish, Italian, Russian, Simplified Chinese, Japanese, Korean, Portuguese
Application Programming Interface	Open API for software integration, including VAPIX® and AXIS Camera Application Platform; specifications at www.axis.com AXIS Video Hosting System (AVHS) with One-Click Connection ONVIF Profile S, specification at www.onvif.org	Warranty Axis 3-year warranty and AXIS Extended Warranty option, see www.axis.com/warranty
Analytics	Video motion detection, Active tampering alarm, Audio detection Support for AXIS Camera Application Platform enabling installation of AXIS Video Motion Detection 3, AXIS Cross Line Detection, AXIS Digital Autotracking and third-party applications, see www.axis.com/acap	
Event triggers	Analytics, Edge storage events, External input Shock detection	

- a. 1400x1050 (1.4 MP) scaled resolution available via VAPIX®
b. This product includes software developed by the OpenSSL Project for use in the OpenSSL Toolkit (<http://www.openssl.org/>), and cryptographic software written by Eric Young (ey@cryptsoft.com).

More information is available at www.axis.com