

Premises Distribution Plenum Indoor/Outdoor

6 x OM3 Premise Distribution Plenum Indoor/Outdoor Cable

Part Number: PDP006EB3010/25-I/O-C4(AQU)

Berk-Tek's plenum rated Indoor/Outdoor Tight-Buffer cables are designed specifically for LAN/WAN campus and building backbone cabling infrastructure. These thermoplastic jacketed cables are suitable for Indoor/Outdoor installations, inconduit, below the frost line.

Description

This fiber optic cable is designed for installation in plenum, riser and horizontal environments and interbuilding backbone structures.

This design incorporates tight buffered optical fibers within a dry water blocked cable core. Suitable for operation across wide temperature variations typically addressed by outside plant cables. No Buffer Tube Fanout kits are required. Direct termination is enabled.

Construction

Each cable utilizes our DryGel water blocking system in the cable core. Cable design can accommodate from 4-24 tight buffered (900 $\mu m)$ fibers. All dielectric.

Interlocking Armor (Armor-Tek) versions are available using aluminum or steel armor.

Outdoor Considerations

These water-blocked plenum-rated cables feature UV and fungus resistant jacketing.

For use in conduit, below the frost line.

Loose Tube cables are recommended if interbuilding conduit systems lie above the frost line and are likely to fill with water.


• Tight Buffer fiber cables are not suitible for aerial-lashed installations.

Applications

Berk-Tek's tight buffered cable is intended for all high speed data applications including:

- 10BASE-FL
- 100BASE-SX/100BASE-FX
- ATM 155/ATM 622
- 1000BASE-SX/1000BASE-LX
- Fibre Channel 1.062/2.125
- 10GBASE-SR/SW
- 10GBASE-LX4
- 40/100 GbE

Features



Standards

International EN 50173; ISO/ IEC 11801

National ANSI/ICEA S-104-696; ANSI/ICEA S-83-596; ANSI/TIA-568-C.3; Telcordia GR-409

Generated 12/21/15 - http://www.nexans.us

All drawings, designs, specifications, plans and particulars of weights, size and dimensions contained in the technical or commercial documentation of Nexans is indicative only and shall not be binding on Nexans or be treated as constituting a representation on the part of Nexans.



Premises Distribution Plenum Indoor/Outdoor

6 x OM3 Premise Distribution Plenum Indoor/Outdoor Cable

- Flexible, small diameter, 900 µm tight buffered construction
- High tensile strength and small diameter design
- 4 to 24 count fiber construction plenum designs ideal for horizontal and backbone installation
- · Single-mode, multimode, and hybrid designs available
- · Also available in low smoke zero halogen design

Benefits

- · Cost-saving design, easy to install and terminate
- · Provides for greater pulling distances thus reducing installation time
- Assurance that cables will meet required specifications for communication networking applications
- Broad design selection allows for mix and match of fiber components to specific networking applications
- One cable design meeting all structured cabling network communications applications

Characteristics

Construction characteristics	
Fiber optic type	OM3 50/125
Type of cable	Tight Buffered (TB)
Jacket Material	Plenum
Sheath colour	Aqua
Dimensional characteristics	
Number of optical fibres	6
Cable diameter (Nominal)	0.18 in
Nominal outer diameter	4.6 mm
Nominal cable weight	12 lb/kft
Approximate weight	18 kg/km
Fransmission characteristics	
Optical performance	EB (50/125 GIGAlite-10, OM3)
Attenuation, max. 850 nm (cabled)	3.0 dB/km
Attenuation, max. 1300 nm (cabled)	1.0 dB/km
Nechanical characteristics	
Maximum installation tension	100 lb
Maximum installation tension	445 N
Max. Load. Long Term (lbs)	30.0 lb
Max. Load. Long Term	133.0 N
Crush resistance per TIA/EIA FOTP-41	100 N/cm
Cable flexibility per TIA/EIA FOTP-104	100 cycles
Impacts per TIA/EIA FOTP-25	2 at 4.41 N-m
Jsage characteristics	
Minimum Bending Radius - Install	2.7 in
Minimum Bend Radius - Install	6.9 cm
Minimum Bending Radius - LongTerm	1.8 in
Minimum Bending Radius - LongTerm	4.6 cm

Generated 12/21/15 - http://www.nexans.us

All drawings, designs, specifications, plans and particulars of weights, size and dimensions contained in the technical or commercial documentation of

Page 2 / 4

Nexans is indicative only and shall not be binding on Nexans or be treated as constituting a representation on the part of Nexans.



Premises Distribution Plenum Indoor/Outdoor


6 x OM3 Premise Distribution Plenum Indoor/Outdoor Cable

Usage characteristics	
Operating temperature, range	-40 75 °C
Ambient installation temperature, range	0 75 °C
Storage temperature, range	-40 85 °C
Field of application	Indoor, Outdoor

Standard Sheath Colors

Fiber Type	Core Size (um)	ISO-TIA Standard	Effective Modal BW @ 850 nm	Overfilled Launch BW @ 850 nm	Attenuation @ 850 nm	Attenuation @ 1300 nm	Attenuation @ 1550 nm	Sheath Color
AB	8.3	OS2	NS	NS	NS	0.7 dB/km	0.7 dB/km	Black
СВ	62.5	OM1	200 MHz-km	200 MHz-km	3.5 dB/km	1.0 dB/km	NS	Black
GB	62.5	OM1+	500 MHz-km	350 MHz-km	3.5 dB/km	1.0 dB/km	NS	Black
ZB	50	OM2	500 MHz-km	500 MHz-km	3.5 dB/km	1.5 dB/km	NS	Black
LB	50	OM2+	950 MHz-km	700 MHz-km	3.0 dB/km	1.0 dB/km	NS	Black
EB	50	OM3	2000 MHz-km	1500 MHz-km	3.0 dB/km	1.0 dB/km	NS	Black
FB	50	OM4	4700 MHz-km	3500 MHz-km	3.0 dB/km	1.0 dB/km	NS	Black
XB	50	OM4+	4900 MHz-km	3675 MHz-km	3.0 dB/km	1.0 dB/km	NS	Black
NS = Not Specified								

Cross-section Diagram - PDP006-I/O



Generated 12/21/15 - http://www.nexans.us

All drawings, designs, specifications, plans and particulars of weights, size and dimensions contained in the technical or commercial documentation of Nexans is indicative only and shall not be binding on Nexans or be treated as constituting a representation on the part of Nexans.



Premises Distribution Plenum Indoor/Outdoor

6 x OM3 Premise Distribution Plenum Indoor/Outdoor Cable

Manufacturing Release

IMPORTANT NOTICE: This product specification is provided for informational purposes only in order to illustrate typical product constructions, applications and/or methods of installation. Because conditions of actual installation and use are unique and will vary, Berk-Tek makes no representation or warranty as to the reliability, accuracy or completeness of this data, even if Berk-Tek is aware of the product's intended use or purpose. Furthermore, this data does not constitute, nor should it be regarded or relied upon, as professional engineering advice. Installation of product should only be done by qualified personnel and in conformance with all safety, electrical and other applicable codes, standards, rules or regulations. Appropriate and correct product selection, installation and use, and compliance with all such codes, standards, rules and regulations, is a customer/end-user responsibility. Product specifications, standards, programs or services are subject to improvement or changes without notice. Berk-Tek accepts no liability for typographical errors, technical inaccuracies, omissions or misuse of the information contained herein. Changes will be periodically made to address any such issues.

Generated 12/21/15 - http://www.nexans.us

Page 4/4

All drawings, designs, specifications, plans and particulars of weights, size and dimensions contained in the technical or commercial documentation of Nexans is indicative only and shall not be binding on Nexans or be treated as constituting a representation on the part of Nexans.