

MODELS:

SRW12US / SRW12USG

SmartRack® Wall-Mount Rack Enclosure Cabinets



12 Rack Units



200 lb
Load Rating



Sturdy Steel
Construction



Locking Doors
& Side Panels



Plexiglas®
Front Door
(SRW12USG
only)



Standard
19" Rack Width



Convenient
Cable Access



Adjustable
Mounting Rails



Hinged Wall
Bracket



Ventilated for
Ample Airflow





Reversible
Cabinet



Square Hole
Mounting

- A** Front Door
(Lockable/Removable/Reversible.
SRW12US door is perforated;
SRW12USG door has a Plexiglas® insert.)
- B** Adjustable Mounting Rails (4)
- C** Side Panels (2)
(Lockable/Removable)
- D** Hinged Wall Bracket
(Lockable/Reversible. Allows the cabinet
to swing away from the wall for convenient
rear access to equipment and cabling.)
- E** Cable Access Port Covers (2)
(Removable)
- F** Ventilation Fan Ports (4)
(Support optional SRFANWM fan kit.)
- G** Keys (2)

Also Includes: Owner's manual, mounting
plate screws (3), cabinet ground screw, pre-
installed front door ground wire and rackmount
equipment mounting hardware (12 cage nuts,
12 mounting screws, 12 nylon cup washers).



- Wall-mount enclosures provide convenient, locking storage for rackmount IT devices and other equipment that should be off the floor, out of the way and secure
- The cabinet is fully reversible, allowing installers to change door hinges from left to right by simply rotating the unit 180 degrees before mounting
- Hinged wall bracket allows cabinet to swing away from the wall for convenient access to equipment and cabling

SEE NEXT PAGE FOR DETAILED UNIT MEASUREMENTS


Specifications

Models	SRW12US / SRW12USG
Rack Spaces	12U
Equipment Mounting Depth	Up to 20.5 in (520.7 mm)
Load Rating*	200 lb (90.7 kg)
Unit Dimensions (H x W x D)	25.08 x 24.53 x 21.57 in (637 x 623.07 x 548 mm)
Shipping Dimensions (H x W x D)	27.95 x 26.38 x 24.41 in (710 x 670 x 620 mm)
Unit Weight	60 lb (27.21 kg)
Shipping Weight	64 lb (28.8 kg) / 70 lb (31.5 kg)
Regulatory Compliance	Meets EIA-310-D, IEC 60297-3-100, NOM, DIN 41494, RoHS and PCI-DSS standards; IP20 Protection Rating


* The load rating includes the combined weight of the unit and installed equipment. The unit must be mounted to a stable surface with user-supplied anchors capable of bearing the full load. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.




1111 W. 35th Street
Chicago, IL 60609 USA
773.869.1234
www.triplite.com




TOP/BOTTOM VIEW



FRONT VIEW



SIDE VIEW





REAR VIEW

Dimensions: [mm] INCHES

Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

MODELS:
SRW12US / SRW12USG





MODELS:
SRW12US / SRW12USG



1111 W. 35th Street
Chicago, IL 60609 USA
773.869.1234
www.tripplite.com

Dimensions: [mm] INCHES

Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.