

AXIS 230 MPEG-2 Network Camera

*Live, full resolution MPEG-2 video
over your network*

The AXIS 230 MPEG-2 Network Camera is a high quality video camera that delivers 25/30 frames per second of DVD-quality video with synchronized audio over an IP network. It uses less bandwidth compared to equal Motion JPEG video, and provides the user with controllable constant bit rate. This makes it ideal for high-end security usage, such as traffic monitoring, casinos and airports, where high quality full frame rate video and quality audio are of vital importance.

This IR sensitive camera is based around a color camera block with built-in 18x optical zoom lens, day/night functionality (color image during daytime, black and white image during night time) and one way audio (from camera to viewer). It compresses video and audio into standard MPEG-2 and makes this available over the network supporting both uni- and multicast. For customers requiring Pan/Tilt control, it is also equipped with built-in support for RS232/485 and comes complete with support for a selected range of Pan/Tilt heads.



- IR-sensitive day/night camera
- Powerful, 18x optical zoom lens
- Synchronized audio and built-in microphone
- Built-in Web server



AXIS 230 MPEG-2 Network Camera



General

- DVD-quality video and synchronized audio over LAN using MPEG-2 compression (Unicast and Multicast)
- Automatic day/night functionality
- Remote configuration and status using Web-based tools
- MPEG-2 Decoder for Windows with 3 viewer licenses included

Functions

- Built-in Web server
- Pre-alarm video storage
- Text, time/date overlay
- Support for selected range of Pan/Tilt heads
- Audio support through external or built-in microphone
- Audio detection alarm, triggers an event when a defined audio level is reached
- Event functionality with alarm notification via e-mail, TCP or HTTP
- Remote MPEG file upload via FTP

System Requirements

The following specification applies to the use of browser based viewing.

- Pentium III 1GHz or higher, AMD Athlon, 256MB
- AGP-card with 32MB memory and support for DirectDraw
- Windows 2000 or Windows XP
- Internet Explorer 5.5 or higher
- DirectX 9 or higher

Alternatively, use AXIS 292 Network Video Decoder + monitor

Hardware & System

- Sony ExView 1/4" CCD day/night module, IR-sensitive
- Motorized zoom lens 4.1 – 73.8 mm, F1.4 – 3.0
- Horizontal viewing angle: 48 – 2.8 degrees, 37mm thread on front allow use of standard filters and wide converters
- Auto Focus, 18x optical + 12x digital zoom
- AXIS ETRAX 100LX 32-bit RISC CPU
- MPEG-2 based compression chip
- Linux 2.4 kernel
- 32 MB RAM and 4 MB Flash
- Electronic shutter 1 – 1/10.000 sec
- White balance: ATW/AWB/Manual/Indoor/Outdoor

Connections

- Network: 10Base-T/100Base-TX Ethernet networks (RJ-45)
- Serial communication: RS-232 (DB-9) and RS-485 (terminal block)
- I/O: 2 alarm inputs + 1 output (terminal block)
- Video: Analog composite video output (BNC)
- Audio: Mic/Line stereo input (3.5mm jack)
- Power: 9 VDC / 9 W – external power supply, included

Video & Audio

- Color and black/white
- Minimum illumination:
 - Color: 0.3 lux @ F1.4 (30 IRE)
 - B/W: 0.005 lux @ F1.4 (30 IRE)
- Image compression: MPEG-2 (main profile, main level)
- 7 video quality levels: 0.25–8 Mbit/s per client
- Available resolutions (PAL/NTSC):
 - D1: 720 x 576 / 720 x 480
 - 4CIF: 704 x 576 / 704 x 480
 - 2CIF: 704 x 288 / 704 x 240
 - CIF: 352 x 288 / 352 x 240
 - QCIF: 160 x 144 / 160 x 112
- 6 audio quality levels

Security

- User level password protection
- IP Address filtering

Firmware Updates

- Flash memory allows firmware updates over the network using FTP over TCP/IP. Firmware upgrades are available from www.axis.com

Customer Applications

- Designed for system integration and custom application development by providing:
 - AXIS HTTP API
 - AXIS Media Control SDK
 - Embedded scripting support

Operating Conditions

- Temp: 5 – 50 °C (41 – 122 °F)
- Humidity: 20 – 80% RHG

Dimensions and Weight

- Height: 80 mm (3.15 in.)
- Width: 75 mm (2.95 in.)
- Depth: 171 mm (6.73 in.)
- Weight: 752 g (1,65 lb.) (camera only)

Approvals

- EMC:
 - CE Compliant according to: EN55022/1998 Class B, EN55024/1998, EN61000-3-2, EN61000-3-3, EN61000-6-2
 - FCC Part 15 subpart B
 - VCCI
 - C-tick AS/NZS 3548
 - Safety: EN60950, CSA

Included Accessories

- Power supply
- Mounting bracket
- Connector kit
- User manual
- One encoding and three decoding MPEG-2 licenses

Available Accessories (not included)

- AXIS MPEG-2 Server 10 user license pack, provides 10 additional MPEG-2 decoding licenses
- Axis IR Illuminators – get good quality images around the clock, in low-light situations (and in complete darkness) without attracting attention

www.axis.com