


## Fire Alarm Nonshielded Nonplenum

**Product Description**

Power limited fire alarm and communications cable for riser or nonriser applications. Fire alarm, smoke detectors, signaling and fire-protective circuits. XX in part number denotes color; call your local sales representative for specific requirements.

**Specifications**

- CONDUCTOR: Solid bare copper
- INSULATION: PVC
- JACKET: PVC with rip cord
- STANDARDS: NEC FPLR, UL/ETL Listed
- TEMPERATURE: 75°C

**Tech. Info & Standards**

PVC

Solid conductor

FPLR, UL/ETL Listed

Part No.	Conductor Size AWG	No. of Conductors	Insulation Thickness (in.)	Jacket Thickness (in.)	Nom. O.D. (in.)	Approx. Wt. lb./1,000 ft.
FA-1202C-1-1N-XX	12	2	0.012	0.015	0.264	62
FA-1204C-1-1N-XX	12	4	0.012	0.015	0.258	80
FA-1402C-1-1N-XX	14	2	0.010	0.015	0.212	40
FA-1404C-1-1N-XX	14	4	0.010	0.015	0.252	73
FA-1602C-1-1N-XX	16	2	0.010	0.015	0.183	28
FA-1604C-1-1N-XX	16	4	0.010	0.015	0.216	49
FA-1802C-1-1N-XX	18	2	0.010	0.015	0.156	19
FA-1804C-1-1N-XX	18	4	0.010	0.015	0.181	33
FA-1806C-1-1N-XX	18	6	0.010	0.015	0.223	49
FA-2204C-1-1N-XX	22	4	0.010	0.015	0.122	15

Electrical and Electronic Wire & Cable • Enterprise Cabling & Security Solutions • Fasteners

Anixter Inc. World Headquarters • 2301 Patriot Boulevard, Glenview, IL 60026-8020 • 1.800.ANIXTER • 224.521.8000 • anixter.com

Anixter is a leading global supplier of communications and security products, electrical and electronic wire and cable, fasteners and other small components. We help our customers specify solutions and make informed purchasing decisions around technology, applications and relevant standards. Throughout the world, we provide innovative supply chain management solutions to reduce our customers' total cost of production and implementation.

Anixter does not manufacture the items described in this publication. Any applicable product warranties are provided by the manufacturers. To the fullest extent permitted by law, Anixter disclaims all warranties, either express or implied.

The information provided and any images shown are for descriptive purposes only. Anixter makes no warranty or representation, express or implied, about the accuracy or completeness of any information provided. Data and suggestions made in the publication are not to be construed as recommendations to purchase or as authorizations to use any products in violation of any law or regulation. All products are sold subject to Anixter's General Conditions of Sale.