

# Safety Data Sheet

## According to 1907/2006 EC - 453/2010 EC

Printing date 08.07.2014

Version number 5

Revision: 08.07.2014

### 1 Identification of the substance/mixture and of the company/undertaking

- **Product identifier**
- **Trade name:** RENOLIT EP 2
- **Article number:** 600046903
- **Relevant identified uses of the substance or mixture and uses advised against**
- **Sector of Use** SU3 Industrial uses: Uses of substances as such or in preparations at industrial sites
- **Application of the substance / the mixture** LUBRICATING GREASE
- **Details of the supplier of the safety data sheet**
- **Manufacturer/Supplier:**  
FUCHS LUBRICANTS (UK) PLC.  
New Century Street  
Hanley  
Stoke-on-Trent, Staffordshire, ST1 5HU  
UK  
e-mail: product.safety@fuchs-oil.com
- **Further information obtainable from:** Product safety department.
- **Emergency telephone number:**  
Fuchs Lubricants (UK) Emergency telephone: (UK) 01782 203700  
NHS Direct: 0845 46 47 / Textphone: 0845 606 46 47

### 2 Hazards identification

- **Classification of the substance or mixture**
- **Classification according to Regulation (EC) No 1272/2008**  
The product is not classified according to the CLP regulation.
- **Classification according to Directive 67/548/EEC or Directive 1999/45/EC** Not applicable.
- **Information concerning particular hazards for human and environment:**  
The product does not have to be labelled due to the calculation procedure of the "General Classification guideline for preparations of the EU" in the latest valid version.
- **Classification system:**  
The classification is according to the latest editions of the EU-lists, and extended by company and literature data.
- **Label elements**
- **Labelling according to EU guidelines:**  
Observe the general safety regulations when handling chemicals.  
The product is not subject to identification regulations under EU Directives and the Ordinance on Hazardous Materials (German GefStoffV).
- **Special labelling of certain preparations:**  
Contains Amine phosphate, Substituted Triazole. May produce an allergic reaction.  
Safety data sheet available for professional user on request.
- **Other hazards**
- **Results of PBT and vPvB assessment**
- **PBT:** Not applicable.
- **vPvB:** Not applicable.

### 3 Composition/information on ingredients

- **Chemical characterization:** Mixtures
- **Description:** A blend of highly refined mineral oils and multifunctional additives with thickener system.

(Contd. on page 2)

\*

# Safety Data Sheet

## According to 1907/2006 EC - 453/2010 EC









Printing date 08.07.2014

Version number 5

Revision: 08.07.2014

**Trade name: RENOLIT EP 2**

(Contd. of page 1)

|   |   |         |
|---|---|---------|
| <b>· Dangerous components:</b>                                    |   |         |
| CAS: 12001-85-3<br>EINECS: 234-409-2                              | Zinc naphthenate<br><br>           | 1-2.5%  |
| CAS: 68649-42-3<br>EINECS: 272-028-3<br>Reg.nr.: 01-2119657973-23 | Zinc alkyl dithiophosphate<br><br> | 0.25-1% |
| EC number: 931-384-6<br>Reg.nr.: 01-2119493620-38-XXXX            | Amine phosphate<br><br>           | 0.25-1% |
| CAS: 80595-74-0<br>EINECS: 279-514-4                              | Substituted Triazole<br><br>      | <0.25%  |

· SVHC None

**· Additional information:**

Annex I Nota L applies to the base oil(s) in this product. Nota L - The classification as a carcinogen need not apply if it can be shown that the substance contains less than 3 % DMSO extract as measured by IP 346.  
For the wording of the listed phrases refer to section 16.

### 4 First aid measures

**· Description of first aid measures**

· **General information:** Immediately remove any clothing soiled by the product.

· **After inhalation:** Supply fresh air; consult doctor in case of complaints.

**· After skin contact:**

Immediately wash with water and soap and rinse thoroughly.

If skin irritation continues, consult a doctor.

**· After eye contact:**

Check for and remove any contact lenses.

Rinse opened eye for several minutes under running water.

**· After swallowing:**

Wash mouth out with water

Seek medical treatment.

· **Information for doctor:** Treat symptomatically

· **Most important symptoms and effects, both acute and delayed** No further relevant information available.

· **Indication of any immediate medical attention and special treatment needed**

No further relevant information available.

### 5 Firefighting measures

**· Extinguishing media****· Suitable extinguishing agents:**

CO2, powder or water spray. Fight larger fires with water spray or alcohol resistant foam.

Use fire extinguishing methods suitable to surrounding conditions.

· **For safety reasons unsuitable extinguishing agents:** Water with full jet

· **Special hazards arising from the substance or mixture** No further relevant information available.

**· Advice for firefighters****· Protective equipment:**

Wear self-contained respiratory protective device.

Wear fully protective suit.

GB

(Contd. on page 3)

# Safety Data Sheet

## According to 1907/2006 EC - 453/2010 EC

Printing date 08.07.2014

Version number 5

Revision: 08.07.2014

**Trade name: RENOLIT EP 2**

(Contd. of page 2)

### 6 Accidental release measures

- **Personal precautions, protective equipment and emergency procedures**

Particular danger of slipping on leaked/spilled product.

- **Environmental precautions:**

Do not allow to penetrate the ground/soil.

Do not allow to enter sewers/ surface or ground water.

- **Methods and material for containment and cleaning up:**

Pick up mechanically.

Send for recovery or disposal in suitable receptacles.

- **Reference to other sections**

No dangerous substances are released.

See Section 7 for information on safe handling.

See Section 8 for information on personal protection equipment.

See Section 13 for disposal information.

### 7 Handling and storage

- **Handling:**

- **Precautions for safe handling** No special measures required.

- **Information about fire - and explosion protection:** No special measures required.

- **Conditions for safe storage, including any incompatibilities**

- **Storage:**

- **Requirements to be met by storerooms and receptacles:** Prevent any seepage into the ground.

- **Information about storage in one common storage facility:** Store away from oxidizing agents.

- **Further information about storage conditions:** Store in cool, dry conditions in well sealed receptacles.

- **Specific end use(s)** No further relevant information available.

### 8 Exposure controls/personal protection

- **Additional information about design of technical facilities:** No further data; see item 7.

- **Control parameters**

- **Ingredients with limit values that require monitoring at the workplace:**

The product does not contain any relevant quantities of materials with critical values that have to be monitored at the workplace.

- **Additional information:** The lists valid during the making were used as basis.

- **Exposure controls**

- **Personal protective equipment:**

Select PPE appropriate for the operations taking place taking into account the product properties.

- **General protective and hygienic measures:**

The usual precautionary measures are to be adhered to when handling chemicals.

Immediately remove all soiled and contaminated clothing

Wash hands before breaks and at the end of work.

Do not eat, drink, smoke or sniff while working.

Do not carry product impregnated cleaning cloths in trouser pockets.

Avoid close or long term contact with the skin.

- **Respiratory protection:** Not required.

- **Protection of hands:**



Protective gloves (EN374)

The glove material has to be impermeable and resistant to the product/ the substance/ the preparation.

(Contd. on page 4)

# Safety Data Sheet

## According to 1907/2006 EC - 453/2010 EC

Printing date 08.07.2014

Version number 5

Revision: 08.07.2014

**Trade name: RENOLIT EP 2**

(Contd. of page 3)

Selection of the glove material on consideration of the penetration times, rates of diffusion and the degradation

- **Material of gloves**

The selection of the suitable gloves does not only depend on the material, but also on further marks of quality and varies from manufacturer to manufacturer. As the product is a preparation of several substances, the resistance of the glove material can not be calculated in advance and has therefore to be checked prior to the application.

- **Penetration time of glove material**

The exact break through time has to be found out by the manufacturer of the protective gloves and has to be observed.

- **For the permanent contact gloves made of the following materials are suitable:**

Nitrile rubber, NBR

Neoprene gloves

- **Not suitable are gloves made of the following materials:**

Butyl rubber, BR

Natural rubber, NR

- **Eye protection:** Not required.

- **Body protection:** Protective work clothing

## 9 Physical and chemical properties

- **Information on basic physical and chemical properties**

- **General Information**

- **Appearance:**

**Form:** Pasty

**Colour:** Brown

- **Odour:** Mineral-oil-like

- **Odour threshold:** Not determined.

- **pH-value:** Not applicable.

- **Change in condition**

**Melting point/Melting range:** Undetermined.

**Boiling point/Boiling range:** Undetermined.

- **Flash point:** > 100 °C

- **Flammability (solid, gaseous):** Not determined.

- **Ignition temperature:** >250 °C

- **Decomposition temperature:** Not determined.

- **Self-igniting:** Product is not selfigniting.

- **Danger of explosion:** Product does not present an explosion hazard.

- **Explosion limits:**

**Lower:** Not determined.

**Upper:** Not determined.

- **Vapour pressure:** Not applicable.

- **Density:** Not determined.

- **Relative density** Not determined.

- **Vapour density** Not applicable.

- **Evaporation rate** Not applicable.

- **Solubility in / Miscibility with water:**

Insoluble.

- **Partition coefficient (n-octanol/water):** Not determined.

(Contd. on page 5)

# Safety Data Sheet

## According to 1907/2006 EC - 453/2010 EC

Printing date 08.07.2014

Version number 5

Revision: 08.07.2014

**Trade name: RENOLIT EP 2**

(Contd. of page 4)

- **Viscosity:**
  - Dynamic:** Not applicable.
  - Kinematic at 40 °C:** 230.0 cSt (Base oil viscosity)
- **Other information** No further relevant information available.

### 10 Stability and reactivity

- **Reactivity**
- **Chemical stability**
- **Thermal decomposition / conditions to be avoided:**  
No decomposition if used and stored according to specifications.
- **Possibility of hazardous reactions** No dangerous reactions known.
- **Conditions to avoid** Naked flames, hot surfaces and other high temperature sources
- **Incompatible materials:** Strong oxidising agents.
- **Hazardous decomposition products:** Carbon monoxide and carbon dioxide

### 11 Toxicological information

- **Information on toxicological effects**
- **Acute toxicity:**

#### · **LD/LC50 values relevant for classification:**

##### **12001-85-3 Zinc naphthenate**

|        |      |                       |
|--------|------|-----------------------|
| Oral   | LD50 | 4920 mg/kg (rat)      |
| Dermal | LD50 | > 5000 mg/kg (rabbit) |

- **Primary irritant effect:**
- **on the skin:** No irritant effect.
- **on the eye:** No irritating effect.
- **Sensitization:** Sensitizing effect by skin contact is possible by prolonged exposure.
- **Additional toxicological information:**  
The product is not subject to classification according to the calculation method of the General EU Classification Guidelines for Preparations as issued in the latest version.  
When used and handled according to specifications, the product does not have any harmful effects to our experience and the information provided to us.

### 12 Ecological information

- **Toxicity**

#### · **Aquatic toxicity:**

##### **12001-85-3 Zinc naphthenate**

|           |                          |
|-----------|--------------------------|
| EC50/48 h | 4.6 - 8.2 mg/l (daphnia) |
| LC50/96 h | 1.53 - 2.0 mg/l (fish)   |

##### **Amine phosphate**

|           |                     |
|-----------|---------------------|
| EC50/48 h | 91.4 mg/l (daphnia) |
| LC50/96 h | 24 mg/l (fish)      |

- **Persistence and degradability** Inherently biodegradable
- **Behaviour in environmental systems:**
- **Bioaccumulative potential** Product is not expected to bioaccumulate.
- **Mobility in soil** No further relevant information available.
- **Additional ecological information:**
- **General notes:**  
Water hazard class 1 (German Regulation) (Self-assessment): slightly hazardous for water

(Contd. on page 6)

# Safety Data Sheet

## According to 1907/2006 EC - 453/2010 EC

Printing date 08.07.2014

Version number 5

Revision: 08.07.2014

**Trade name: RENOLIT EP 2**

(Contd. of page 5)

Do not allow undiluted product or large quantities of it to reach ground water, water course or sewage system.

- **Results of PBT and vPvB assessment**

- **PBT:** Not applicable.

- **vPvB:** Not applicable.

- **Other adverse effects** No further relevant information available.

### 13 Disposal considerations

- **Waste treatment methods**

- **Recommendation**

Must not be disposed together with household garbage. Do not allow product to reach sewage system.

Contact waste processors for recycling information.

Delivery of waste oil to officially authorized collectors only.

Used, degraded or contaminated product may be classified as hazardous waste. Anyone classifying hazardous waste and determining its fate must be qualified in accordance with state and international legislation.

- **European waste catalogue**

12 01 12\* spent waxes and fats

- **Uncleaned packaging:**

- **Recommendation:**

Empty contaminated packagings thoroughly. They may be recycled after thorough and proper cleaning.

Disposal must be made according to official regulations.

EWC 15 01 02 (plastic) or 15 01 04 (metal) if fully drained and cleaned; otherwise 15 01 10\*

Containers, even those that are "empty," may contain residues that can develop flammable vapours upon heating. Do not cut, drill, grind, weld, or perform similar operations on or near empty containers.

### 14 Transport information

- **UN-Number**

- **ADR, ADN, IMDG, IATA** Void

- **UN proper shipping name**

- **ADR, ADN, IMDG, IATA** Void

- **Transport hazard class(es)**

- **ADR, ADN, IMDG, IATA**

- **Class** Void

- **Packing group**

- **ADR, IMDG, IATA** Void

- **Environmental hazards:**

- **Marine pollutant:** No

- **Special precautions for user** Not applicable.

- **Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code**

Not applicable to packaged goods.

- **Transport/Additional information:**

Not dangerous according to the above specifications.

- **UN "Model Regulation":**

-

GB

(Contd. on page 7)

# Safety Data Sheet

## According to 1907/2006 EC - 453/2010 EC

Printing date 08.07.2014

Version number 5

Revision: 08.07.2014

**Trade name: RENOLIT EP 2**

(Contd. of page 6)

### 15 Regulatory information

- **Safety, health and environmental regulations/legislation specific for the substance or mixture**
- **National regulations:**
- **Other regulations, limitations and prohibitive regulations**
- **Substances of very high concern (SVHC) according to REACH, Article 57** None
- **Chemical safety assessment:** A Chemical Safety Assessment has not been carried out.

### 16 Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

This data sheet is a Safety Data Sheet in accordance with 1907/2006/EC - 453/2010/EC, Article 31.

For products which are not subject to classification according to EU lists, this data sheet is supplied on a voluntary basis.

- **Relevant phrases**
  - The Hazard / Risk phrases shown below are for those component substances which are listed in section 3 and not necessarily for the finished formulation.
  - Hazards are concentration dependent. Therefore for the hazard classification and risk/safety phrases appropriate for the actual finished formulated product refer to section 2.
- H226 Flammable liquid and vapour.
- H302 Harmful if swallowed.
- H315 Causes skin irritation.
- H317 May cause an allergic skin reaction.
- H318 Causes serious eye damage.
- H411 Toxic to aquatic life with long lasting effects.
- R22 Harmful if swallowed.
- R38 Irritating to skin.
- R41 Risk of serious damage to eyes.
- R43 May cause sensitisation by skin contact.
- R51/53 Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

- **Department issuing SDS:** Product safety department.

- **Contact:** STEVEN PRITCHARD

- **Abbreviations and acronyms:**

ADR: Accord européen sur le transport des marchandises dangereuses par Route (European Agreement concerning the International Carriage of Dangerous Goods by Road)

IMDG: International Maritime Code for Dangerous Goods

IATA: International Air Transport Association

GHS: Globally Harmonized System of Classification and Labelling of Chemicals

EINECS: European Inventory of Existing Commercial Chemical Substances

ELINCS: European List of Notified Chemical Substances

CAS: Chemical Abstracts Service (division of the American Chemical Society)

LC50: Lethal concentration, 50 percent

LD50: Lethal dose, 50 percent

- **\* Data compared to the previous version altered.**

GB