

HDMI In-Line Signal Booster/Extender, 1920x1200 at 24Hz/1080p (HDMI F/F)

MODEL NUMBER: **B122-000**



Description

Tripp Lite's B122-000 HDMI Signal Extender increases the distance a 1080p @ 24Hz (or 1920 x 1200) signal can be transmitted beyond the recommended 16 ft. (5 m.). It supports computer video resolutions up to 1920 x 1200, and HD resolutions up to 1080p @ 24Hz, as well as a maximum distance of 150 ft. from the source. Use P568-Series HDMI cables in most applications. When extending a 1080p @ 24Hz (or 1920 x 1200) signal more than 75 ft., use cable made with 24Awg wiring, such as the P568-100-HD. (Lengths over 100 ft. are available from Tripp Lite as a custom order) 24Awg HDMI cable is also needed when extending a 3D signal more than 50 ft.. A 3D signal can be extended up to 125 ft. using 24Awg HDMI cable. Simply connect the longer cable between the source and the B122-000, and the shorter cable (16 ft. or less) between the adapter and the monitor.

Software or drivers are not required. HDCP compliant. Compatible with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases.

Features

- Extend a 1080p @ 24Hz (or 1920 x 1200) HDMI signal up to 150 ft. from the source
- Use P568-Series HDMI cables in most applications
- When extending a 1080p @ 24Hz (or 1920 x 1200) signal more than 75 ft., use cable made with 24Awg wiring, such as the P568-100-HD. (Lengths over 100 ft. are available from Tripp Lite as a custom order)
- 24Awg HDMI cable is also needed when extending a 3D signal more than 50 ft.. A 3D signal can be extended up to 125 ft. using 24Awg HDMI cable
- Supports DTS-HD, Dolby True HD and 7.1 Channel Surround Sound Audio
- HDCP compliant
- No software or drivers required
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Specifications

Highlights

- Extend a 1080p @ 24Hz (or 1920 x 1200) HDMI signal up to 150 ft. from the source
- When extending a 1080p @ 24Hz (or 1920 x 1200) signal more than 75 ft., use cable made with 24Awg wiring, such as the P568-100-HD
- 24Awg HDMI cable is also needed when extending a 3D signal more than 50 ft.. A 3D signal can be extended up to 125 ft. using 24Awg HDMI cable
- Supports DTS-HD, Dolby True HD and 7.1 Channel Surround Sound Audio
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Package Includes

- B122-000 HDMI Signal Extender
- External Power Supply (Input: 100-240V, 50/60Hz, 0.5A Output: 5V, 0.5A)
- Owner's Manual



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

| General Info | |
|-------------------------------------|-------------------------|
| RoHS | Y |
| OVERVIEW | |
| Chromebook Compatible | Yes |
| Display Style | Signal Booster |
| Model Type | HDMI |
| Cable Types | CAT5/CAT5E |
| CONNECTIONS | |
| Connector A | HDMI (FEMALE) |
| Connector B | HDMI (FEMALE) |
| Number of Connectors | 2 |
| WARRANTY | |
| Product Warranty Period (Worldwide) | 1-year limited warranty |

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.