


LioN-Power Active I/O M12, 7/8" Power, EtherNet/IP, 16DO






Bit assignm	ient							
Bit	7	6	5	4	3	2	1	0
Output Data: 16D0								
Byte 0	4B	4A	3B	3A	2B	2A	1B	1A
Byte 1	8B	8A	7B	7A	6B	6A	5B	5A

Pin assignment		
M12 I/O port, A-coded	Power supply 7/8"	M12 EtherNet/IP, D-coded
$\begin{array}{c} 3 \\ 0 \\ 0 \\ 2 \\ 0 \\ 0 \\ 0 \\ 0 \\ 0 \\ 1 \\ 0 \\ 0 \\ 1 \\ 0 \\ 0$	$\begin{array}{c} 3 \\ 2 \\ 0 \\ 0 \\ 0 \\ 0 \\ 0 \\ 0 \\ 0 \\ 0 \\ 0$	3 4 1 = TD+ 2 = RD+ 3 = TD- 2 1 4 = RD-

Part number	Order number		
0980 ESL 312-111	934880002		





LioN-Power Active I/O M12, 7/8" Power, EtherNet/IP, 16DO

Technical Data			
Environmental Temperature	-20 °C to +70 °C (Operation)		
Housing Material	Metal Zinc Die-cast		
Contact Bearer	РА/ТРИ		
Contact	M12 A, D-coded CuSn, Gold-plated 7/8" CuZn, Gold-plated		
0-ring	FKM		
Mechanical Data			
Weight	520 g		
Protection Class (IEC 60529)	IP65, IP67 (only if mounted and locked in combination with Hirschmann/Lumberg connector)		
Module Supply			
Rated Voltage	24V DC		
Voltage Range	19 to 30V DC		
Nominal Current	9 A		
Connection Type	7/8" power connector, 5 poles		
Number	2		
Bus-System			
Network	EtherNet/IP		
Transmission Rate	10/100 Mbit/s		
Address Range	0 to 255		
Connection Type	M12 LAN connection, 4 poles, D-coded		
Number	2		
Outputs			
Number of Digital Channels	16		
Actoric Current	2 A per channel		
Actoric Current (max.)	9 A C		
Short-circuit Proof	yes		
Channel Type N.O.	p-switching		
Status Indicator	LED white or yellow per channel		
Diagnostic Indicator	LED red per port		

The application of these products in harsh environments should always be checked before use. Specifications subject to alteration.