

LC Duplex to SC Duplex Patch cord, 2 fibres, Zipcord Tight-Buffered cable, LSZH, 2.0 mm legs

50 µm ClearCurve® multimode (OM2), 15 m

CORNING

Patch cables are used for non-permanent connections between patch panels, transmission equipment, etc. Pre-assembled cables allow for the implementation of complete Plug & Play solutions. When such a solution is adopted with accurate dimensioning and appropriate cable routing, it is possible to install even large cabling systems rapidly.

Features and Benefits

Connectors

- LC Duplex connector according to TIA/EIA-604 -10, SC Duplex connector according to TIA/EIA-604 -10 -3
- All connectors are tested to FOTP -21.
- Connectors are pre-radius polished to provide the optimal end-face geometry for long-term performance.

Cable

Low smoke (IEC 61034) and zero-halogen (LSZH), flame retardant to IEC 60332-3-24 (C) and noncorrosive to IEC 60754-2 (FRNC)

Cables are metal free; hence, there are no ground-loop or potential-equalisation problems. Completely dry design (without gel)

Colour of outer sheath: OM1, OM2 – orange; OM3, OM4 – turquoise; OS2 – yellow



Part Number: 055702B5Z20015M

Standards

Intermateability TIA/EIA-604-10 / TIA/EIA-604-3

Specifications

General Specifications

Flame rating	LSZH™/FRNC
Cable assembly type	Two Fibre
Fibre Category	50 µm MM (OM2)

Temperature Range

Operation	-20 °C to 60 °C
Installation and assembly	-5 °C to 50 °C
Storage	-25 °C to 70 °C

LC Duplex to SC Duplex Patch cord, 2 fibres, Zipcord Tight-Buffered cable, LSZH, 2.0 mm legs

50 µm ClearCurve® multimode (OM2), 15 m

CORNING

Design - Connector A

Connector Type	LC Duplex
Ferrule Material	Ceramic
Polish	PC
Housing material	Composite
Housing Colour	black
Boot type	Individual
Boot colour	Black / White
Keyed (security)	No

Mechanical Specifications - Connector A

Durability	≤ 0.2 dB 500 rematings, FOTP-21
Tensile strength jacketed cable	44 N

Optical Specifications - Connector A

Insertion loss, typical	0.35 dB
Insertion loss, max.	0.5 dB

Design - Connector B

Connector Type	SC duplex
Ferrule Material	Ceramic
Polish	PC
Housing material	Composite
Housing Colour	black
Boot type	Individual
Boot colour	Black / White
Keyed (security)	No

Mechanical Specifications - Connector B

Durability	≤ 0.2 dB 1000 rematings, FOTP-21
Tensile strength jacketed cable	44 N

LC Duplex to SC Duplex Patch cord, 2 fibres, Zipcord Tight-Buffered cable, LSZH, 2.0 mm legs

50 µm ClearCurve® multimode (OM2), 15 m

CORNING

Optical Specifications - Connector B

Insertion loss, typical	0.35 dB
Insertion loss, max.	0.5 dB

Cable design

Fibre Count	2
Outer diameter	2 mm x 4.1 mm
Outer jacket colour	orange
Outer jacket material	LSZH™/FRNC
Minimum Bend Radius	10 mm
Crush resistance (reversible)	1000 N/10 cm
Tensile strength	300 N

Chemical Characteristics

RoHS	Free of hazardous substances according to RoHS 2002/95/EG
------	---

Ordering Information

Part Number	055702B5Z20015M
Product Description	LC Duplex to SC Duplex patch cord on 2-fibres Zipcord cable, with 2 mm legs, and a low-smoke, zero-halogen sheath. Length is variable.
EAN Code	4056418605869
Length	15 m
Weight	0.1345 kg

Shipping Information

Packing type	Cardboard box
Packing dimensions (L x W x H)	380 mm x 250 mm x 180 mm
Units Per Delivery	1/1

LC Duplex to SC Duplex Patch cord, 2 fibres, Zipcord Tight-Buffered cable, LSZH, 2.0 mm legs

50 µm ClearCurve® multimode (OM2), 15 m

CORNING

Notes



Corning Optical Communications LLC • PO Box 489 • Hickory, NC 28603-0489 USA

800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/opcomm

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/trademarks.
All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified.

© 2016 Corning Optical Communications. All rights reserved.