

ADAM-4541 ADAM-4542+ ADAM-4561/4562

Multi-mode Fiber Optic to RS-232/422/485 Converter
Single-mode Fiber Optic to RS-232/422/485 Converter
1-port Isolated USB to RS-232/422/485 Converter



ADAM-4541



ADAM-4542+



ADAM-4561/4562



Specifications

General

- **Power Input** Unregulated 10 ~ 30 V_{DC}
- **Connectors** 1 x plug-in terminal block (#14 ~ 22 AWG)
(RS-232/422/485)
2 x ST fiber connector
- **Power Consumption** 1.5 W @ 24 V_{DC}

Serial Communications

- **Communication Mode** Asynchronous
- **Speed Modes (bps)** 1,200, 2,400, 4,800, 9,600, 19.2 k, 38.4 k, 57.6 k, 115.2 k and RS-232/422 mode (switchable)
- **Transmission Mode** Full/half duplex, bidirectional

Fiber Optic Communications

- **Optical Power Budget (Attenuation)** 12.5 dB (measured with 62.5/125 μm)
- **Transmission Distance** 2.5 km
- **Transmission Mode** Multi mode (Send and Receive)
- **Wavelength** 820 nm

Specifications

General

- **Power Input** Unregulated 10 ~ 30 V_{DC}
- **Connectors** 1 x plug-in terminal block (#14 ~ 22 AWG)
(RS-232/422/485)
1 x SC fiber connector
- **Power Consumption** 3 W @ 24 V_{DC}

Serial Communications

- **Communication Mode** Asynchronous
- **Speed Modes (bps)** 1,200, 2,400, 4,800, 9,600, 19.2 k, 38.4 k, 57.6 k, 115.2 k and RS-232/422 mode (switchable)
- **Transmission Modes** Full/half duplex, bidirectional

Fiber Optic Communications

- **Optical Power Budget (Attenuation)** 15 dB
- **Transmission Distance** 15 km
- **Transmission Mode** Single mode (Send and Receive)
- **Wavelength** 1310 nm

Specifications

General

- **Connectors** Network: USB-type A connector (type A to type B cable provided)
Serial:
ADAM-4561 1 x plug-in terminal (#14 ~ 22 AWG) (3-wire RS-232/422/485)
ADAM-4562 1 x DB-9 serial connectors (9-wire RS-232)
- **Isolation Voltage** ADAM-4561: 3,000 V_{DC}
ADAM-4562: 2,500 V_{DC}
- **Power Consumption** ADAM-4561: 1.5 W @ 5 V
ADAM-4562: 1.1 W @ 5 V
- **Driver Support** Windows 98/2000/XP
- **Full Compliance with USB v1.1 specifications**

Serial Communications

- **Speed Modes (bps)** 75 bps to 115.2 kbps
- **Transmission Modes** Full/half duplex, bidirectional

Common Specifications

Environment

- **Humidity** 5 ~ 95% RH
- **Operating Temperature** ADAM-4541/4542+: -10 ~ 70° C (14 ~ 158° F)
ADAM-4561/4562: 0 ~ 70° C (32 ~ 158° F)
- **Storage Temperature** -25 ~ 85° C (-13 ~ 185° F)

Ordering Information

- **ADAM-4541** Multi-mode Fiber to RS-232/422/485 Converter
- **ADAM-4542+** Single-mode Fiber to RS-232/422/485 Converter
- **ADAM-4561** 1-port Isolated USB to RS-232/422/485 Converter
- **ADAM-4562** 1-port Isolated USB to RS-232 Converter