

Z-MAX™ 6A UTP PATCH PANELS

Z-MAX 6A UTP patch panels harness unprecedented performance and reliability in a high-density modular solution. These complete patch panel kits combine 19 inch patch panels with Z-MAX 6A panel outlets to offer the industry's highest performing category 6A patching solution.

The Z-MAX 6A UTP patch panels facilitate a world-class installation for data centers and telecommunications rooms by offering an attractive appearance combined with flexible labeling and color coding options.

The Z-MAX panel modules feature a patent pending angled IDC contact pattern to exploit the widest module cross-section to minimize alien crosstalk. This enables up to 48-ports in just 1U while still meeting strict category 6A AXT requirements. Panels are offered in flat and angled styles with fixed or removable rear cable managers.



PATENTED



Z-MAX™

MODULAR PATCHING

STANDARDS COMPLIANCE

- ANSI/TIA-568-C.2
- ISO/IEC 11801 Ed.2.2
- ETL Tested
- IEEE 802.3an
- IEEE 802.3af (PoE)
- IEEE 802.3at (PoE+)
- IEC 60603-7
- IEC 60603-7-41
- ANSI/TIA-1096-A

Additional space is provided for custom user labeling

High visibility snap-on magnifying label holders except either paper labels or Z-MAX icons for port identification


Lightweight, high strength steel with durable black finish

A quick-release lever allows individual modules to be easily removed even in high density applications

Panel outlets easily snap into place to accelerate installation

Bold port numbering enables quick identification of outlets

Rear cable manager ensures proper cable management practices for all installations, critical to category 6A performance



Panels are provided in complete kits which include the patch panel and Z-MAX panel outlets

Leverage the quick-snap design by combining Z-MAX trunk assemblies with empty Z-MAX patch panels

High density version provides 48 ports in just 1U to reduce valuable rack space consumption

PRODUCT INFORMATION

Performance Specification Chart:

MECHANICAL – PANEL	
Operating Temperature	-10 to 60 °C, (14 to 140 °F)
Flammability Rating	UL 94 V-0
Green Features	RoHS, lead-free, halogen-free, PVC free
Plastic Materials	Flame retardant themoplastic
Dimensions (LxWxH)	109.2 mmx 482.6mm x 44.2mm (4.30" x19.00" x1.74 ")
Mounting	CEA-310-E 19-inch (482.6mm) rack
Material – Panel	18 gauge cold rolled steel, black e-coat



MODULAR PATCHING

Fixed Ordering Information:

- Z6A-PNL(X)-24K.....Z-MAX 24-Port, CAT 6A UTP Patch Panel Kit, 1 RMS, Black, with Jacks
- Z6A-PNL(X)-U48K.....Z-MAX 48-Port, CAT 6A UTP Patch Panel Kit, 1 RMS, Black, with Jacks
- Z-PNL(X)-24E.....Z-MAX 24-Port UTP Patch Panel, 1RMS, Black, Empty
- Z-PNL(X)-U48E.....Z-MAX 48-Port UTP Patch Panel, 1RMS, Black, Empty

Panel Style
(Blank) - Flat
A - Angled

Removable Ordering Information

- Z6A-P(X)-24.....Z-MAX 24-Port, CAT 6A UTP Patch Panel with removable wire manager kit, 1 RMS, Black with Jacks
- Z6A-P(X)-48.....Z-MAX 48-Port, CAT 6A UTP Patch Panel with removable wire manager kit, 1 RMS, Black with Jacks
- Z-P(X)-24.....Z-MAX 24-Port, UTP Patch Panel with removable wire manager, 1RMS, Black, Empty
- Z-P(X)-48.....Z-MAX 48-Port, UTP Patch Panel with removable wire manager, 1RMS, Black, Empty

Panel Style
(F) - Flat
A - Angled

ZBL-01

Panels include Z-Tool, label / icon holders, designation labels, cable ties and mounting hardware.*

Note: 1U = 44.5mm (1.75 in.)

** included in panel kit only*

Because we continuously improve our products, Siemon reserves the right to change specifications and availability without prior notice. Z-MAX™ is a trademark of Siemon

For additional resource information:

Visit our web site at www.siemon.com

Panel Accessories

- Z-PNL-PL24.....Patch panel label sheet, numbered 1 to 24, bag of 100
- Z-PNL-PL48.....Patch panel label sheet, numbered 25 to 48, bag of 100
- Z-PNL-PS.....Patch panel label holder, bag of 25
- Z6A-P.....Z-MAX 6A UTP panel outlet
- Z-BL-01.....Z-MAX panel blank, bag of 10, black



Note: Z-MAX UTP panels are designed for use with Z-MAX UTP panel outlets only, for more information on panel outlets please reference outlet specifications sheet.

* Termination technique may vary. See product instructions for details

**Worldwide Headquarters
 North America**
 Watertown, CT USA
 Phone (1) 860 945 4200 US
 Phone (1) 888 425 6165

**Regional Headquarters
 EMEA**
 Europe/Middle East/Africa
 Surrey, England
 Phone (44) 0 1932 571771

**Regional Headquarters
 Asia/Pacific**
 Shanghai, P.R. China
 Phone (86) 21 5385 0303

**Regional Headquarters
 Latin America**
 Bogota, Colombia
 Phone (571) 657 1950