

Easy Pull Type-B Connectors (M/F set of DVI-Single-Link with Faceplate)

MODEL NUMBER: **EZB-DVIX-2**



Description

Easy Pull Connector Kit includes: 2 x DVI-D Single Link Male and Female 1 ft. pigtailed and 1 Wall Plate. Completes your Easy Pull trunk run with a finished appearance. Digital video support up to 1080p. Use with either PVC or Plenum digital trunk cables. Requires B120-000 signal booster.

Features

- Eliminates the need to field terminate DVI connectors
- Allows cable to be run according to code - inside conduit, drop ceilings, etc.
- Makes pulling long cables fast and easy
- Digital trunk cables available in 50 and 100 ft. lengths
- High quality digital cable supports resolutions up to 1080p
- Requires B120-000 signal booster

Specifications

OVERVIEW	
Intended Application	Connecting Devices
Display Style	Easy Pull
Model Type	DVI
Cable Type	CAT6
INPUT	
Cable Length (ft.)	1

Highlights

- DVI-D Connector Kit includes: 2 x DVI-D M/F Cable - 1 ft. Pigtail & Wall Plate
- Versatile trunk cable allows for a variety of connection
- High quality digital cable supports resolutions up to 1080p
- Requires B120-000 signal booster

Applications

- Use where standard DVI cables won't fit, such as conduit or confined wall or ceiling spaces

Package Includes

- 1 x DVI-D Female 1 ft. pigtail cable
- 1 x DVI-D Male 1 ft. pigtail cable
- 1 x Wall plate
- Requires B120-000 signal booster (not included)



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Cable Length (m)	0.30
UPC ASSIGNMENT	
Unit Carton UPC#	037332142856
CONNECTIONS	
Connector A	DVI-D SINGLE LINK (MALE)
Connector B	DVI-D SINGLE LINK (FEMALE)
Number of Connectors	2
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.