

Micro Environment Monitoring System / Remote Temperature/Humidity Sensor over IP

ENVIROMUX®

Monitor and manage environmental and security conditions over IP. Provides early warnings before critical events turn into disaster.

Environment Monitoring

- Temperature
- Humidity
- Water Leaks
- Air Flow
- Power
- Motion / Intrusion
- Vibration
- Smoke / Carbon Monoxide

Alert Notifications

- Email
- SNMP
- Web Page
- SMS

Key Features

- ENVIROMUX-MICRO-T
 - 1 integrated sensor – temperature
 - 2 RJ45 ports for external temperature/humidity sensors
 - 2 digital inputs sensitive to contact closure
 - Dual DC power provides dual redundancy.
- ENVIROMUX-MICRO-TRHP
 - 2 integrated sensors – temperature, humidity
 - 2 RJ45 ports for external temperature/humidity sensors
 - 2 digital inputs sensitive to contact closure
 - Built-in Power over Ethernet (POE) and dual DC power provides triple redundancy.
- Sensors are hot pluggable.
- Monitor (ping) up to 4 IP network devices – alerts are sent if devices are not responding.
- Sensor conditions can be configured to trigger alerts by themselves, and/or be used in combination with other alerts to trigger one Smart Alert.
- Supports 4 IP network video cameras for live view of any facility.
- Integrates with various Open Source SNMP monitoring packages.
 - The unit can be polled via SNMP.
- USB port for connecting USB modem.
- (Coming Soon) Optional intuitive graphical management software provides an easy-to-use, unified interface for both monitoring and configuring up to 3,000 ENVIROMUX units and all connected sensors.




ENVIROMUX-MICRO-T

- **Integrated temp-only or temp/humidity sensor, 2 temp/humidity ports, 2 digital inputs**
- **USB port for 3G modem**
- **Power over Ethernet option**

The ENVIROMUX® Micro Environment Monitoring System monitors critical environmental conditions, such as temperature, humidity, liquid water presence, power, intrusion, and smoke. When a sensor goes out of range of a configurable threshold, the system will notify you via email, web page, network management (SNMP), and/or SMS messages (via external USB 3G modem).

The system functions independently or as an IP-connected remote sensor for the ENVIROMUX-2D/5D/16D. The ENVIROMUX-MICRO-T features an integrated temperature sensor, two RJ45 sensor ports for external temperature/humidity sensors, and two dry contact inputs. The ENVIROMUX-MICRO-TRHP features an integrated temperature/humidity sensor, two RJ45 sensor ports for external temperature/humidity sensors, two dry contact inputs and built-in Power over Ethernet (PoE).



Micro Environment Monitoring System / Remote Temperature/Humidity Sensor over IP

ENVIROMUX®

**Monitor and manage environmental and security conditions over IP.
Provides early warnings before critical events turn into disaster.**

	ENVIROMUX-MICRO-T	ENVIROMUX-MICRO-TRHP
Integrated Sensors	1	2
Temperature	-4 to 167°F (-20 to 75°C) ±0.72°F at -14 to 167°F (±0.4°C at -10 to 75°C) ±0.9°F at -4 to 23°F (±0.5°C at -20 to 5°C)	-4 to 167°F (-20 to 75°C) ±0.72°F at -14 to 167°F (±0.4°C at -10 to 75°C) ±0.9°F at -4 to 23°F (±0.5°C at -20 to 5°C)
Humidity	N/A	0 to 80% relative humidity, ±2% 80 to 90% relative humidity, ±3%
RJ45 Sensor Ports	2 Compatible with: ENVIROMUX-T-E7, ENVIROMUX-T-IND-E7, ENVIROMUX-TRHM-E7	2 Compatible with: ENVIROMUX-T-E7, ENVIROMUX-T-IND-E7 ENVIROMUX-TRHM-E7
Digital Inputs – Screw Terminal Pairs	2	2
Alerts	5 Methods	5 Methods
Email	✓	✓
Web Page	✓	✓
SNMP traps (v1, v2c)	✓	✓
Syslog	✓	✓
SMS Messages	✓ – via external USB 3G modem (not included)	✓ – via external USB 3G modem (not included)
Smart Alerts	1	1
IP Cameras	✓ – up to 4 cameras	✓ – up to 4 cameras
Control Methods	3 Methods	3 Methods
Web Interface	✓	✓
Telnet Monitoring	✓	✓
SNMP Monitoring (v1, v2c)	✓	✓
USB Ports for Modem	1	1
Expandable (Coming Soon)	Up to 3,000 units via optional management software	Up to 3,000 units via optional management software
Flash Upgrade	✓	✓
Protocols Supported HTTP/HTTPS, SNMP V1/V2c, SMTP, TCP/IP, Syslog, SNTP, DHCP, SSLv3, AES 256-bit, 3DES, Blowfish, RSA, EDH-RSA, Arcfour	✓	✓
Restore Defaults Button	✓	✓
Operating & Storage Temperature	-4 to 167°F (-20 to 75°C)	-4 to 167°F (-20 to 75°C)
Operating & Storage Relative Humidity	0 to 99% non-condensing RH	0 to 99% non-condensing RH
Monitor (Ping) IP Devices	✓ – up to 4 network devices	✓ – up to 4 network devices
Power	Dual DC Power	Built-in Power-over-Ethernet (POE) Dual DC Power
	110 to 240 VAC at 50 or 60 Hz via AC adapter (Includes one country- specific AC adapter. The second AC adapter is sold separately.)	110 to 240 VAC at 50 or 60 Hz via AC adapter (Not included. Country-specific AC adapters sold separately – PWR-SPLY-EMICRO)
	5.5VDC ±5% input voltage	5.5VDC ±5% input voltage
MTBF	648,857 hours	628,394 hours
Dimensions WxDxH (in)	4x3.44x1.37	4x3.44x1.37
Mounting	Mounting holes to match rack hole spacing	Mounting holes to match rack hole spacing
Regulatory Approvals	CE, RoHS	CE, RoHS
Warranty	2 years	2 years