


Wyr-Grid® Overhead Cable Tray Routing System


specifications

The overhead cable tray routing system shall consist of pathway sections, splice connectors, sidewalls, waterfalls, mounting brackets, and accessories designed to route and manage copper, fiber optic, or power cables. The pathway sections shall be provided in five widths: 8" (203mm), 12" (305mm), 18" (457mm), 24" (610mm) and 30" (762mm). Optional snap-on sidewalls shall include 2" (50mm), 4" (102mm), and 6" (152mm) heights that can be hand installed at any location along pathway sections. Sidewall waterfalls and intersection bend radius parts shall provide 3" (76mm) bend radius protection. Trapeze, cantilever, and wall mount brackets shall be provided to support the system. Components shall be painted black or electro zinc plated.



technical information

Wire fill table:



X (in.)	Y (in.)	Internal Area (in. ²)	Category 6A Dia. 0.300" 7.6mm	Category 6 Dia. 0.240" 6.1mm	X (in.)	Y (in.)	Internal Area (in. ²)	Category 6A Dia. 0.300" 7.6mm	Category 6 Dia. 0.240" 6.1mm
12.2	2	24.3	172	269	24.2	2	48.3	342	534
	4	48.7	344	538		4	96.7	684	1069
	6	73.0	516	807		6	145.0	1026	1603
18.2	2	36.3	257	401	30.2	2	60.3	427	666
	4	72.7	514	804		4	120.7	854	1334
	6	109.0	771	1205		6	181.0	1280	2000

Material:

Black (BL): Pre-galvanized steel wire and galvanized cold rolled steel prior to paint
Pre-Galvanized (PG): Pre-galvanized steel wire and galvanized cold rolled steel prior to paint
Electro Zinc (EZ): Steel wire and cold rolled steel, electro zinc plated
ABS (Side Waterfall)
RoHS Compliant

Approvals:

UL Classified for their suitability for use as Equipment Grounding Conductor in accordance with Sections 392.3(C) and 392.7(B) of the NEC
Metal Cable Tray in accordance with CAN/CSA-C22.2 No.126.1-02
NEMA VE 1-2002 and ANSI/NFPA 70, "National Electric Code" (NEC)
Corrosion resistant per ASTM A653/A653M-08 and A641/A641M-09
EN61537:2007 Cable Tray Systems and Cable Ladder Systems for Cable Management
Black: Corrosion resistant per ASTM A653/A653M-08 and A641/A641M-09
Electro Zinc: ASTM B633 SC3, Type III

CSI spec form:

LP-CSISPEC-WG

key features and benefits

Strength to weight ratio

The design of the Wyr-Grid® Pathway Sections provides a greater strength to weight ratio than competitive wire basket; easier handling translates into faster installation

Grid pattern

The 4" x 5" wire mesh grid pattern allows greater amounts of cables and QuickNet® Cassettes to pass through grid openings without additional cutting, reducing installation time

No integral sidewalls

Less cutting on straight sections, no cutting at intersections and waterfalls reduces installation time

Snap-on sidewalls

Sidewalls can be attached where needed to retain cables within the Wyr-Grid® Pathway Sections providing greater configuration versatility

Bend radius control sidewalls

Protects cables at intersections and can be easily attached without cutting or fabrication

Bonding splice

A thread cutting screw pierces the paint of adjacent cable tray sections providing a completely bonded connection, ensuring electrical continuity between the sections

Snap-on waterfalls

Protects cables when transitioning down to equipment and can be easily attached without cutting or fabrication

applications

The Wyr-Grid® Overhead Cable Tray System is designed to route and manage copper data cables, fiber optic, or power cables within data centers, connected buildings, and industrial automation applications. Innovative features

provide quick, safe, and easy assembly for reduced installation costs and faster deployment. Can easily accommodate FiberRunner® Pathways into the application to provide a segregated copper and fiber cabling strategy.

www.panduit.com

PANDUIT®

SPECIFICATION SHEET

Wyr-Grid® Pathway Sections

8"W x 120"L:	WG8BL10
12"W x 120"L:	WG12**10
18"W x 120"L:	WG18**10
24"W x 120"L:	WG24**10
30"W x 120"L:	WG30**10

Splice Connectors

8", 12", and 18" splice:	WGSPL1218**
24" and 30" splice:	WGSPL2430**
Intersection splice:	WGINTSPL**
8", 12", and 18" splice with clip:	WGESPL**
24" and 30" splice with clip:	WGESPL2430**
Expansion splice:	WGEXS**

Snap-On Sidewalls

2" sidewall:	WGSW2**
4" sidewall:	WGSW4**
6" sidewall:	WGSW6**

Waterfalls

4" side waterfall:	WGSWF4BL
Bottom waterfall:	WGBTMWF**

Mounting Brackets

8" trapeze bracket:	WGTBS8**
12" trapeze bracket:	WGTBS12**
18" trapeze bracket:	WGTBS18**
24" trapeze bracket:	WGTBS24**
30" trapeze bracket:	WGTBS30**
12" cantilever bracket:	WGCBS12**
18" cantilever bracket:	WGCBS18**
24" cantilever bracket:	WGCBS24**

2 Post Channel Trapeze Rack

Mount Brackets

12" pathway:	WG2PRB12BL
18" pathway:	WG2PRB18BL
24" pathway:	WG2PRB24BL

12" wall bracket:	WGWMTB12**
18" - 30" wall bracket:	WGWMTB1830**
Strut bracket:	WGSK**

Vertical mounting bracket:

WGVWMBEZ

1200mm D cabinet direct mounting bracket:WGCMB1200BL

1070mm D cabinet direct mounting bracket:WGCMB1070BL

1200mm D cabinet mounting bracket: WGCMK1200BL

1070mm D cabinet mounting bracket: WGCMK1070BL

4 post rack mounting bracket: WGR4PK30

Intersection Bend Radius Control

2" high sidewall:	WGINTBRC2**
4" high sidewall:	WGINTBRC4**
6" high sidewall:	WGINTBRC6**

Tray Liner (Offered in PG only)

8" tray liner:	WGTL8PG
12" tray liner:	WGTL12PG
18" tray liner:	WGTL18PG
24" tray liner:	WGTL24PG
30" tray liner:	WGTL30PG

Divider Wall (Offered in PG only)


2" divider wall:	WGDW2PG
4" divider wall:	WGDW4PG
6" divider wall:	WGDW6PG

Accessories

Manual cutting tool:	WGCT-M
Hydraulic cutting tool:	WGCT-A
Hardware kit:	WGHRDWKT**

**Substitute BL = Black Powder Coat,
EZ = Electro Zinc Plated

Wyr-Grid® Overhead Cable Tray Routing System



Pathway Sections

8" Width: WG8BL10 (not shown)

- 1 12" Width: WG12BL10
- 2 18" Width: WG18BL10
- 3 24" Width: WG24BL10
- 4 30" Width: WG30BL10

Mounting Brackets

Trapeze Brackets

8" Wide: WGTBS8BL (not shown)
12" Wide: WGTBS12BL (not shown)

- 5 18" Wide: WGTBS18BL
- 6 24" Wide: WGTBS24BL
- 7 30" Wide: WGTBS30BL

Cantilever Brackets

- 8 12" Wide: WGCB12BL
- 18" Wide: WGCB18BL (not shown)
- 24" Wide: WGCB24BL (not shown)

Wall Mount Termination Brackets

- 8" Wide: WGWMTB8BL (not shown)
- 12" Wide: WGWMTB12BL (not shown)
- 9 18" – 30" Wide: WGWMTB1830BL

Splice Connectors

- 10 For 8", 12", and 18" Widths: WGSPL1218BL
- 11 For 24" and 30" Widths: WGSPL2430BL
- 12 Intersection Splice: WGINTSPLBL

Additional splice connectors are available. Refer to page 1.

Snap-On Sidewalls

- 2" Sidewall: WGSW2BL (not shown)
- 13 4" Sidewall: WGSW4BL
- 6" Sidewall: WGSW6BL

Waterfalls

- 14 4" Side Waterfall: WGSWF4BL
- 15 Bottom Waterfall: WGBTMWFB

Intersection Bend Radius Control

- 16 2" High Sidewall: WGINTBRC2BL
- 17 4" High Sidewall: WGINTBRC4BL
- 18 6" High Sidewall: WGINTBRC6BL

Accessories

- 19 Hardware Kit: WGHRDWKTBL

Tray Liner

- 8" Tray Liner: WTGL8PG (not shown)
- 12" Tray Liner: WTGL12PG (not shown)
- 18" Tray Liner: WTGL18PG (not shown)
- 24" Tray Liner: WTGL24PG (not shown)
- 20 30" Tray Liner: WTGL30PG

Divider Wall

- 2" Divider Wall: WGDW2PG (not shown)
- 21 4" Divider Wall: WGDW4PG
- 6" Divider Wall: WGDW6PG (not shown)

WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT CANADA
Markham, Ontario
cs-cdn@panduit.com
Phone: 800.777.3300

PANDUIT EUROPE LTD.
London, UK
cs-emea@panduit.com
Phone: 44.20.8601.7200

PANDUIT SINGAPORE PTE. LTD.
Republic of Singapore
cs-ap@panduit.com
Phone: 65.6305.7575

PANDUIT JAPAN
Tokyo, Japan
cs-japan@panduit.com
Phone: 81.3.6863.6000

PANDUIT LATIN AMERICA
Guadalajara, Mexico
cs-la@panduit.com
Phone: 52.33.3777.6000

PANDUIT AUSTRALIA PTY. LTD.
Victoria, Australia
cs-aus@panduit.com
Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to www.panduit.com/warranty

For more information

Visit us at www.panduit.com

Contact Customer Service by email: cs@panduit.com
or by phone: 800.777.3300

PANDUIT®

©2015 Panduit Corp.
ALL RIGHTS RESERVED.
FRSP13--WW-ENG
11/2015