

NetCommander 8-Port Cat5 Rack-Mount Console KVM Switch w/19-in. LCD

MODEL NUMBER: **B070-008-19**



Description

Tripp Lite's B070-008-19 NetCommander Rackmount Console KVM switch is a cost effective and highly flexible system for controlling up to 128 computers from a single 19" display console. This console can be cascaded with Tripp Lites stand-alone B072 NetCommander series KVM switches. Switching between attached servers can be accomplished via the On Screen Display (OSD) menu or Hotkey commands. Utilizing Tripp Lite's B078-101-Series server interface units, KVM cabling is kept to a minimum via inexpensive Cat5/5e/6 patch cables. Servers can be located up to 100 ft. away from the switch. Add Remote access over IP by connecting Tripp Lite [B051-000](#) Remote IP Access Unit.

Password feature provides additional security to prevent unauthorized access to attached computers. All rackmount hardware is included, and is designed for easy, one person installation. Fits into any rack from 27" to 42" deep. 2-post rackmounting available using Tripp Lite's B019-000. Compatible with all major operating systems. Constructed of heavy-duty steel housing. Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Features

- 8-port Cat5 KVM Switch with built-in 19" Monitor, Keyboard, and Mouse
- Supports resolutions up to 1366 x 768
- Connect and control up to 128 computers locally or remotely
- Standard EIA 19" rackmounting
- Use in racks from 27" to 42" deep
- OSD menu for intuitive operation and easy control
- USB and PS/2 mouse/keyboard support
- Password protection and auto-logout features
- Firmware upgradeable
- Hot-swappable: disconnect and reconnect USB computers w/o reboot
- Easy port selection via On Screen Display (OSD) or Hotkey commands

Highlights

- 8-port Cat5 KVM Switch with built-in 19" Monitor, Keyboard, and Mouse
- Expandable: Connect and control up to 128 computers
- Compatible with all major operating systems
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

System Requirements

- PS/2 or USB computer / server
- (1) [B078-101-PS2](#) (PS/2) or [B078-101-USB](#) (USB) Server Interface Unit is required for each connected computer/server
- Compatible with all major operating systems

Package Includes

- B070-008-19, 8-port Cat5 KVM 19" Console
- Power Cord
- Serial Firmware Upgrade Cable
- KVM/Console Jumper cable
- Owners manual CD



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

- Rugged ball bearing slides offer long life usage
- Uses readily available Cat5/5e/6 patch cables to locate computers up to 100 ft. from the KVM
- IP upgradeable using Tripp Lite [B051-000](#) IP Remote Unit
- Compatible with all major operating systems
- Constructed of heavy-duty steel housing
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Specifications

General Info	
RoHS	Y
OVERVIEW	
Users	1
Console	Yes
Port Control	Hotkeys, OSD
Max CPU	128
PC/Server Connections	PS/2
Cat5 KVM Switch	Yes
IP Remote Access	No
Style	1U Rackmount Console
INPUT	
Electrical Consumption	(Line Mode) 30W / (Standby Mode) 5W
Nominal Input Voltage Description	Internal Switching 100-240 VAC 50/60Hz
PHYSICAL	
Unit Dimensions (hwd / in.)	1.7" x 19" x 26.8"
Unit Dimensions (hwd / cm)	4.32 x 48.26 x 68.07
Unit Weight (lbs.)	36.0
Unit Weight (kg)	16.33
Color	Black
LCD Monitor (in.)	19
LCD Monitor (cm)	48.26
ENVIRONMENTAL	
Storage Temperature Range	-40F to 158F



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Relative Humidity	80% Non-condensing Relative Humidity
Operating Temperature	32F to 104F
BTUs	(Line Mode) 102 BTU/Hr / (Standby Mode) 17.06 BTU/Hr
CONNECTIONS	
Ports	8
Computer/Server Ports	8 x RJ45
Firmware Upgrade Port	RJ11
FEATURES & SPECIFICATIONS	
Autoscan (Y,N)	Y
Autoscan Duration	Variable
CERTIFICATIONS	
Certifications	UL 60950-1 (USA), CAN/CSA (Canada), FCC Part 15 Class A, CE, IEC 60950-1
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.