

14-Outlet Economy Network Server Surge Protector, 1U Rack-Mount, 15-ft. Cord, 3000 Joules

MODEL NUMBER: **DRS-1215**



Description

Tripp Lite's DRS-1215 offers surge and noise suppression in a versatile all-metal multi-mount cabinet.

Detachable mounting flanges are configurable for rackmount, wallmount and under-counter installation. Uses only 1 rack space (1U) when installed in any 19 inch EIA standard rack. Includes 14 outlets (6 front/8 rear), 15 ft AC power cord and guarded power switch to reduce the risk of accidental shutoff. Diagnostic LED indicates surge protection status.

PLUG/OUTLETS: Input: NEMA 5-15P/Output: 14 NEMA5-15R (6 front & 8 rear)

ELECTRICAL: 120V AC, 50/60Hz, 15A (Requires NEMA 5-15R wall receptacle)

SUPPRESSION: AC: 140V RMS Clamping/3000 joules

FORMAT: Supports 19 in. rackmount (uses 1 rack space/1U), wallmount, under-counter and more

Features

- Versatile all-metal cabinet with detachable mounting flanges allows rackmount, wallmount, undercounter and other creative mounting options
- Uses one rack space (1U) in standard 19 inch rack ("zero U" mounting possible in many racks)
- 3000 joules AC surge suppression with EMI/RFI filtering
- 14 NEMA 5-15R output receptacles (6 front/8 rear)
- 15 foot AC cord with NEMA 5-15P straight-in plug connection
- Diagnostic LED confirms suppressor operation
- Lighted power switch confirms power on/off status
- Snap-in switch guard prevents accidental turn off
- 15 amp capacity with circuit breaker
- 120V AC, 50/60Hz electrical compatibility

Specifications

Highlights

- 14 outlets / 15-ft. cord
- 3000 joule rating
- Adjustable rackmount hardware

Applications

- Ideal for protection of sensitive electronic equipment in 19 inch rackmount, wallmount and under-counter applications, such as internetworking equipment, PC systems, telecommunications, audio/video, security, sound reinforcement and more.

Package Includes

- DRS-1215 Surge Suppressor
- Warranty information
- Instruction manual



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

RoHS	Y
OVERVIEW	
Style	Rack-Mount
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(14) 5-15R
Output (Watts)	1800
Circuit Breaker (amps)	15
USB Charging	No
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Connection Type	NEMA 5-15P input plug
Input Cord Length (ft.)	15
Input Cord Length (m)	4.57
Voltage Compatibility (VAC)	120
Maximum Surge Amps	120000
USER INTERFACE, ALERTS & CONTROLS	
Switches	Power switch controls power to all outlets
Diagnostic LEDs	Green - Protection Present
Locking Switch Cover	Transparent locking switch cover prevents accidental shutoff
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	3000
AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
Clamping Voltage (RMS)	140
Safe Thermal Fusing	Prevents unsafe conditions during extreme extended over-voltages and catastrophic occurrences
UL1449 Let Through Rating	330V
EMI / RFI Filtering	40-80 dB
Immunity	Conforms to IEE 587 / ANSI C62.41
DATALINE SURGE SUPPRESSION	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Telephone/DSL Protection	No
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
PHYSICAL	
Shipping Dimensions (hwd / in.)	2.25 x 20.5 x 9.25
Shipping Dimensions (hwd / cm)	5.72 x 52.07 x 23.50
Shipping Weight (lbs.)	5.5
Shipping Weight (kg)	2.49
Unit Dimensions (hwd / in.)	1.75 x 17.5 x 4
Unit Dimensions (hwd / cm)	4.45 x 44.45 x 10.16
Unit Weight (lbs.)	4.6
Unit Weight (kg)	2.09
Material of Construction	Metal
Included Mounting Accessories	Included mounting flanges are pre-installed for 1U rackmount installation and can be re-configured to support a variety of mounting options
Housing Color	Black
Receptacle Color	Black
Color (AC Line Cord)	Black
Form Factors Supported	1U rackmount, 0U vertical rackmount, wallmount and under-counter mounting supported - detachable flanges can be re-configured to support a variety of additional mounting options
Outlets Measurement (Center to Center)	Distance between front outlets = 38.9mm; Distance between rear outlets = 38.9mm
SPECIAL FEATURES	
Right-Angle Plug	No
CERTIFICATIONS	
UL1449 3rd Edition (AC Suppression)	Tested to UL1449 3rd Edition by ETL
cUL / CSA (Canada)	Approved for Canada by ETL
Approvals	Exceeds IEEE 587 category A&B specifications
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty