

NOTES:


1. IDENTIFICATION: VERTICAL, MIXED (24) C-13 & (6) C-19 NETWORKED & ENVIRONMENTAL MONITORED 230/400V / 16A / THREE-PHASE WYE POU

<u>PART NO.</u>	<u>COLOR</u>
QN1D2Q0BA30P1	BLACK



2. ACCESSORY COMPONENTS:
 - (4) M6 x 20mm MOUNTING SCREWS
 - (4) #12-24 x 1/2" MOUNTING SCREWS
 - (2) #10-32 LOCKING COLLAR SCREWS
 - (2) L-BRACKETS
3. DIMENSIONS IN PARENTHESES ARE METRIC (mm).
4. POWER (A,V,PF,KWH) MONITORING AND ENVIRONMENTAL SENSOR DATA CAN BE ACCESSED REMOTELY VIA ETHERNET CONNECTION, LOCAL DISPLAY, OR OPTIONAL REMOTE DISPLAY (PVQ-RD).
5. UNIT COMPLIES WITH IEC 60950-1, EN55022, EN55024, AND IS CE MARKED.
6. RoHS COMPLIANT.
7. VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART.
8. MAXIMUM AVAILABLE INPUT POWER = 11 KW
9. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES.




TOOLLESS MOUNTING
BUTTON 2X




TOOLLESS MOUNTING BUTTON LOCATION




— 3 METER INLET POWER CORD



PLUG
16 AMP, 230/400V x 3~ WYE
4P/5W
IEC 60309, SPLASHPROOF





TWENTY-FOUR (24)
RECEPTACLES
10 AMP, 250V
STRAIGHT BLADE
IEC 60320/C13



SIX (6)
RECEPTACLES
16 AMP, 250V
STRAIGHT BLADE
IEC 60320/C19

01A	8-29-12	PIP	MRWA	A. UPDATED DETAIL A. B. ADDED BUTTON MOUNTING NOTE.	09V098KK				
00A	11-22-11	MRWA	KRKE	RELEASED TO PRODUCTION	09V098KK				
REV	DATE	BY	CHK	DESCRIPTION	ECN - R	CUST	SUP	OTH	

MODEL FILENAME		09V098KK/01.PRT	
CAD FILENAME/LAYERS		09V098KK_DC/01A.PRT	
 PANDUIT CORP TINLEY PARK, ILLINOIS			
VERTICAL, MIXED (24) C-13 & (6) C-19 NETWORKED & ENVIRONMENTAL MONITORED POWER OUTLET UNIT CUSTOMER DRAWING			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: INCHES +/- 0.03 X.X +/- 0.015 X.XXX +/- 0.005 [METRIC - MILLIMETER] X +/- 0.8 X.X +/- 0.4 X.XX +/- 0.13		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION	
DRAWN BY MRWA	MAT'L:	SCALE NONE	DWG  SIZE
DATE 11-22-11		DRAWING NO. 09V098KK	
CHK'D KRKE			