# MORPHOACCESS® SIGMA LITE SERIES

**SLIM AND POWERFUL FINGERPRINT ACCESS TERMINALS** 







- World's #1 fingerprint technology inside 1:10,000 user identification in 1 second
- High capacity 250,000 users (1:1), 10,000 users (1:N), 1 Million logs
- Anti-fraud features
   Fake finger detection, duress finger, timed anti-pass back
- Flexibility
  Prox®, iClass® or MIFARE®/DESFire®/NFC contactless card reader as an option
- Tough design Weather (IP65) and vandal (IK08) resistant



## MORPHOACCESS® SIGMA LITE SERIES

SLIM AND POWERFUL FINGERPRINT ACCESS TERMINALS

#### The SIGMA family welcomes new members!

Engineered with the same attention to detail and performance as their predecessor, the MorphoAccess® SIGMA Lite terminals are specifically designed to equip narrow mounting surfaces, such as glass/aluminum door mullions, turnstiles, or server rack doors.

With two designs and multiple card reader options, there are a variety of models to address the widest range of deployment scenarios, both indoors and outdoors.

#### World's #1 fingerprint technology inside —

- Latest generation Morpho embedded algorithms (MINEX and FIPS 201 approved)
- Up to 250,000 users in 1:1 verification mode
- Up to 10,000 users (30,000 templates) in 1:N identification mode
- 1:10,000 user matching in 1 second
- Accuracy maintained regardless of number of users in database
- FBI PIV IQS certified optical sensor

#### **Full set of card reader options**

- Prox®
- iClass®
- MIFARE®/MIFARE® Plus/DESFire®/NFC

N S S G A = THE RIGHT COMBINATION

> R Ε



ttachment to axis of axis

#### **MA SIGMA Lite**

With blue/green/red LED indicator and buzzer

(2.36'')



#### EMBEDDED WEB SERVER

- Enables on-device enrollment, terminal configuration and transaction log retrieval 0 m × m n Use with any device (PC, laptop, tablet,
  - Use with any OS (Windows, Android, Apple iOS)
  - Use with any web browser (Google Chrome, Mozilla Firefox, Safari, Internet Explorer)



#### **Enhanced interactivity** on MA SIGMA Lite+ touchscreen

- Time & Attendance In & Out function keys
- User ID, PIN and BioPIN<sup>(2)</sup> management
- Intuitive icons and live messages

#### **Anti-fraud features**

- Fake finger detection
- Duress finger

- Timed anti-pass back function(3)
- Banned/authorized user lists

## The SIGMA family







### MA SIGMA Lite+

Morpho

With 2.8" OVGA color touchscreen and buzzer

#### BUILT FOR THE REAL WORLD

WEATHER AND VANDAL(1) RESISTANT BY DESIGN







**COMPATIBLE WITH EXISTING INSTALLATIONS** 

### Morpho and bioscrypt°

- Using MorphoManager application or MIK SDK on a Morpho network
- Using SecureAdmin application or SecureSDK on a Bioscrypt network

- CPU: ARM® Cortex™-A9 core 1GHz
- Linux Operating System
- FBI PIV IQS certified optical fingerprint sensor
- Contactless reader options: Prox<sup>®</sup>, iClass<sup>®</sup>, MIFARE®/MIFARE® Plus/DESFire®/NFC
- Network/Communication:
- Ethernet, RS485, USB
- Wi-Fi option
- · Power supply:
- 12V-24V DC
- Power over Ethernet (PoE)

- Internal storage capacity: 512MB Flash, 512MB RAM
- 1:N mode: 3,000 user records, extendable to 10,000 with license (\*3 templates each, including 1 duress)
- 1:1 mode: 250,000 user IDs - 1 Million transaction logs
- Inputs/outputs: Wiegand In & Out (customizable up to 512 bits), Door Relay, 2 General Purpose Inputs (including Door monitoring), 2 General Purpose Outputs
- Tamper switches

- Operating conditions:
- Temperature: -20°C to 55°C (-4°F to 131°F)
- Humidity: 10% to 80% (non condensing)
- Ingress protection: IP65
- Mechanical impact protection: IK08<sup>(1)</sup>
- **HxWxD** = 156\*68\*62 mm (6.14\*2.68\*2.44 inches)
- Weight: 280 grams
- EMC/Safety standards: CE, CB, FCC
- RoHS, REACh and WEEE compliant

<sup>(1)</sup> IK08 rating is not available for MA SIGMA Lite+ design

<sup>&</sup>lt;sup>(2)</sup> Alternate password solution instead of fingerprints

<sup>(3)</sup> Prevents repeated authorizations by the same user, within a configurable time period

KEY MISSIONS, KEY TECHNOLOGIES, KEY TALENTS