






D10100DB/09



DETAIL A
(SCALE 4X)



PLUG
16 AMP, 250V, SINGLE-PHASE
2P/3W
IEC 60309, SPLASHPROOF

ONE (1)
RECEPTACLE
16 AMP, 250V
IEC 60309, SPASHPROOF

00A	5-14-13	MRWA	KRKE		RELEASED TO PRODUCTION	09V098TP	
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	

PANDUIT P/N	WEIGHT
LZ1D2A0FA0AJ1	10 lb (4.5 kg)

- NOTES:
- IDENTIFICATION: INLINE NETWORKED CURRENT MONITOR
230V / 16A / SINGLE PHASE POU
 - ACCESSORY COMPONENTS:
(4) M6 x 20mm MOUNTING SCREWS
(4) #12-24 x 1/2" MOUNTING SCREWS
 - DIMENSIONS IN PARENTHESES ARE METRIC (mm).
 - CURRENT METER - RED, 4-DIGIT LED DISPLAY PROVIDES TRUE RMS CURRENT THAT CONTINUOUSLY SCROLLS THROUGH THE THREE DIFFERENT MEASURED CIRCUITS. METER DISPLAYS CIRCUIT NAME FOLLOWED BY THE MEASURED CURRENT (E.G. CR-1 REPRESENTS PHASE 1). BREAKER/PHASE (X,Y,Z) LEVEL MONITORING CAN ALSO BE ACCESSED REMOTELY VIA ETHERNET CONNECTION.
 - UNIT COMPLIES WITH IEC 60950-1, EN55022, EN55024, AND IS CE MARKED.
 - RoHS COMPLIANT.
 - VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART.
 - INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES.

PART NO.	COLOR
LZ1D2A0FA0AJ1	BLACK

TITLE			
INLINE NETWORKED CURRENT MONITOR CUSTOMER DRAWING			
ITEM REVISION NAME		<div>PANDUIT</div> <div>TM</div>	
09V098TP/00.PRT			
DATASET FILE NAME		<div>MATERIAL:</div> <div></div> <div>DRAWING NUMBER:</div> <div>09V098TP</div>	
09V098TP_DC/00A.PRT			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:			
INCHES	METRIC - MILLIMETER	ANGLE	
X.X	X. +/- 0.03	X. +/- 0.8	
X.XX	X.X +/- 0.018	X.X +/- 0.46	
X.XXX	X.XX +/- 0.007	X.XX +/- 0.18	
<div></div>		THIRD ANGLE PROJECTION	
DRAWN BY	DATE	CHK	SCALE
MRWA	5-14-13	KRKE	NONE
SHT 1 OF 1		SIZE	
B			