


126-00069

Article Number: 126-00069

Wing Push Mount Tie, 6.0" Long, 50lb Tensile, PA66, Natural, 500/bag



Base Data

Local Order Number	126-00069
Type	T50SSFM
Color	Natural (NA)
Features and Benefits	• Wing design helps stabilize the tie in high vibration applications. • Includes a ladder type strap as opposed to a conventional serrated strap; giving the benefit of being extra flexible. • Wing design provides low insertion and high extraction force.
Product Description	Wing Push Mount Ties' supporting legs ensure a firm and secure fixing for bundles. These legs also reduce vibration in panel thickness enabling one part to suit many different applications such as sheet metal, wood, and cast iron.
Short Description	Wing Push Mount Tie, 6.0" Long, 50lb Tensile, PA66, Natural, 500/bag

Product Dimensions

Minimum Tensile Strength (Imperial)	50.0 lbs
Minimum Tensile Strength (Metric)	225 N
Length L (Imperial)	6.3 "
Length L (Metric)	160.0 mm
Fixation Method	Arrowhead
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Variant	Inside Serrated
Width W (Imperial)	0.18 "
Width W (Metric)	4.6 mm
Width W2 (Metric)	14.7 mm
Height H (Imperial)	0.2 "
Height H (Metric)	5.6 mm
Bundle Diameter Min. (Imperial)	0.06 "
Bundle Diameter Min. (Metric)	1.5 mm
Bundle Diameter Max. (Imperial)	1.4 "
Bundle Diameter Max. (Metric)	35.0 mm
Panel Thickness Max. (Imperial)	0.12 "
Panel Thickness Max. (Metric)	3.0 mm
Panel Thickness Min. (Imperial)	0.03 "
Panel Thickness Min. (Metric)	0.7 mm

Mounting Hole Diameter D (Metric)	6.0 - 6.6 mm
Mounting Hole Diameter D Max. (Metric)	6.6 mm
Mounting Hole Diameter D Min. (Metric)	6.0 mm

Logistics and Packaging

Quantity Per	bag
Package Quantity (Metric)	500
Carton Quantity	5000

Material and Specifications

Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
Flammability	UL94 V2
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
ROHS Compliant	Yes