

118-00111

Article Number: 118-00111

Outside Serrated Cable Tie, 7.9" Long, 50lb Tensile Strength, PA66HS, Black, 1000/pkg



Download drawing



Download spec sheet

Base Data

Local Order Number 118-00111

Type T50ROS

Color Black (BK)

- Features and Benefits
- Outside serrations minimize damage to cables, while still providing high tensile strength and low insertion force.
 - Contour style head design provides additional space in constrained areas.
 - Heat stabilized material provides excellent resistance to high heat exposures.

Product Description HellermannTyton outside serrated cable ties are designed with a smooth inside surface to help minimize indentation or damage to wire and cable insulation, while offering high tensile strength and low insertion force. The contour style head takes up less space than traditional style cable ties making it ideal for space constrained areas. For high volume applications, tensioning tools are available to ensure consistent and safe installation.

Short Description Outside Serrated Cable Tie, 7.9" Long, 50lb Tensile Strength, PA66HS, Black, 1000/pkg

Product Dimensions

Minimum Tensile Strength (Imperial) 50.0 lbs

Minimum Tensile Strength (Metric) 225.0 N

Length L (Imperial) 7.9 "

Length L (Metric) 200.0 mm

Fixation Method None

Identification Plate Position none

Releasable Closure No

Tie Closure plastic pawl

Variant Outside Serrated

Width W (Imperial) 0.18 "

Width W (Metric) 4.6 mm

Height H (Imperial) 0.05 "

Height H (Metric) 1.3 mm

Bundle Diameter Min. (Imperial) 0.06 "

Bundle Diameter Min. (Metric) 1.6 mm

Bundle Diameter Max. (Imperial) 2.0 "

Bundle Diameter Max. (Metric) 50.0 mm

Logistics and Packaging

Quantity Per bag

Package Quantity (Metric) 1000

Material and Specifications

Material	Polyamide 6.6 heat stabilized (PA66HS)
Material Shortcut	PA66HS
Flammability	UL94 V2
Halogenfree	Yes
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
ROHS Compliant	Yes