




T30L0HSM4




Article Number: 111-03341

High Temp Cable Tie, 7.8" Long, 30lb Tensile Strength, PA66HS, Black, 1000/pkg

 RoHS

 Download drawing

 Download spec sheet

Base Data

Local Order Number	T30L0HSM4
Type	T30L
Color	Black (BK)
Features and Benefits	<ul style="list-style-type: none"><li>• Heat stabilized cable ties provide excellent resistance to high heat exposures.</li><li>• Inside serrations allow for strong hold on cables and wire bundles.</li><li>• Head design provides high tensile strength with very low insertion force.</li><li>• Bent tail ensures a quick and simple installation.</li></ul>
Product Description	HellermannTyton high temperature cable ties are made of specially formulated materials providing various levels of temperature resistance and performance. The cable ties feature inside serrations providing a positive hold onto wire and cable bundles. The head design guarantees high tensile strength, as well as a low insertion force. The bent tail design allows quick and simple installations by hand. For high volume applications, tensioning tools are available to ensure consistent and safe installation.
Short Description	High Temp Cable Tie, 7.8" Long, 30lb Tensile Strength, PA66HS, Black, 1000/pkg

Product Dimensions

Minimum Tensile Strength (Imperial)	30.0 lbs
Minimum Tensile Strength (Metric)	135.0 N
Length L (Imperial)	7.8 "
Length L (Metric)	198.0 mm
Fixation Method	None
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Variant	Inside Serrated
Width W (Imperial)	0.14 "
Width W (Metric)	3.6 mm
Bundle Diameter Min. (Imperial)	0.06 "
Bundle Diameter Min. (Metric)	1.5 mm
Bundle Diameter Max. (Imperial)	2.0 "
Bundle Diameter Max. (Metric)	50.0 mm

Logistics and Packaging

Quantity Per	bag
Package Quantity (Metric)	1000
Carton Quantity	5000

Material and Specifications

---

Material	Polyamide 6.6 heat stabilized (PA66HS)
Material Shortcut	PA66HS
Flammability	UL94 V2
Halogenfree	Yes
Operating Temperature	-40°F to +257°F (-40°C to +125°C)
ROHS Compliant	Yes
Certification/Specification	UL-ZODZ2.E64139 VG U48/04103
UL Listed (US and Canada)	Yes
UL Recognized (US and Canada)	Yes