




4763214/10 | 7504 BLUE CPK

UltraMedia® 7504 ETL Verified Category 6e U/UTP Cable, plenum, blue jacket, 4 pair count, 1000 ft (305 m) length CommPak

Cross Section Drawing



Construction Materials

Jacket Material	PVC
Conductor Material	Bare copper
Insulation Material	FEP Polyolefin
Separator Material	FEP

Dimensions

Cable Length	305 m 1000 ft
Cable Weight	28.52 lb/kft
Diameter Over Jacket	5.664 mm 0.223 in
Jacket Thickness	0.483 mm 0.019 in

Electrical Specifications

ANSI/TIA Category	6
Characteristic Impedance	100 ohm
dc Resistance Unbalance, maximum	5 %
dc Resistance, maximum	6.66 ohms/100 m
Delay Skew, maximum	45 ns
Mutual Capacitance	5.4 nF/100 m @ 1 kHz
Nominal Velocity of Propagation (NVP)	74 %
Operating Frequency, maximum	400 MHz
Transmission Standards	ANSI/TIA-568-C.2 CENELEC EN 50288-6-1 ISO/IEC 11801 Class E
Safety Voltage Rating	300 V
Dielectric Strength, minimum	1500 Vac 2500 Vdc
Note	All electrical transmission tests include swept frequency measurements

Environmental Specifications

Environmental Space	Plenum
Flame Test Method	CMP
Installation Temperature	0 °C to +60 °C (+32 °F to +140 °F)
Operating Temperature	-20 °C to +60 °C (-4 °F to +140 °F)
Smoke Test Method	CMP
UL Temperature Rating	75 °C 167 °F

General Specifications

Cable Type	U/UTP (unshielded)
Pairs, quantity	4
Cable Component Type	Horizontal
Packaging Type	CommPak® box
Brand	UltraMedia® Uniprise®
Jacket Color	Blue
Product Number	7504
Conductor Gauge, singles	23 AWG
Conductor Type, singles	Solid

Product Specifications



4763214/10 | 7504 BLUE CPK

Conductors, quantity 8
Separator Type Isolator

Mechanical Specifications

Pulling Tension, maximum 11 kg | 25 lb

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system



Electrical Performance

CS CommScope
 Std Refers to the standard value listed under Transmission Standards in the Electrical Specifications above
 Typ Typical
 IL Insertion Loss (dB/100m)
 NEXT Near End Crosstalk (dB/100m)
 ACR Attenuation to Crosstalk Ratio (dB/100m)
 PSNEXT Power Sum Near End Crosstalk (db/100m)
 PSACR Power Sum Attenuation to Crosstalk Ratio (dB/100m)
 ACRF Attenuation to Crosstalk Ratio - Far End (dB/100m)
 PSACRF Power Sum Attenuation to Crosstalk Ratio - Far End (dB/100m)
 RL Return Loss (dB)
 TCL Transverse Conversion Loss (dB/100m)
 ELTCTL Equal Level Transverse Conversion Transfer Loss (dB/100m)

Freq. MHz	IL			NEXT			ACR			PSNEXT			PSACR			ACRF			PSACRF			RL			TCL		ELTCTL	
	CS	Std	Typ	CS	Std	Typ	CS	Std	Typ	CS	Std	Typ	CS	Std	Typ	CS	Std	Typ	CS	Std	Typ	CS	Std	Typ	CS	Std	CS	Std
1	2.0	2.0	2.1	77.3	74.3	92.6	75.3	72.3	90.5	75.3	72.3	90.7	73.3	70.3	88.6	68.8	67.8	85.1	65.8	64.8	83.8	20.0	20.0	34.5	40.0	40.0	35.0	35.0
4	3.8	3.8	3.9	68.3	65.3	85.0	64.5	61.5	81.1	66.3	63.3	82.9	62.5	59.5	79.0	56.8	55.8	73.3	53.8	52.8	72.1	23.6	23.0	33.1	40.0	40.0	23.0	23.0
8	5.3	5.3	5.3	63.8	60.8	80.8	58.5	55.4	75.5	61.8	58.8	78.7	56.5	53.4	73.3	50.7	49.7	67.5	47.7	46.7	66.3	25.4	24.5	34.4	40.0	40.0	16.9	16.9
10	5.9	6.0	6.0	62.3	59.3	79.2	56.4	53.3	73.2	60.3	57.3	77.1	54.4	51.3	71.1	48.8	47.8	65.5	45.8	44.8	64.3	26.0	25.0	35.7	40.0	40.0	15.0	15.0
16	7.5	7.6	7.5	59.2	56.2	76.3	51.7	48.7	68.8	57.2	54.2	74.0	49.7	46.7	66.5	44.7	43.7	61.5	41.7	40.7	60.2	26.0	25.0	35.7	38.0	38.0	10.9	10.9
20	8.4	8.5	8.4	57.8	54.8	74.6	49.4	46.3	66.2	55.8	52.8	72.4	47.4	44.3	64.1	42.8	41.8	59.6	39.8	38.8	58.3	26.0	25.0	37.0	37.0	37.0	9.0	9.0
25	9.4	9.5	9.4	56.3	53.3	73.0	46.9	43.8	63.7	54.3	51.3	70.9	44.9	41.8	61.5	40.8	39.8	57.6	37.8	36.8	56.3	25.3	24.3	38.1	36.0	36.0	7.0	7.0
31.25	10.6	10.7	10.5	54.9	51.9	71.7	44.3	41.2	61.2	52.9	49.9	69.6	42.3	39.2	59.1	38.9	37.9	55.6	35.9	34.9	54.3	24.6	23.6	38.2	35.1	35.1		
62.5	15.3	15.4	14.9	50.4	47.4	66.2	35.1	32.0	51.3	48.4	45.4	64.1	33.1	30.0	49.2	32.9	31.9	49.3	29.9	28.9	48.1	22.5	21.5	36.6	32.0	32.0		
100	19.7	19.8	19.0	47.3	44.3	63.5	27.6	24.5	44.5	45.3	42.3	61.3	25.6	22.5	42.4	28.8	27.8	44.9	25.8	24.8	43.8	21.1	20.1	33.6	30.0	30.0		
155	25.0	25.2	23.9	44.4	41.4	61.3	19.5	16.3	37.4	42.4	39.4	58.8	17.5	14.3	35.0	25.0	24.0	40.8	22.0	21.0	39.7	19.8	18.8	32.0	28.1	28.1		
200	28.8	29.0	27.3	42.8	39.8	58.9	14.0	10.8	31.6	40.8	37.8	56.9	12.0	8.8	29.6	22.8	21.8	38.6	19.8	18.8	37.5	19.0	18.0	31.1	27.0	27.0		
250	32.6	32.8	30.7	41.3	38.3	56.8	8.7	5.5	26.1	39.3	36.3	54.8	6.7	3.5	24.1	20.8	19.8	36.6	17.8	16.8	35.5	18.3	17.3	30.6	26.0	26.0		
300	36.2		33.9	40.1		55.4	4.0		21.5	38.1		53.5	2.0		19.6	19.3		34.8	16.3		33.7	17.8		30.7				
350	39.5		36.8	39.1		54.3	-0.4		17.5	37.1		52.3	-2.4		15.5	17.9		33.4	14.9		32.1	17.3		31.1				
400	42.7		39.4	38.3		53.0	-4.4		13.5	36.3		51.1	-6.4		11.6	16.8		32.1	13.8		30.8	16.9		32.5				
500			44.7			50.7			6.0			48.7			4.0			28.9			27.6			33.8				
550			44.9			50.9			6.0			48.8			3.9			28.7			27.3			33.6				
650			51.5			47.0			-4.4			45.0			-6.4			24.4			22.9			26.2				