

This specification is OBSOLETE

8219304/10 | 5782 BKRL 2-RG6 QD 1000

Dual RG 6 Type Quad Shield Non-Plenum Satellite Coaxial Cable, black jacket, 1000 ft (305 m) reel**OBSOLETE****This product was discontinued on: June 30, 2015****Construction Materials**

Construction Type	Non-armored
Center Conductor Material	Bare copper
Dielectric Material	Foam PE
Inner Shield (Braid) Coverage	60 %
Inner Shield (Braid) Gauge	34 AWG
Inner Shield (Braid) Material	Aluminum
Inner Shield (Tape) Material	Aluminum/Poly, bonded
Outer Shield (Braid) Coverage	40 %
Outer Shield (Braid) Gauge	34 AWG
Outer Shield (Braid) Material	Aluminum
Outer Shield (Tape) Material	Aluminum/Poly, non-bonded
Jacket Material	PVC

Dimensions

Cable Length	305 m 1000 ft
Cable Weight	70.00 lb/kft
Diameter Over Center Conductor	1.0236 mm per 1 strand 0.0403 in per 1 strand
Diameter Over Dielectric	4.5720 mm 0.1800 in
Diameter Over Dielectric Tolerance	±0.004 in
Diameter Over Jacket	7.620 mm 0.300 in
Diameter Over Jacket Tolerance	±0.008 in
Overall Cable Width	16.002 mm 0.630 in
Diameter Over Inner Shield (Braid)	5.385 mm 0.212 in
Diameter Over Outer Shield (Braid)	5.893 mm 0.232 in

Dimensions, Coaxial

Diameter Over Jacket	7.620 mm 0.300 in
Diameter Over Jacket Tolerance	±0.008 in
Jacket Thickness	0.762 mm 0.030 in

Electrical Specifications

Capacitance	52.5 pF/m 16.0 pF/ft
-------------	------------------------

8219304/10 | 5782 BKRL 2-RG6 QD 1000

Characteristic Impedance	75 ohm
Characteristic Impedance Tolerance	±3 ohm
Conductor dc Resistance	6.50 ohms/kft
Dielectric Strength, conductor to shield	2500 Vdc
Jacket Spark Test Voltage	4000 Vac
Nominal Velocity of Propagation (NVP)	82 %
Shield dc Resistance	4.90 ohms/kft
Structural Return Loss	15 dB @ 1000–3000 MHz 20 dB @ 5–1000 MHz
Structural Return Loss Test Method	100% Swept Tested

Environmental Specifications

Environmental Space	Non-plenum
Flame Test Method	CMG
Operating Temperature	-40 °C to +75 °C (-40 °F to +167 °F)
Safety Standard	cETL ETL
UL Temperature Rating	75 °C 167 °F

General Specifications

Cable Type	Series 6
Jacket Color	Black
Product Number	5782
Center Conductor Gauge	18 AWG
Center Conductor Type	Solid
Packaging Type	Reel

Mechanical Specifications

Minimum Bend Radius, loaded	20 times
Minimum Bend Radius, unloaded	10 times

Electrical Performance

Frequency	Attenuation (dB/100 m)	Attenuation (dB/100 ft)
1 MHz	0.82	0.25
10 MHz	2.16	0.66
50 MHz	4.62	1.41
100 MHz	6.30	1.92
200 MHz	8.66	2.64
400 MHz	12.23	3.73
700 MHz	16.56	5.05
900 MHz	18.99	5.79
1000 MHz	20.04	6.11
1200 MHz	22.07	6.73
1450 MHz	24.57	7.49
1800 MHz	27.65	8.43
2200 MHz	30.67	9.35
2500 MHz	32.70	9.97
3000 MHz	35.82	10.92

Regulatory Compliance/Certifications

Product Specifications



8219304/10 | 5782 BKRL 2-RG6 QD 1000

Agency

RoHS 2011/65/EU
ISO 9001:2008

Classification

Compliant
Designed, manufactured and/or distributed under this quality management system

