

OXYLUBE Spray

Inorganic dry film coating of molybdenum disulphide in aerosol form

Product Overview

ROCOL® OXYLUBE Spray provides a very high content molybdenum disulphide film.

It is designed to lubricate sliding mechanisms such as plain bearings, pins, cams and slides particularly in oxygen or vacuum environments.

ROCOL OXYLUBE Spray is also suitable for applications where contamination by aggressive chemicals or petroleum based solvents, oils and greases would destroy conventional lubricants.

Typical Applications

ROCOL OXYLUBE Spray is ideal for use as an assembly and dry film lubricant for sliding mechanisms, plain bearings, valve seats etc.

Features and Benefits

- Temperature range of applied film -200°C to +450°C.
- Dry film lubrication – resists pick up of contaminants.
- Inorganic resin bonded - suitable for oxygen and vacuum environments.
- Prevents galling, pick-up and seizure.
- Resistant to high loads (up to 7,000 kg/cm²).
- Excellent wear resistance (high molybdenum disulphide content).

Directions for Storage and Use

- Ensure surfaces to be treated are clean, dry and free from oil, grease or dirt contamination.
- Shake aerosol thoroughly for 2-3 mins after agitator ball begins to rattle.
- Hold upright and apply a thin even coating from approx distance of 10-15 cm (4-6 inches).
- Use only in well ventilated areas.
- After use, invert the can and spray until nozzle is clear.
- Film will be touch dry in 2-3 mins, leave at least 10-15 mins for complete cure @ 20°C.
- The cured film can be improved by lightly burnishing with a lint free cloth.
- The storage temperature should be kept below +50°C, and the storage area should be out of direct sunlight.
- Shelf life is 4 years from date of manufacture.

Specifications

- Rolls Royce Specification – R-R OMAT 4/54
- Naval Cat No.:
 - 0475-224-1963
- NATO Stock No.:
 - 9150-99-224-1963

Pack Sizes

Pack size	Part Code
400ml	10125

OXYLUBE Spray

Inorganic dry film coating of molybdenum disulphide in aerosol form

Property	Result
Appearance	Thin dark grey film
Solids	Molybdenum disulphide
Binder	Inorganic resin
Solvent	Hydrocarbon
Propellant	LPG (Hydrocarbon)
Drying Times:	
Touch dry	2-3 mins
Complete cure (20°C)	Approximately 10-15 mins
Temperature Range of applied film (for best performance apply at ambient temperature)	-200°C to +450°C

Values quoted above are typical and do not constitute a specification.

Safety Data Sheets

Safety data sheets are available for download from our website www.ocol.com or may be obtained from your usual ROCOL contact.

The information in this publication is based on our experience and reports from customers. There are many factors outside our control or knowledge which affect the use and performance of our products, for which reason it is given without responsibility.

Issue: 2 Date: 07-15

T +44 (0) 113 232 2600
F +44 (0) 113 232 2740
E customer-service@ocol.com
www.ocol.com

ROCOL House, Swillington, Leeds LS26 8BS

Registered Company No. 559693 VAT No. 742 0531 67

Registered Office: Admiral House, St Leonard's Road, Windsor, Berkshire SL4 3BL

ROCOL A division of **ITW** Ltd

