

# Technical Data



Performance you can trust

## Foliac Graphited P.J.C

**Setting pipe sealant for metallic threaded and flanged joints  
Primarily for High Pressure Steam, Air & Water**

### Features

- Temperature range  $-20^{\circ}\text{C}$  to  $450^{\circ}\text{C}$
- Suitable for pressures up to 1400 psi (97 bar)
- Pressure test after a minimum 24 hours
- Sets semi-hard but flexible
- Resists vibration and thermal expansion
- Easy to break and clean joints

### Directions for Use

- Do not apply in sub-zero temperatures
- Ensure surfaces are clean and free of contaminants. Apply by brush
- Assemble within 5 minutes
- Pressure test after a minimum of 24 hours at ambient ( $20-25^{\circ}\text{C}$ )
- Lower temperatures will extend drying time

T +44 (0) 113 232 2600  
F +44 (0) 113 232 2740  
E [customer-service@rocol.com](mailto:customer-service@rocol.com)  
[www.rocol.com](http://www.rocol.com)

ROCOL House, Swillington, Leeds LS26 8BS

Registered Company No. 559693 VAT No. 742 0531 67  
Registered Office: Admiral House, St Leonard's Road, Windsor, Berkshire SL4 3BL

ROCOL A division of  Ltd



BS EN ISO 9001  
Certificate No. RM 12448



BS EN ISO 14001  
Certificate No. EMS 67596



OHSAS 18001  
Certificate No. OHS 78173



INVESTOR IN PEOPLE

The information in this publication is based on our experience and reports from customers.  
There are many factors outside our control or knowledge which affect the use and performance  
of our products, for which reason it is given without responsibility.

# Technical Data

**ROCOL**<sup>®</sup>

Performance you can trust

## Foliac Graphited P.J.C

<b>Appearance</b>	Grey compound
<b>Unworked penetration at 25<sup>0</sup>C</b>	260 - 310
<b>Base type</b>	Vegetable oil
<b>Solids</b>	Graphite
<b>Temperature range</b>	-20 <sup>0</sup> C to 450 <sup>0</sup> C
<b>Pressure</b>	Up to 1400 psi (97 bar)
<b>Suitable applications</b>	Steam Air Water
<b>Storage</b>	Storage temperature should be controlled to between 1 and 40 °C.
<b>Pack sizes</b>	375g

T +44 (0) 113 232 2600  
F +44 (0) 113 232 2740  
E [customer-service@rocol.com](mailto:customer-service@rocol.com)  
[www.rocol.com](http://www.rocol.com)

ROCOL House, Swillington, Leeds LS26 8BS

Registered Company No. 559693 VAT No. 742 0531 67

Registered Office: Admiral House, St Leonard's Road, Windsor, Berkshire SL4 3BL

ROCOL A division of **ITW** Ltd



BS EN ISO 9001  
Certificate No. RM 12448



BS EN ISO 14001  
Certificate No. EMS 67596



OHSAAS 18001  
Certificate No. OHS 78173



INVESTOR IN PEOPLE

The information in this publication is based on our experience and reports from customers.  
There are many factors outside our control or knowledge which affect the use and performance  
of our products, for which reason it is given without responsibility.