

170-03045



Article Number: 170-03045

Expandable Braided Sleeving, 1.25" Dia., Black, 250.0 ft/Bulk Reel

 RoHS

 Download drawing

 Download spec sheet

Base Data

Local Order Number	170-03045
Type	BSP1140B
Color	Black (BK)
Features and Benefits	• Weave construction adjusts to twisting and flexing without creating wrinkles or bends. • Durable construction offers excellent abrasion and cut-through resistance as well as inertness to most chemicals and fungus. • Color options available to provide easy visual and safety identification of critical wiring components. • Expands to 150% of nominal diameter for fast, easy installation.
Product Description	General purpose expandable braided sleeving provides flexible abrasion protection for wire bundles and hoses.
Short Description	Expandable Braided Sleeving, 1.25" Dia., Black, 250.0 ft/Bulk Reel

Product Dimensions

Length L (Imperial)	250.0 ft
Length L (Metric)	76.2 m
Reel Length (imperial)	250.0 ft
Bundle Diameter Min. (Imperial)	0.75 "
Bundle Diameter Min. (Metric)	19.1 mm
Bundle Diameter Max. (Imperial)	1.75 "
Bundle Diameter Max. (Metric)	44.5 mm
Nominal Diameter (Imperial)	1-1/4 "
Nominal Diameter (Metric)	31.8 mm

Logistics and Packaging

Quantity Per	reel
Package Quantity	250 ft
Package Quantity (Metric)	250.0 ft
Weight (imperial)	4.0 lbs
Weight (Metric)	1.82 kg

Material and Specifications

Material	Polyester (PET)
Material Shortcut	PET
Flammability	FAR 25 FMVSS 302 UL94 V0

Halogenfree Yes

Operating Temperature -94°F to +257°F (-70°C to +125°C)

ROHS Compliant Yes

UL Recognized (US and Canada) Yes