



170-03058



Article Number: 170-03058

Resin Coated Fiberglass Sleeve, 0.25" Dia., Black, 50.0 ft/Standard Reel

 RoHS

 Download drawing

 Download spec sheet

Base Data

Local Order Number	170-03058
Type	BSHTFG140
Color	Black (BK)
Features and Benefits	<ul style="list-style-type: none"><li>• An extremely tough sleeving material which provides thermal protection up to 1,200°F.</li><li>• Sturdy construction maintains its tight structure under extreme shaking, scraping, pressure and varying temperature conditions.</li><li>• Cuts easily with ordinary scissors for easy application.</li><li>• UL VW-1 flammability rating for use in conditions requiring a very high degree of flame resistance.</li></ul>
Product Description	An extremely high-temperature resistant sleeving designed to protect wires and cables subjected to continuous temperature variations, vibration, abrasion, and mechanical stress.
Short Description	Resin Coated Fiberglass Sleeve, 0.25" Dia., Black, 50.0 ft/Standard Reel

Product Dimensions

Length L (Imperial)	50.0 ft
Length L (Metric)	15.2 m
Reel Length (imperial)	50.0 ft
Bundle Diameter Max. (Imperial)	0.375 "
Bundle Diameter Max. (Metric)	9.5 mm
Nominal Diameter (Imperial)	1/4 "
Nominal Diameter (Metric)	6.4 mm

Logistics and Packaging

Package Quantity	50 ft
Weight (Metric)	0.45 kg
Weight (imperial)	1.0 lbs

Material and Specifications

Material	Glass Fiber (GF)
Operating Temperature	-94°F to +1202°F (-70°C to +650°C)
ROHS Compliant	Yes
UL Recognized (US)	Yes

