

SSB-1900/NBDrop Ceiling Adjustable Load Support,
without 1900 Box**GENERAL DESCRIPTION**

The SSB-1900/NB is a rust resistant steel, adjustable, load bearing support without an electrical junction box.

INTENDED USE - Indoor or Protected Outdoor Environment


Installation	Parallel to floor plane in a suspended ceiling structure; maximum span of 24" in one dimension.
---------------------	---

JUNCTION BOX ACCESS

All 4 Vertical Sides	2x 1/2" k/o conduit 1x 1/2" / 3/4" eccentric k/o conduit
Top Horizontal Surface	3 x 1/2" k/o conduit 2x 1/2" / 3/4" eccentric k/o conduit

MECHANICAL ATTACHMENT

Bottom Horizontal	2x 8-32 formed threads to attach 2-gang Surface adapter plate if required
Tie-Offs	4x Total, 1 each at end of bridge rail 2x Terminal plate



Recommended construction sequences, installation instructions, and A&E Specifications are available in various formats in the QUAM Architects' and Engineers' Resources section on the web at:
www.QuamSpeakers.com

© 2013 Quam-Nichols Company reserves the right to make changes and/or improvements to its products at any time and without notice.



QUAM-NICHOLS COMPANY, INC.
234 East Marquette Rd.
Chicago, IL. 60637
Tel: 1-800-NEED-NOW (800-633-3669)
Fax: 1-888-NEED-NOW (888-633-3669)
e-mail: NeedNow@QNC.com
www.QuamSpeakers.com