

170-03061



**Article Number:** 170-03061

**Resin Coated Fiberglass Sleeving, 1.0" Dia., Black, 25.0 ft/Standard Reel**

 **RoHS**

 [Download drawing](#)

 [Download spec sheet](#)

Base Data

<b>Local Order Number</b>	170-03061
<b>Type</b>	BSHTFG100
<b>Color</b>	Black (BK)
<b>Features and Benefits</b>	<ul style="list-style-type: none"><li>• An extremely tough sleeving material which provides thermal protection up to 1,200°F.</li><li>• Sturdy construction maintains its tight structure under extreme shaking, scraping, pressure and varying temperature conditions.</li><li>• Cuts easily with ordinary scissors for easy application.</li><li>• UL VW-1 flammability rating for use in conditions requiring a very high degree of flame resistance.</li></ul>
<b>Product Description</b>	An extremely high-temperature resistant sleeving designed to protect wires and cables subjected to continuous temperature variations, vibration, abrasion, and mechanical stress.
<b>Short Description</b>	Resin Coated Fiberglass Sleeving, 1.0" Dia., Black, 25.0 ft/Standard Reel

Product Dimensions

<b>Length L (Imperial)</b>	25.0 ft
<b>Length L (Metric)</b>	7.62 m
<b>Reel Length (imperial)</b>	25.0 ft
<b>Bundle Diameter Max. (Imperial)</b>	1.625 "
<b>Bundle Diameter Max. (Metric)</b>	41.3 mm
<b>Nominal Diameter (Imperial)</b>	1 "
<b>Nominal Diameter (Metric)</b>	25.4 mm

Logistics and Packaging

<b>Quantity Per</b>	reel
<b>Package Quantity</b>	25 ft
<b>Weight (Metric)</b>	1.2 kg
<b>Weight (imperial)</b>	2.61 lbs

Material and Specifications

<b>Material</b>	Glass Fiber (GF)
<b>Operating Temperature</b>	-94°F to +1202°F (-70°C to +650°C)
<b>ROHS Compliant</b>	Yes
<b>UL Recognized (US)</b>	Yes

