

170-03145



Article Number: 170-03145

Flame Retardant Expandable Braided Sleeving, 1.25" ID, Black, 75.0 ft/Bulk Reel



Download drawing



Download spec sheet

Base Data

Local Order Number 170-03145

Type BSSWFR1140B

Color Black (BK)

Features and Benefits

- Split wrap design installs quickly, saving assembly time and future accessibility without disassembly.
- Unique construction retains shape and rigidity throughout unrolling.
- Easy open design allows quick assembly, future access, and ability to apply protective sleeving post assembly or post installation situations.

Product Description A lateral split, semi-rigid and flame retardant braided sleeving configuration used when ease of installation and repeat access to wire bundle is required. The lateral split allows the sleeving to open and accommodate a variety of bundling requirements. The 25% edge overlap rolls back over connectors and splices without exposing the bundled wires.

Short Description Flame Retardant Expandable Braided Sleeving, 1.25" ID, Black, 75.0 ft/Bulk Reel

Product Dimensions

Length L (Imperial) 75.0 ft

Length L (Metric) 22.9 m

Reel Length (imperial) 75.0 ft

Bundle Diameter Max. (Imperial) 1.25 "

Bundle Diameter Max. (Metric) 31.8 mm

Nominal Diameter (Imperial) 1-1/4 "

Nominal Diameter (Metric) 31.8 mm

Logistics and Packaging

Quantity Per reel

Package Quantity 75 ft

Package Quantity (Metric) 75.0 ft

Weight (Metric) 0.82 kg

Weight (imperial) 1.8 lbs

Material and Specifications

Material Polyester (PET)

Material Shortcut PET

Flammability FAR 25
VW-1

Operating Temperature -94°F to +257°F (-70°C to +125°C)

ROHS Compliant Yes

UL Recognized (US) Yes

UL Recognized (US and Canada) Yes