


FFSU06SD Modular Connectors - FX ULTRA FRAME



For more Information
please call

1-800-Belden1



General Description:

FX ULTRA FRAME, OS2, 06 PORTS, SC DUPLEX, BLUE ADAPTERS

Usage (Overall)

Suitable Applications:	FiberExpress Ultra Solutions, Backbone, Telecommunications Room, Main Distribution Room, Data Centers
Related Parts:	FiberExpress Ultra Patch panels, Pre-terminated MPO low loss cable assemblies

Physical Characteristics (Connectivity)

Capacity

Dimensions

Dimensions:

Height (in.)	Width (in.)	Depth (in.)
1.500	4.460	2.200

Materials

Materials:

Description	Type	Material	Color
Frame		Plastic - UL94V-0	Black
Front Connector Body	SC-Duplex	Plastic - UL94V-0	Blue
Adapter Sleeve		Phosphor Bronze	

Included Parts

Included Parts:	Dust caps
-----------------	-----------

Packaging

Packaging:	Individually packaged in a plastic shell, Shipped in cardboard box (60/box)
------------	---

Mechanical Characteristics (Connectivity)

Footprint/Type:	1 inch Pullout
-----------------	----------------

Termination Interface:

Termination	Connection	Durabilities
Front	Mated Connection	500 cycles
Rear	Mated Connection	500 cycles

Cable/Connector Retention:	11.250 lbs.
----------------------------	-------------

Connector/Hardware Retention:	11.250 lbs.
-------------------------------	-------------

Storage Temperature Range:	-40°C To +75°C
----------------------------	----------------

Operating Temperature Range:	-10°C To +60°C
------------------------------	----------------

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	07/01/2006
MII Order #39 (China RoHS):	EUP 50
Telecommunications Standards:	TIA/EIA-604-3, TIA-455-21

Suitability

Suitability - Indoor:	Yes
-----------------------	-----

Transmission Characteristics (Connectivity)

Notes (Overall)

Product Family

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
FFSU06SD	1 EA	0.030 LB			FXU FRAME OS2 06P

Revision Number: 0 Revision Date: 12-17-2014

© 2015 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein. All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.