

SAFETY DATA SHEET

Dow Corning C60

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1 Product identifier

Product name : Dow Corning C60

Product code : Dow Corning C60

1.2 Relevant identified uses of the substance or mixture and uses advised against

Material uses : Sealants and adhesives

1.3 Details of the supplier of the safety data sheet

Sherwin Williams Diversified Brands Limited
Western Wood Way
Langage Science Park
Plympton
Plymouth
PL7 5BG

National contact

Sherwin Williams Diversified Brands Limited
Western Wood Way
Langage Science Park
Plympton
Plymouth
PL7 5BG

e-mail address of person responsible for this SDS : technical@geocel.co.uk

1.4 Emergency telephone number

National advisory body/Poison Centre

Telephone number : National Poisons Information Service +44 844 892 0111 / 112

Supplier

Telephone number : 01752 202060 (09:00 - 17:00)

SECTION 2: Hazards identification

2.1 Classification of the substance or mixture

Product definition : Mixture

Classification according to Regulation (EC) No. 1272/2008 [CLP/GHS]

The product is not classified as hazardous according to Regulation (EC) 1272/2008 as amended.

Ingredients of unknown toxicity : Percentage of the mixture consisting of ingredient(s) of unknown toxicity: 95.3%

Ingredients of unknown ecotoxicity : Percentage of the mixture consisting of ingredient(s) of unknown hazards to the aquatic environment: 95.3%

Classification according to Directive 1999/45/EC [DPD]

The product is not classified as dangerous according to Directive 1999/45/EC and its amendments.

Classification : Not classified.

See Section 16 for the full text of the R phrases or H statements declared above.

See Section 11 for more detailed information on health effects and symptoms.

2.2 Label elements

Signal word : No signal word.

Hazard statements : No known significant effects or critical hazards.

Precautionary statements

General : Read label before use. Keep out of reach of children. If medical advice is needed, have product container or label at hand.

Prevention : Not applicable.

SECTION 2: Hazards identification

Response	: Not applicable.
Storage	: Not applicable.
Disposal	: Not applicable.
Supplemental label elements	: Not applicable.
Annex XVII - Restrictions on the manufacture, placing on the market and use of certain dangerous substances, mixtures and articles	: Not applicable.
Special packaging requirements	
Containers to be fitted with child-resistant fastenings	: Not applicable.
Tactile warning of danger	: Not applicable.

2.3 Other hazards

Other hazards which do not result in classification	: None known.
--	---------------

SECTION 3: Composition/information on ingredients**3.2 Mixture :**

There are no ingredients present which, within the current knowledge of the supplier and in the concentrations applicable, are classified as hazardous to health or the environment, are PBTs or vPvBs or have been assigned a workplace exposure limit and hence require reporting in this section.

SECTION 4: First aid measures**4.1 Description of first aid measures**

General	: In all cases of doubt, or when symptoms persist, seek medical attention. Never give anything by mouth to an unconscious person. If unconscious, place in recovery position and seek medical advice.
Eye contact	: Check for and remove any contact lenses. Immediately flush eyes with running water for at least 15 minutes, keeping eyelids open. Seek immediate medical attention.
Inhalation	: Remove to fresh air. Keep person warm and at rest. If not breathing, if breathing is irregular or if respiratory arrest occurs, provide artificial respiration or oxygen by trained personnel.
Skin contact	: Remove contaminated clothing and shoes. Wash skin thoroughly with soap and water or use recognised skin cleanser. Do NOT use solvents or thinners.
Ingestion	: If swallowed, seek medical advice immediately and show the container or label. Keep person warm and at rest. Do NOT induce vomiting. If swallowed, rinse mouth with water (only if the person is conscious). Get immediate medical attention.
Protection of first-aiders	: No action shall be taken involving any personal risk or without suitable training.

4.2 Most important symptoms and effects, both acute and delayed

There are no data available on the mixture itself.

If splashed in the eyes, the liquid may cause irritation and reversible damage.

This takes into account, where known, delayed and immediate effects and also chronic effects of components from short-term and long-term exposure by oral, inhalation and dermal routes of exposure and eye contact.

4.3 Indication of any immediate medical attention and special treatment needed

SECTION 4: First aid measures

- Notes to physician** : Treat symptomatically. Contact poison treatment specialist immediately if large quantities have been ingested or inhaled.
- Specific treatments** : No specific treatment.

See toxicological information (Section 11)

SECTION 5: Firefighting measures**5.1 Extinguishing media**

- Suitable extinguishing media** : Recommended: alcohol-resistant foam, carbon dioxide, powders.
- Unsuitable extinguishing media** : Do not use water jet.

5.2 Special hazards arising from the substance or mixture

- Hazards from the substance or mixture** : Fire will produce dense black smoke. Exposure to decomposition products may cause a health hazard.
- : Fire will produce dense black smoke. Exposure to decomposition products may cause a health hazard.
- Hazardous thermal decomposition products** : Decomposition products may include the following materials: carbon monoxide, carbon dioxide, smoke, oxides of nitrogen.
- Appropriate breathing apparatus may be required.

5.3 Advice for firefighters

- Special protective actions for fire-fighters** : Cool closed containers exposed to fire with water. Do not release runoff from fire to drains or watercourses.
- Special protective equipment for fire-fighters** : Fire-fighters should wear positive pressure self-contained breathing apparatus (SCBA) and full turnout gear.

SECTION 6: Accidental release measures**6.1 Personal precautions, protective equipment and emergency procedures**

- For non-emergency personnel** : Avoid breathing vapour or mist. Refer to protective measures listed in sections 7 and 8.
- : Keep unnecessary and unprotected personnel from entering.
- For emergency responders** : If specialised clothing is required to deal with the spillage, take note of any information in Section 8 on suitable and unsuitable materials. See also the information in "For non-emergency personnel".

6.2 Environmental precautions

- : Do not allow to enter drains or watercourses. If the product contaminates lakes, rivers, or sewers, inform the appropriate authorities in accordance with local regulations.

6.3 Methods and material for containment and cleaning up

- : Contain and collect spillage with non-combustible, absorbent material e.g. sand, earth, vermiculite or diatomaceous earth and place in container for disposal according to local regulations (see Section 13). Preferably clean with a detergent. Avoid using solvents.

6.4 Reference to other sections

- : See Section 1 for emergency contact information.
See Section 8 for information on appropriate personal protective equipment.
See Section 13 for additional waste treatment information.

SECTION 7: Handling and storage

The information in this section contains generic advice and guidance. The list of Identified Uses in Section 1 should be consulted for any available use-specific information provided in the Exposure Scenario(s).

7.1 Precautions for safe handling : Avoid contact with skin and eyes. Avoid inhalation of vapour, spray or mist. Eating, drinking and smoking should be prohibited in areas where this material is handled, stored and processed. Put on appropriate personal protective equipment (see Section 8). Never use pressure to empty. Container is not a pressure vessel. Always keep in containers made from the same material as the original one. Comply with the health and safety at work laws. Do not allow to enter drains or watercourses.

7.2 Conditions for safe storage, including any incompatibilities : Store in accordance with local regulations.
Notes on joint storage
 Keep away from: oxidising agents, strong alkalis, strong acids.
Additional information on storage conditions
 Store in a dry, cool and well-ventilated area. Keep container tightly closed. No smoking. Prevent unauthorised access. Containers that have been opened must be carefully resealed and kept upright to prevent leakage.

Contaminated absorbent material may pose the same hazard as the spilt product.

7.3 Specific end use(s)

Recommendations : Not available.

Industrial sector specific solutions : Not available.

Good housekeeping standards, regular safe removal of waste materials will minimise the risks of spontaneous combustion and other fire hazards.

Before use of this material please refer to the Exposure Scenario(s) if attached for the specific end use, control measures and additional PPE considerations.

SECTION 8: Exposure controls/personal protection

The information in this section contains generic advice and guidance. The list of Identified Uses in Section 1 should be consulted for any available use-specific information provided in the Exposure Scenario(s).

8.1 Control parameters

Occupational exposure limits

No exposure limit value known.

Recommended monitoring procedures : If this product contains ingredients with exposure limits, personal, workplace atmosphere or biological monitoring may be required to determine the effectiveness of the ventilation or other control measures and/or the necessity to use respiratory protective equipment. Reference should be made to monitoring standards, such as the following: European Standard EN 689 (Workplace atmospheres - Guidance for the assessment of exposure by inhalation to chemical agents for comparison with limit values and measurement strategy) European Standard EN 14042 (Workplace atmospheres - Guide for the application and use of procedures for the assessment of exposure to chemical and biological agents) European Standard EN 482 (Workplace atmospheres - General requirements for the performance of procedures for the measurement of chemical agents) Reference to national guidance documents for methods for the determination of hazardous substances will also be required.

DNELs/DMELs

No DNELs/DMELs available.

PNECs

No PNECs available

SECTION 8: Exposure controls/personal protection

8.2 Exposure controls

- Appropriate engineering controls** : Provide adequate ventilation. Where reasonably practicable, this should be achieved by the use of local exhaust ventilation and good general extraction.
- : Users are advised to consider national Occupational Exposure Limits or other equivalent values.

Individual protection measures

- Hygiene measures** : Wash hands, forearms and face thoroughly after handling chemical products, before eating, smoking and using the lavatory and at the end of the working period. Appropriate techniques should be used to remove potentially contaminated clothing. Wash contaminated clothing before reusing. Ensure that eyewash stations and safety showers are close to the workstation location.

- Eye/face protection** : Use safety eyewear designed to protect against splash of liquids.

Skin protection

Hand protection

Gloves

- : Wear suitable gloves tested to EN374.
- : Short Term Exposure less than 10 minutes Continuous use Nitrile gloves.
Long Term Exposure Spill / For prolonged or repeated handling, use PE / PE Laminated gloves > 8 hours (breakthrough time) .
- There is no one glove material or combination of materials that will give unlimited resistance to any individual or combination of chemicals.
The breakthrough time must be greater than the end use time of the product.
The instructions and information provided by the glove manufacturer on use, storage, maintenance and replacement must be followed.
Gloves should be replaced regularly and if there is any sign of damage to the glove material.
Always ensure that gloves are free from defects and that they are stored and used correctly.
The performance or effectiveness of the glove may be reduced by physical/chemical damage and poor maintenance.
Barrier creams may help to protect the exposed areas of the skin but should not be applied once exposure has occurred.
The user must check that the final choice of type of glove selected for handling this product is the most appropriate and takes into account the particular conditions of use, as included in the user's risk assessment.

Body protection

- : Personnel should wear protective clothing.
- : Personal protective equipment for the body should be selected based on the task being performed and the risks involved and should be approved by a specialist before handling this product.

Other skin protection

- : Appropriate footwear and any additional skin protection measures should be selected based on the task being performed and the risks involved and should be approved by a specialist before handling this product.

Respiratory protection

- : Approved/certified respirator with organic vapour cartridge. Filter type: A2P2 (EN14387).

Environmental exposure controls

- : Do not allow to enter drains or watercourses.

Before use of this material please refer to the Exposure Scenario(s) if attached for the specific end use, control measures and additional PPE considerations.

SECTION 9: Physical and chemical properties

9.1 Information on basic physical and chemical properties

Appearance

- Physical state** : Liquid. [Paste.]
- Colour** : Various
- Odour** : Sweetish.
- Odour threshold** : Not Available (Not Tested).
- pH** : Not Available (Not Tested).
- Melting point/freezing point** : Not Available (Not Tested).

SECTION 9: Physical and chemical properties

Initial boiling point and boiling range	: Not Available (Not Tested).
Flash point	: Closed cup: >93.3°C
Evaporation rate	: Slower than Ether Phase
Flammability (solid, gas)	: Not Available (Not Tested).
Burning time	: Not Available (Not Tested).
Burning rate	: Not Available (Not Tested).
Upper/lower flammability or explosive limits	: Testing not technically possible.
Vapour pressure	: Testing not technically possible.
Vapour density	: Testing not technically possible.
Relative density	: Not Available (Not Tested).
Solubility(ies)	: Not Available (Not Tested).
Solubility in water	: Not Available (Not Tested).
Partition coefficient: n-octanol/ water	: Not Available (Not Tested).
Auto-ignition temperature	: Not Available (Not Tested).
Decomposition temperature	: Not Available (Not Tested).
Viscosity	: Not Available (Not Tested).
Explosive properties	: Not Available (Not Tested).
Oxidising properties	: Under normal conditions of storage and use, hazardous reactions will not occur.

9.2 Other information**SECTION 10: Stability and reactivity**

10.1 Reactivity	: No specific test data related to reactivity available for this product or its ingredients.
10.2 Chemical stability	: Stable under recommended storage and handling conditions (see Section 7).
10.3 Possibility of hazardous reactions	: Under normal conditions of storage and use, hazardous reactions will not occur.
10.4 Conditions to avoid	: When exposed to high temperatures may produce hazardous decomposition products.
10.5 Incompatible materials	: Keep away from the following materials to prevent strong exothermic reactions: oxidising agents, strong alkalis, strong acids.
10.6 Hazardous decomposition products	: Under normal conditions of storage and use, hazardous decomposition products should not be produced.

Refer to Section 7: HANDLING AND STORAGE and Section 8: EXPOSURE CONTROLS/PERSONAL PROTECTION for additional handling information and protection of employees.

SECTION 11: Toxicological information**11.1 Information on toxicological effects**

There are no data available on the mixture itself.

If splashed in the eyes, the liquid may cause irritation and reversible damage.

This takes into account, where known, delayed and immediate effects and also chronic effects of components from short-term and long-term exposure by oral, inhalation and dermal routes of exposure and eye contact.

Acute toxicity

Product/ingredient name	Result	Species	Dose	Exposure
No data available				

SECTION 11: Toxicological information**Acute toxicity estimates**

No data available

Irritation/Corrosion

No data available

Sensitisation

No data available

Mutagenicity

No data available

Carcinogenicity

No data available

Reproductive toxicity

No data available

Teratogenicity

No data available

Specific target organ toxicity (single exposure)

Product/ingredient name	Category	Route of exposure	Target organs
No data available			

Specific target organ toxicity (repeated exposure)

Product/ingredient name	Category	Route of exposure	Target organs
No data available			

Aspiration hazard

Product/ingredient name	Result
No data available	

Other information : Not available.**SECTION 12: Ecological information****12.1 Toxicity**

There are no data available on the mixture itself.
Do not allow to enter drains or watercourses.

The mixture has been assessed following the conventional method of the Dangerous Preparations Directive 1999/45/EC and is not classified as dangerous for the environment.

12.2 Persistence and degradability

Product/ingredient name	Test	Result	Dose	Inoculum
No data available				

Product/ingredient name	Aquatic half-life	Photolysis	Biodegradability
No data available			

12.3 Bioaccumulative potential

Product/ingredient name	LogP _{ow}	BCF	Potential
No data available			

SECTION 12: Ecological information**12.4 Mobility in soil**

Soil/water partition coefficient (K_{oc}) : Not available.

Mobility : Not available.

12.5 Results of PBT and vPvB assessment

PBT : Not applicable.

vPvB : Not applicable.

12.6 Other adverse effects : No known significant effects or critical hazards.

: Avoid dispersal of spilt material and runoff and contact with soil, waterways, drains and sewers.

SECTION 13: Disposal considerations

The information in this section contains generic advice and guidance. The list of Identified Uses in Section 1 should be consulted for any available use-specific information provided in the Exposure Scenario(s).

13.1 Waste treatment methods**Product**

Methods of disposal : The generation of waste should be avoided or minimised wherever possible. Disposal of this product, solutions and any by-products should at all times comply with the requirements of environmental protection and waste disposal legislation and any regional local authority requirements. Dispose of surplus and non-recyclable products via a licensed waste disposal contractor. Waste should not be disposed of untreated to the sewer unless fully compliant with the requirements of all authorities with jurisdiction.

Hazardous waste : No.

Disposal considerations : Do not allow to enter drains or watercourses. Dispose of according to all federal, state and local applicable regulations. If this product is mixed with other wastes, the original waste product code may no longer apply and the appropriate code should be assigned. For further information, contact your local waste authority.

European waste catalogue (EWC)

The European Waste Catalogue classification of this product, when disposed of as waste, is:

Waste code	Waste designation
08 04 10	waste adhesives and sealants other than those mentioned in 08 04 09

Packaging

Methods of disposal : The generation of waste should be avoided or minimised wherever possible. Waste packaging should be recycled. Incineration or landfill should only be considered when recycling is not feasible.

Disposal considerations : Using information provided in this safety data sheet, advice should be obtained from the relevant waste authority on the classification of empty containers. Empty containers must be scrapped or reconditioned. Dispose of containers contaminated by the product in accordance with local or national legal provisions.

European waste catalogue (EWC) Contaminated packaging : Recycling possible. Ensure packaging is completely empty before recycling. Dispose of uncured residues in the same way as the product itself. Plastic articles 15 01 02 - metallic packaging 15 01 04 - mixed packaging 15 01 06.

Special precautions : This material and its container must be disposed of in a safe way. Empty containers or liners may retain some product residues. Avoid dispersal of spilt material and runoff and contact with soil, waterways, drains and sewers.

SECTION 14: Transport information

	ADR/RID	IMDG	IATA
14.1 UN number	Not regulated.	Not regulated.	Not regulated.
14.2 UN proper shipping name	-	-	-
14.3 Transport Hazard Class(es)/ Label(s)	-	-	-
14.4 Packing group	-	-	-
14.5 Environmental hazards	No.	No.	No.
Additional information	-	-	-

This mixture is not classified as dangerous according to international transport regulations (ADR/RID, IMDG, ICAO/IATA).

Do not carry by air without prior consent of the airline

14.6 Special precautions for user : **Transport within user's premises:** always transport in closed containers that are upright and secure. Ensure that persons transporting the product know what to do in the event of an accident or spillage.

14.7 Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code : Not available.

Multi-modal shipping descriptions are provided for informational purposes and do not consider container sizes. The presence of a shipping description for a particular mode of transport (sea, air, etc.), does not indicate that the product is packaged suitably for that mode of transport. All packaging must be reviewed for suitability prior to shipment, and compliance with the applicable regulations is the sole responsibility of the person offering the product for transport. People loading and unloading dangerous goods must be trained on all of the risks deriving from the substances and on all actions in case of emergency situations.

SECTION 15: Regulatory information

15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

EU Regulation (EC) No. 1907/2006 (REACH)**Annex XIV - List of substances subject to authorisation****Annex XIV**

None of the components are listed.

Substances of very high concern

None of the components are listed.

Annex XVII - Restrictions : Not applicable.

*on the manufacture,
placing on the market
and use of certain
dangerous substances,
mixtures and articles*

Other EU regulations

SECTION 15: Regulatory information

Seveso II Directive : This product is not controlled under the Seveso II Directive.

15.2 Chemical Safety Assessment : This product contains substances for which Chemical Safety Assessments are still required.

SECTION 16: Other information

✔ Indicates information that has changed from previously issued version.

Abbreviations and acronyms : ATE = Acute Toxicity Estimate
 CLP = Classification, Labelling and Packaging Regulation [Regulation (EC) No. 1272/2008]
 DMEL = Derived Minimal Effect Level
 DNEL = Derived No Effect Level
 EUH statement = CLP-specific Hazard statement
 PBT = Persistent, Bioaccumulative and Toxic
 PNEC = Predicted No Effect Concentration
 RRN = REACH Registration Number
 vPvB = Very Persistent and Very Bioaccumulative

Hazard pictograms :

Signal word : No signal word.

Hazard statements : No known significant effects or critical hazards.

Procedure used to derive the classification according to Regulation (EC) No. 1272/2008 [CLP/GHS]

Classification	Justification
Not classified.	

Full text of abbreviated H statements : Not applicable.

Full text of classifications [CLP/GHS] : Not applicable.

Full text of abbreviated R phrases : Not applicable.

Full text of classifications [DSD/DPD] : Not applicable.

Date of printing : 27, Oct, 2014.

Date of issue/ Date of revision : 27, Oct, 2014.

Date of previous issue : No previous validation.
 : If there is no previous validation date please contact your supplier for more information.

Version : 1

Notice to reader

It is recommended that each customer or recipient of this Safety Data Sheet (SDS) study it carefully and consult resources, as necessary or appropriate, to become aware of and understand the data contained in this SDS and any hazards associated with the product. This information is provided in good faith and believed to be accurate as of the effective date herein. However, no warranty, express or implied, is given. The information presented here applies only to the product as shipped. The addition of any material can change the composition, hazards and risks of the product. Regulatory requirements are subject to change and may differ between various locations and jurisdictions. The customer/buyer/user is responsible to ensure that his activities comply with all country, federal, state, provincial or local laws. The conditions for use of the product are not under the control of the manufacturer; the customer/buyer/user is responsible to determine the conditions necessary for the safe use of this product. The customer/buyer/user should not use the product for any purpose other than the purpose shown in the applicable section of this SDS without first referring to the supplier and obtaining written handling instructions. Due to the proliferation of sources for information such as manufacturer-specific SDS, the manufacturer cannot be responsible for SDSs obtained from any other source.