

553-50040



Article Number: 553-50040

Heat Shrink Label, 1.0" 1-Slit Single Sided, Polyolefin, White, 500/BX

 RoHS



[Download spec sheet](#)

Base Data

Local Order Number	553-50040
Type	HST24-8WH-S
Color	White (WH)
Features and Benefits	• Slide Slit and optional center slits for easy wire insertion. • Smooth surface for clean and legible printing. • Supplied on a ladder style carrier so that markers can be kitted after printing. • A 3:1 shrink ratio means fewer skews as each marker covers a wider range of wire diameters.
Product Description	HellermannTyton's ShrinkTrak heat shrinkable markers make it easy to mark wire, cable and other components. The military approved heat shrink tubing is flattened and assembled in a ladder style carrier system for easy printing using a thermal transfer printer. The ladder system creates a kit of markers that can be sorted, removed and applied in any order thus saving time, labor and speeding production.
Short Description	Heat Shrink Label, 1.0" 1-Slit Single Sided, Polyolefin, White, 500/BX

Product Dimensions

Length L (Imperial)	0.95 "
Length L (Metric)	24 mm
Printable (Yes/No)	Yes
Variant	Thin-Wall
Width W (Imperial)	0.95 "
Width W (Metric)	24 mm
Height H (Imperial)	1.69 "
Height H (Metric)	42.93 mm
Diameter Min. (Imperial)	0.33 "
Diameter Max. (Imperial)	1.0 "
Outside Diameter Max. (Imperial)	1.0 "
Outside Diameter Max. (Metric)	25.4 mm
Wall Thickness WT (Imperial)	0.024 "
Wall Thickness WT (Metric)	1.20 mm
Print Method	Thermal Transfer
Recovered Diameter d (metric)	8.0 mm
Recovered Diameter d (imperial)	0.33 "
Supplied Diameter D (metric)	24.0 mm
Supplied Diameter D (imperial)	1.57 "
Thickness T (Metric)	3.0 µm

Width of Liner WL (metric)	76.2 mm
Width of Liner WL (imperial)	3.0 "
Width of printable area (metric)	24.10 mm
Width of Printable Area (imperial)	0.95 "

Logistics and Packaging

Quantity Per	box
Package Quantity	500
Package Quantity (Metric)	500
Markers per row	2
Weight (Metric)	0.68 kg
Weight (imperial)	1.48 lbs

Material and Specifications

Material	Polyolefin, cross-linked (PO-X)
Material Shortcut	PO-X
US MILSPEC	SAE-AS81531 AMS-DTL-23053/5 Class 1 and 3 MIL-STD-202G Method 215K
Dielectric Strength (Metric)	19.7 kV min.
Flammability	UL224 VW-1
Shrink Temperature	+194 °F (+90 °C)
Operating Temperature	-67°F to +275°F (-55°C to +135°C)
ROHS Compliant	Yes
Certification/Specification	SAE - AMS - DTL-23053/5 Class 1 and 3 SAE-AS81531 UL224 125 °C 600V VW-1 MIL-STD-202G Method 215K