

596-00474

Article Number: 596-00474

Pre-Printed Solar Label, Reflective, " PHOTOVOLTAIC SYSTEM EQUIPPED WITH RAPID SHUTDOWN", 5.5" X 1.75", Red, 50/pkg



Base Data

Local Order Number	596-00474
Type	PSEWRS
Color	Red (RD)
Features and Benefits	<ul style="list-style-type: none">• Made with UV stable inks and materials for durability and weather resistance• Supplied with aggressive adhesive to ensure long life• Meets NEC & IFC standards for printed text, character height, color and outdoor UV stability to pass inspections• Pre-printed labels offer significant time and cost savings over high priced engraved and lead time purchased markers
Product Description	HellermannTyton pre-printed Solar Installation labels are designed to meet the requirements of the 2014 National Electrical Code (NEC 2014) and the 2012 International Fire Code (IFC 2012) as well as being acceptable to the Authority Having Jurisdiction (AHJ). Labels are made with durable UV stable materials and adhesives that are designed to stick to both baked enamel and powder coat surfaces. Where applicable, labels are made using reflective materials for first responder safety. Some pre-printed labels are printable using a thermal transfer printer when variable voltage or series data must be printed and displayed.
Technical Description	5.5" X 1.75" White text on red background that reads as: "PHOTOVOLTAIC SYSTEM WITH RAPID SHUTDOWN." in 3/8" tall characters. 50 per pkg.
Local Order Number 2	Spanish Version: 596-00823
Short Description	Pre-Printed Solar Label, Reflective, " PHOTOVOLTAIC SYSTEM EQUIPPED WITH RAPID SHUTDOWN", 5.5" X 1.75", Red, 50/pkg

Product Dimensions

Length L (Imperial)	5.5 "
Length L (Metric)	139.7 mm
Width W (Imperial)	5.5 "
Width W (Metric)	139.7 mm
Height H (Imperial)	1.75 "
Height H (Metric)	44.45 mm

Logistics and Packaging

Quantity Per	roll
Package Quantity	50
Package Quantity (Metric)	50
Labels per Column	1
Labels per Row	1

Material and Specifications

Material	Type 242/552, UV Stable Reflective Vinyl w/Acrylic Laminate
Material Shortcut	242/552
Adhesive Shortcut	Acrylic
Adhesive	Acrylic
Adhesive Operating Temperature	-40°F to +302°F (-40°C to +150°C)
Halogenfree	Yes
Operating Temperature	-40°F to +174°F (-40°C to +79°C)
ROHS Compliant	Yes
Certification/Specification	UL969
UL Recognized (US)	Yes