

XF40-Q1765 Explosion Protected Fixed Network Camera

Network 1080p fixed camera suitable for hazardous areas

XF40-Q1765 Explosion Protected Fixed Network Camera is suitable for onshore, offshore, marine and heavy industrial environments. It features a 316L stainless steel housing certified for hazardous areas according to for example ATEX and IECEx. The housing prevents any inside sparks or explosions from escaping and igniting vapors, gases, dust or fibers in the surrounding air. XF40-Q1765 provides superb image quality and color fidelity and a high level of flexible integration with other equipment, such as access control and fire alarms. It offers flexible remote accessibility, using any existing IP-based networks. XF40-Q1765 for hazardous areas is a complement to Axis' wide range of network cameras that can be used in safe areas.

- > IP66- and IP67-rated
- > Wide temperature ranges
- > Full HDTV 1080p resolution
- > 18x zoom and autofocus
- > Wide dynamic range



XF40-Q1765 Explosion Protected Fixed Network Camera

Models	XF40-Q1765 XF40-Q1765 -60C Both models are available in different versions depending on the regional requirements for hazardous equipment certification	Day/Night vision mode
Certification part number	1410-15-00	Data streaming Event data
Camera		Built-in installation aids Pixel counter
Image sensor	Progressive scan RGB CMOS 1/2.9"	General
Lens	4.7–84.6 mm, F1.6–2.8 Horizontal angle of view 59°–4° Vertical angle of view 35°–2° Autofocus	Casing IP66–, IP67– and IK10– rated Electro-polished 316L stainless steel casing for maximum corrosion protection IK08 glass protective window
Day and night	Automatically removable infrared-cut filter	Memory 256 MB RAM, 128 MB Flash
Minimum illumination	Color: 0.5 lux at 30 IRE F1.6 B/W: 0.04 lux at 30 IRE F1.6	Power 24 V AC XF40-Q1765: Max consumption: 28 W XF40-Q1765 -60C: Max consumption: 28 W
Shutter time	1/28000 s to 2 s	Edge storage Support for recording to dedicated network-attached storage (NAS) For NAS recommendations see www.axis.com
Pan/Tilt/Zoom	18x optical zoom and 12x digital zoom, total 216x zoom 64 preset positions	Operating conditions XF40-Q1765: -40 °C to +60 °C (-40 °F to 140 °F) XF40-Q1765 -60C: -60 °C to +40 °C (-76 °F to 104 °F) Humidity 10–100% RH (condensing)
Video		Approvals EN 55022 Class A, EN 61000-3-2, EN 61000-3-3, EN 55024, EN 61000-6-1, EN 61000-6-2, FCC Part 15 Subpart B Class A, ICES-003 Class A, C-tick AS/NZS CISPR 22 Class A, IEC/EN 60950-1, IEC/EN 60950-22, EN 50121-4, IEC/EN 60529 IP66, NEMA 250 Type 4x, IEC/EN 62262 IK10 body, IK8 glass ATEX: II 2 G Ex d op pr IIC T4 II 2 D Ex tb IIIC T135°C Db IP66/67 IECEx: Ex d IIC T4 -60°C ≤ Ta ≤ +60°C Gb Ex tb IIIC T130°C Db IP66/67 Immetro: Ex d IIC T4 -60°C ≤ Ta ≤ +60°C Gb Ex tb IIIC T130°C Db IP66/67 LCus: Class 1 Zone 1 AEx d IIC T4 LC1311396 Gb -60°C ≤ Ta ≤ +60°C DIV: Class I, Division 1, Groups B, C, D, -60°C ≤ Ta ≤ +60°C / Class II, Division 1, Groups E, F, G cLC: Ex d IIC T4 LC1311396 -60°C ≤ Ta ≤ +60°C EAC: Ex d IIC -60°C ≤ Ta ≤ +60°C Gb Ex tb IIIC T130°C Db IP6x - POCC GB.ГБ.В00659, IP66/67 CCOE: Ex d IIC -60°C ≤ Ta ≤ +60°C Gb Ex tb IIIC T130°C Db IP6x - P306928/1/2, IP66/67 CNEX: Ex d IIC T4 Gb Ex d IIIC 135°C Db, IP66/67
Video compression	H.264 (MPEG-4 Part 10/AVC) Baseline, and Main profiles Motion JPEG	Dimensions 165x176x480 mm (6½x7x19 in)
Resolutions	1920x1080 HDTV 1080p to 320x180	Weight 14 kg (31 lb)
Frame rate	Up to 30/25 fps (60/50 Hz) in all resolutions	Included accessories Sunshield, Installation Guide, Windows decoder 1-user license
Video streaming	Multiple, individually configurable streams in H.264 and Motion JPEG Controllable frame rate and bandwidth VBR/CBR H.264	Optional accessories Washer tank pressurized Power supply cabinet Explosion protected cables in various lengths Mounting accessories For more accessories, see www.axis.com
Image settings	Manual shutter time, Compression, Color, Brightness, Sharpness, White balance, Exposure control, Exposure zones, Backlight compensation, WDR-dynamic contrast, Fine tuning of behavior at low light, Rotation, Text and image overlay, Day/night shift level	Video management software AXIS Camera Companion, AXIS Camera Station, Video management software from Axis' Application Development Partners available on www.axis.com/techsup/software
Network		Languages German, French, Spanish, Italian, Russian, Simplified Chinese, Japanese, Korean, Portuguese
Security	Password protection, IP address filtering, HTTPS ^a encryption, IEEE 802.1X ^a network access control, Digest authentication, User access log, Centralized Certificate Management	Warranty Axis 3-year warranty and AXIS Extended Warranty option, see www.axis.com/warranty
Supported protocols	IPv4/v6, HTTP, HTTPS ^a , SSL/TLS ^a , QoS Layer 3 DiffServ, FTP, CIFS/SMB, SMTP, Bonjour, UPnP TM , SNMP v1/v2c/v3 (MIB-II), DNS, DynDNS, NTP, RTSP, RTP, SFTP, TCP, UDP, IGMP, RTCP, ICMP, DHCP, ARP, SOCKS, SSH	
System integration		
Application Programming Interface	Open API for software integration, including VAPIX [®] and AXIS Camera Application Platform; specifications at www.axis.com AXIS Video Hosting System (AVHS) with One-Click Connection ONVIF Profile S, specification at www.onvif.org	
Analytics	Video motion detection, Active tampering alarm Support for AXIS Camera Application Platform enabling installation of AXIS Video Motion Detection 3, AXIS Cross Line Detection, AXIS Digital Autotracking and third-party applications, see www.axis.com/acap	
Event triggers	Analytics, Edge storage events	
Event actions	File upload: FTP, SFTP, HTTP, HTTPS network share and email Notification: email, HTTP, HTTPS and TCP and SNMP trap Video recording to edge storage Pre- and post-alarm video buffering Status LED indicator PTZ preset, Overlay text	

a. This product includes software developed by the OpenSSL Project for use in the OpenSSL Toolkit. (www.openssl.org), and cryptographic software written by Eric Young (ey@cryptsoft.com).

More information is available at www.axis.com