



596-00667



Article Number: 596-00667

Solar Label, Warning - Bipolar PV Array Label, 3.75" X 2.0", Vinyl, Orange/White, 10/pkg

 RoHS

 Download spec sheet

Base Data

Local Order Number	596-00667
Type	BIPOLARPV10
Color	Red (RD)
Features and Benefits	<ul style="list-style-type: none">• Made with UV stable inks and materials for durability and weather resistance.• The labels are supplied with aggressive adhesive to ensure long life.• Solar Installation labels meet NEC & IFC standards for printed text, character height, color and outdoor UV stability to pass inspections.
Product Description	HellermannTyton pre-printed Solar Installation labels are designed to meet the requirements of the 2014 National Electrical Code (NEC 2014) and the 2012 International Fire Code (IFC 2012) as well as being acceptable to the Authority Having Jurisdiction (AHJ). Labels are made with durable UV stable materials and adhesives that are designed to stick to both baked enamel and powder coat surfaces. Where applicable, labels are made using reflective materials for first responder safety. Some pre-printed labels are printable using a thermal transfer printer when variable voltage or series data must be printed and displayed.
Technical Description	3.75" X2" Black text on an Orange/White background that reads as: "WARNING - BIPOLAR PHOTOVOLTAIC ARRAY. DISCONNECTION OF NEUTRAL OR GROUNDED CONDUCTORS MAY RESULT IN OVERVOLTAGE ON ARRAY OR INVERTER." - 10 per pkg.
Short Description	Solar Label, Warning - Bipolar PV Array Label, 3.75" X2.0", Vinyl, Orange/White, 10/pkg

Product Dimensions

Width W (Imperial)	3.75 "
Width W (Metric)	92.25 mm
Height H (Imperial)	2.0 "
Height H (Metric)	50.8 mm

Logistics and Packaging

Quantity Per	pack
Package Quantity	10
Package Quantity (Metric)	10

Material and Specifications

Material	Vinyl
Material Shortcut	VL
Adhesive	Acrylic
Adhesive Shortcut	Acrylic
Adhesive Operating Temperature	-40°F to +174°F (-40°C to +79°C)
Halogenfree	Yes

Operating Temperature -40°F to +174°F (-40°C to +79°C)

ROHS Compliant Yes

UL Recognized (US) Yes