

TYHC9

Article Number: 598-00030

Handi-Card, .25" X 1.5", Solid #9, 36 Per Card, White, 25/pkg



Download drawing

Download spec sheet

Base Data

Local Order Number	TYHC9
Type	TYHC9
Color	White (WH)
Features and Benefits	<ul style="list-style-type: none">• Handi Cards have a split backing so that a portion of the liner can be removed to expose the markers for easy dispensing.• Handi-Cards are kitted on the card so that specific markers can be removed without affecting the other markers on the card.• Markers are pre-printed so no additional post printing is required, saving time and money.• Label material is a conformable cloth that ensures markers stay on wires and cables for the life of the application.
Product Description	HellermannTyton Handi-Cards are easy release pre-printed cloth markers, on a plastic card, with a strong adhesive for a long lasting bond on wire and cable. The markers are available in Solid format where each marker on the card contains the same legend and Sequence format where each marker on the card contains a different number or letter which is usually printed in sequence from lowest to highest in sort order.
Short Description	Handi-Card, .25" X 1.5", Solid #9, 36 Per Card, White, 25/pkg

Product Dimensions

Length L (Imperial)	1.5 "
Length L (Metric)	38.1 mm
Width W (Imperial)	0.25 "
Width W (Metric)	6.35 mm
Height H (Imperial)	1.5 "
Height H (Metric)	38.1 mm
Bundle Diameter Min. (Imperial)	0.13 "
Bundle Diameter Min. (Metric)	3.40 mm
Bundle Diameter Max. (Imperial)	0.29 "
Bundle Diameter Max. (Metric)	7.50 mm
Outside Diameter Min. (Imperial)	0.13 "
Outside Diameter Min. (Metric)	3.40 mm
Outside Diameter Max. (Imperial)	0.29 "
Outside Diameter Max. (Metric)	7.50 mm

Logistics and Packaging

Quantity Per	pack
Package Quantity	25
Package Quantity (Metric)	25

Labels per Column 1

Labels per Row 36

Labels per Sheet 36

Material and Specifications

Material Vinyl Cloth (TYHC)

Material Shortcut TYHC

Adhesive Rubber

Adhesive Shortcut Synthetic rubber

Adhesive Operating Temperature -40°F to +248°F (-40°C to +120°C)

Operating Temperature -40°F to +248°F (-40°C to +120°C)

ROHS Compliant Yes