



#9061

#9061

G.P. Duct tape

Tape Structure

Backing PE LAMINATED
SYNTHETIC CLOTH

Adhesive SYNTHETIC RUBBER /
RESINS CLEAR ADHESIVE

Characteristic

This Duct tape is designed to fix insulating covers such as panels or pipes, but also used for packaging and emergencies. Its resistance to breaking loads allows it to resist under conditions of high tension.

CHARACTERISTICS	UNITS	STD. VALUES	TOLER.	TEST METHOD
Total Weight	g/m ²	155	± 10%	ISO 536
Total Thickness	µm	165	± 10%	AFERA 5006
MD tensile strength	N/cm	> 32		AFERA 5004
MD elongation at break	%	> 10		AFERA 5004
Adhesion to steel plate	N/cm	> 6		AFERA 5001
Rolling ball tack	cm	< 0,5		PSTC 6

Available colours: SILVER - BLACK - WHITE - RED - ORANGE - YELLOW -
DARK BROWN- GREEN - BLUE- DARK OLIVE GREEN

Figures shown refer to average values only, based on tests carried out in conditioned laboratory and are not valid for specification. The company reserves the right to modify or change the products at any time without notice. All information has to be intended as generic advice for the use of products. Users have to verify the suitability of each tape in actual application under specific conditions.

DATE OF ISSUE: 07/01/15

REV_02_140515



IN TAPE WE TRUST



#9061

G.P Duct tape

Technical Features



Technical Skills



Terms & Conditions of liability

PPM tapes must be stored in a dry location, protected from direct sunlight exposure and from freezing. Storage temperatures should be as close as possible to room temperature; suggested storage temperature should range from 15 to 25°C with max. relative humidity of 60%.

Make sure the surface you wish to place the tape on is cleaned, dried and free from oil and dust.

It is suggested not to apply the tape with temperatures lower than 10°C.

With a storage temperature lower than 10°C, it is always suggested temperature reconditioning of the tape at room temperature (15°C - 25 °C) before its use.

Shelf life from date of manufacture:

(no yellowing and < 10% loss in performance at 23 °C, 50 % humidity) is considered 12 months for Slit rolls and 6 for Jumbo rolls.

PPM does not take responsibility for the defective material is not stored and used in accordance with the conditions listed above.