

AXIS Q6115-E PTZ Dome Network Camera

High-end HDTV 1080p PTZ camera with Sharpdome technology

The compact, outdoor-ready AXIS Q6115-E delivers smooth HDTV 1080p video at 50/60 fps, with 30x optical zoom and autofocus. Axis Sharpdome technology provides full scene fidelity and sharp images in all directions—above as well as below the horizon. Quick and precise pan performance of over 700°/s makes it easy to change viewing position and follow fast moving objects. AXIS Q6115-E supports Wide Dynamic Range – Dynamic Capture for challenging lighting conditions. Axis Speed Dry function easily removes water drips from the dome glass, providing sharp images in rainy weather.

- > [Sharpdome technology](#)
- > [Speed Dry function](#)
- > [HDTV 1080p at 50/60 fps](#)
- > [Pan performance 700° per second](#)



AXIS Q6115-E PTZ Dome Network Camera

Models	AXIS Q6115-E 50 Hz AXIS Q6115-E 60 Hz	File upload via FTP, SFTP, HTTP, HTTPS, and email Notification via email, HTTP, HTTPS, and TCP PTZ preset, guard tour, video recording to edge storage, autotracking, day/night mode Pre- and post-alarm video buffering, Send SNMP Trap
Camera		
Image sensor	1/3" Progressive Scan CMOS	
Lens	4.4–132 mm, F1.4–4.6, Horizontal angle of view: 63.4°–2.3° Vertical angle of view: 37.3°–1.3° Autofocus, auto-iris	
Day and night	Automatically removable infrared-cut filter	
Minimum illumination	Color: 0.2 lux at 30 IRE F1.4 B/W: 0.02 lux at 30 IRE F1.4	
Shutter time	1/30000 s to 1 s	
Pan/Tilt/Zoom	Pan: 360° endless, 0.05°–700°/s Tilt: +20 to -90°, 0.05°–500°/s Zoom: 30x Optical, 12x Digital, Total 360x zoom Nadir flip, 256 preset positions, Tour recording, Guard tour, Control queue, On-screen directional indicator, Set new pan 0°, Adjustable zoom speed, Speed Dry	
Video		
Video compression	H.264 (MPEG-4 Part 10/AVC) Baseline, Main and High Profiles Motion JPEG	
Resolutions	1920x1080p (HDTV 1080p) to 320x180	
Frame rate	Up to 25/30 or 50/60 fps (50/60 Hz) in all resolutions and H.264	
Video streaming	Multiple, individually configurable streams in H.264 and Motion JPEG Controllable frame rate and bandwidth VBR/MBR H.264	
Image settings	Compression, Color, Brightness, Sharpness, White balance, Exposure control, Exposure zones, Rotation, Backlight compensation, Fine tuning of behavior at low light, Electronic Image Stabilization (EIS), Defogging, Manual shutter time, Text and image overlay, Image freeze on PTZ WDR – Dynamic Capture: 115 dB 32 individual 3D privacy masks	
Network		
Security	Password protection, IP address filtering, HTTPS ^a encryption, IEEE 802.1X ^a network access control, Digest authentication, User access log, Centralized Certificate Management	
Supported protocols	IPv4/v6, HTTP, HTTPS ^a , SSL/TLS ^a , QoS Layer 3 DiffServ, FTP, CIFS/SMB, SMTP, Bonjour, UPnP TM , SNMP v1/v2c/v3 (MIB-II), DNS, DynDNS, NTP, RTSP, RTP, SFTP, TCP, UDP, IGMP, RTCP, ICMP, DHCP, ARP, SOCKS, SSH, NTCP	
System integration		
Application Programming Interface	Open API for software integration, including VAPIX [®] and AXIS Camera Application Platform; specifications at www.axis.com AXIS Video Hosting System (AVHS) with One-Click Connection ONVIF Profile S, specification at www.onvif.org	
Analytics	Video motion detection, Active Gatekeeper, Shock detection, Autotracking Support for AXIS Camera Application Platform enabling installation of third-party applications, see www.axis.com/acap	
Event triggers	Detectors: Live Stream Accessed, Motion Detection, Shock Detection Hardware: Network, Temperature Input Signal: Manual Trigger, Virtual Inputs PTZ: Autotracking, Error, Moving, Preset Reached, Ready Storage: Disruption, Recording System: System Ready Time: Recurrence, Use Schedule	
Event actions	Overlay text Record video	
Data streaming	Event data	
Built-in installation aids	Pixel counter	
General		
Casing	IK08, IP66- and NEMA 4X-rated metal casing (aluminum), Polycarbonate (PC) clear dome with Sharpdome technology	
Memory	1 GB RAM, 256 MB Flash	
Power	Axis High PoE midspan 1-port: 100–240 V AC, max 74 W Camera consumption: typical 10 W, max 51 W Axis PoE+ midspan 1-port: 100–240 V AC, max 37 W IEEE 802.3at Type 2 Class 4 Camera consumption: typical 10 W, max 25 W	
Connectors	RJ45 10BASE-T/100BASE-TX PoE RJ45 Push-pull Connector (IP66)	
Edge storage	Support for SD/SDHC/SDXC card Support for recording to dedicated network-attached storage (NAS) For SD card and NAS recommendations see www.axis.com	
Operating conditions	With 30 W midspan: -20 °C to 50 °C (4 °F to 122 °F) With 60 W midspan: -50 °C to 50 °C (-58 °F to 122 °F) Maximum temperature (intermittent): 60 °C (140 °F) Arctic Temperature Control: Start-up as low as -40 °C (-40 °F) Humidity 10–100% RH (condensing)	
Storage conditions	-40 °C to 70 °C (-40 °F to 158 °F)	
Approvals	EN 55022 Class A, EN 61000-3-2, EN 61000-3-3, EN 61000-6-1, EN 61000-6-2, EN 55024, EN 50121-4, IEC 62236-4, FCC Part 15 Subpart B Class A, ICES-003 Class A, VCCI Class A, C-tick AS/NZS CISPR22 Class A, KCC KN22 Class A, KN24, IEC/EN/UL 60950-1, IEC/EN/UL 60950-22, IEC/EN 62262 IK08, IEC/EN 60529 IP66, NEMA 250 Type 4X, IEC 60068-2-1, IEC 60068-2-2, IEC 60068-2-78, IEC 60068-2-14, IEC 60068-2-6, IEC 60068-2-27, ISO4892-2 Midspan: EN 60950-1, GS, UL, cUL, CE, FCC, VCCI, CB, KCC, UL-AR	
Dimensions	222x165x165 mm (8 3/4 x 6 1/2 x 6 1/2 in) With mounting hook: 275x165x165 mm (10 13/16 x 6 1/2 x 6 1/2 in)	
Weight	2.7 kg (5.9 lb)	
Included accessories	IP66-rated RJ45 connector kit, High PoE Midspan 1-port, Installation Guide, Windows decoder 1-user license	
Optional accessories	AXIS T91/T94 mounting accessories, Axis High PoE midspans For more accessories, see www.axis.com	
Video management software	AXIS Camera Companion, AXIS Camera Station, Video management software from Axis' Application Development Partners available on www.axis.com/techsup/software	
Languages	English, German, French, Spanish, Italian, Russian, Simplified Chinese, Japanese, Korean, Portuguese, Traditional Chinese	
Warranty	Axis 3-year warranty and AXIS Extended Warranty option, see www.axis.com/warranty	

a. This product includes software developed by the OpenSSL Project for use in the OpenSSL Toolkit. (www.openssl.org), and cryptographic software written by Eric Young (ey@cryptsoft.com).

Environmental responsibility:

www.axis.com/environmental-responsibility