




CommandCenter® Secure Gateway

Centralized Remote Access and Control of IT Infrastructures

Raritan's CommandCenter Secure Gateway (CC-SG) provides IT and lab organizations with secure and consolidated access and power control of all technology platforms at the application, operating system or BIOS level. CC-SG's single pane of glass helps simplify remote management and expedite troubleshooting of your physical and virtual servers, intelligent PDUs, and serial devices. Plus, it helps you maximize uptime and productivity of these devices, while reducing network overhead and the Total Cost of Ownership (TCO). Available as both hardware and software appliance.

Features and Benefits

- Single point of access to physical servers (including blade systems and PCs), virtual machines and VMware® infrastructures
- Flexible client options for convenient server access and management of servers and PDUs from an iPhone or iPad
- Centralized authentication, authorization and logging
- Intuitive menus and easy reporting - everything from usage and auditing to assets and nodes
- Centralized, role-based, user access policy management
- Robust security features
- High availability and redundancy
- Integrates with Raritan's Power IQ® for remote power control



Smart, secure remote access and control of centralized and distributed IT assets

From small and medium server rooms to large enterprises with multiple data centers around the globe, CC-SG is relied upon worldwide for secure and consolidated remote access and control in a variety of settings. Its key features are designed to meet the needs of today's IT and lab administrators.

Features	V1	E1
Form Factor	1U	2U
Dimensions (DxWxH)	440mm x 615mm x 44mm; 7.3" x 24.2" x 1.75"	440mm x 699mm x 89mm; 17.3" x 27.5" x 3.5"
Weight	10.8 kg; 23.8 lbs	20 kg; 44.1 lbs
Power	Single Supply (1 x 300 watt)	Dual Supply (2 x 500 watt)
Operating Temperature	10°C - 35°C; 50° - 95° F	10°C - 40°C; 50°F - 104°F
Mean Time Between Failure (MTBF)	38,269 hours	53,564 hours
KVM Admin Port	DB15 + PS/2 or USB Keyboard/Mouse	DB15 + PS/2 or USB Keyboard/Mouse
Serial Admin Port	DB9	DB9
Console Port	2 x USB 2.0 Ports	2 x USB 2.0 Ports
Hardware		
Processor	Intel® Core™ 2 Duo E8400	Intel Xeon® X3360
Memory	4 GB	8 GB
Network Interfaces	(2) 10/100/1000 Eth. (RJ45)	(2) 10/100/1000 Eth. (RJ45)
Hard Disk & Controller	(2) 80 GB SATA @ 7,200 rpm, RAID 1	(2) 300 GB SATA @ 10,000 rpm, RAID 1
CD-ROM Drive	DVD-ROM	DVD-ROM
Remote Connection		
Protocols	TCP/IP, UDP, IPv4/IPv6, RADIUS, LDAP, TACACS+, SNMPv3, SNMP, HTTP, HTTPS	
Warranty	Two years. In addition, Raritan offers two years extended warranty.	



Endorser of the EU Code of Conduct on Data Centre Energy Efficiency

Formulated by the EU's Joint Research Centre, the Code is a measured response to the energy challenges the EU faces. It's aim is to encourage companies with data centers to reduce energy consumption while ensuring business objectives continue to be met.

As an endorser, Raritan have pledged to implement the Code's ethos through devising products and services that help organizations to bring their data centers into line with its best practice recommendations.

Call +31 (0)10 284 4040 or visit www.raritan.eu

Raritan is a proven innovator of power management solutions, DCIM software, and KVM-over-IP for data centers of all sizes. Based in Somerset, NJ, Raritan has a global presence across 38 offices, serving 76 countries and 50,000 locations worldwide. Raritan's award-winning hardware and software solutions increase energy efficiency, improve reliability, and raise productivity. For more information, please visit www.raritan.eu or call +31 (0)10 284 4040.

© 2014 Raritan Inc. All rights reserved. Raritan®, Know more. Manage smarter.™ are registered trademarks or trademarks of Raritan Inc. or its wholly-owned subsidiaries. All others are registered trademarks or trademarks of their respective owners.