

2412F Multi-Conductor - Enhanced Category 6 Nonbonded-Pair ScTP Cable



For more Information
please call

1-800-Belden1

**General Description:**

CAT6+ (350MHz), 4-Pair, F/UTP-Foil Shielded, Riser-CMR, Premise Horizontal Cable, 23 AWG Solid Bare Copper Conductors, Polyolefin Insulation, Patented X-Spline, Overall Beldfoil Shield, PVC Jacket

Usage (Overall)**Suitable Applications:**

Networking Horizontal Cable, HDBaseT, 1000Base-T (Gigabit Ethernet), 100Base-T (Fast Ethernet), 10Base-T (Ethernet), 100BaseVG, ANYLAN, 155ATM, 622ATM, ANSI.X3.263 FDDI TP-PMD, NTSC/PAL Component or Composite Video, AES/EBU, Digital Video, RS-422, Noisy Environments, 250 MHz Category 6

Physical Characteristics (Overall)**Conductor****AWG:**

# Pairs	AWG	Stranding	Conductor Material
4	23	Solid	BC - Bare Copper

Insulation**Insulation Material:**

Insulation Material
PO - Polyolefin

Outer Shield**Outer Shield Material:**

Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
Beldfoil®	Tape	Aluminum Foil-Polyester Tape	100.000

Outer Shield Drain Wire AWG:

AWG	Stranding	Drain Wire Conductor Material
24	Solid	TC - Tinned Copper

Outer Jacket**Outer Jacket Material:**

Outer Jacket Material
PVC - Polyvinyl Chloride

Outer Jacket Diameter:

Nom. Dia. (in.)
0.290

Outer Jacket Ripcord: Yes

Overall Cable

Overall Cabling Fillers: Patented Central X-spline

Overall Cabling Separator Material: Polyester

Overall Nominal Diameter: 0.290 in.

Pair**Pair Color Code Chart:**

Number	Color
1	White/Blue Stripe and Blue
2	White/Orange Stripe and Orange
3	White/Green Stripe and Green
4	White/Brown Stripe and Brown

Mechanical Characteristics (Overall)

Storage Temperature Range: -20°C To +75°C

Installation Temperature Range: 0°C To +60°C

Operating Temperature Range: -20°C To +75°C

Bulk Cable Weight: 44 lbs/1000 ft.

Max. Recommended Pulling Tension: 25 lbs.

2412F Multi-Conductor - Enhanced Category 6 Nonbonded-Pair ScTP Cable

Min. Bend Radius/Minor Axis:	3 in.
------------------------------	-------

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC(UL) Specification:	CMR, UL444
CEC/C(UL) Specification:	CMR
EU Directive 2011/65/EU (ROHS II):	Yes
Other Standards:	ISO/IEC 11801 ed 2.1 (2008) Class E
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	12/08/2011
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes
Telecommunications Standards:	Category 6 - TIA 568.C.2

Applicable Patents:

Country

www.belden.com/p

Flame Test

UL Flame Test:	UL1666 Vertical Riser
C(UL) Flame Test:	FT4
CSA Flame Test:	FT4

Plenum/Non-Plenum

Plenum (Y/N):	No
Plenum Number:	2413F

Electrical Characteristics (Overall)

Nom. Mutual Capacitance:

Capacitance (pF/ft)

14.000

Maximum Capacitance Unbalance:

Capacitance (pF/ft)

66.000

Nominal Velocity of Propagation:

VP (%)

68.000

Maximum Delay:

Description Delay (ns/100 m)

@ 100 MHz 537.000

Max. Delay Skew:

Delay Skew (ns/100 m)

30.000

Maximum Conductor DC Resistance:

DCR @ 20°C (Ohm/100 m)

8.200

Max. Operating Voltage - UL:

Voltage

300 V RMS

Maximum DCR Unbalanced:

DCR Unbalance @ 20°C (%)

3.000

Electrical Characteristics-Premise (Overall)

Premise Cable Electrical Table 1:

Freq. (MHz)	Max. Attenuation (dB/100 m)	Min. NEXT (dB)	Min. PSNEXT (dB)	Min. ACR (dB)	Min. PSACR (dB)	Min RL (dB)
-------------	-----------------------------	----------------	------------------	---------------	-----------------	-------------

2412F Multi-Conductor - Enhanced Category 6 Nonbonded-Pair ScTP Cable

1	2.000	75.3	73.3	73.3	72.3	20.000
4	3.700	66.3	64.3	62.6	61.6	23.000
8	5.200	63.3	61.3	58.1	57.1	24.500
10	5.800	61.8	59.8	56.0	55.0	25.000
16	7.400	58.6	56.6	51.2	50.2	25.000
20	8.300	57.1	55.1	48.8	47.8	25.000
25	9.300	55.5	53.5	46.3	45.2	24.300
31.25	10.400	54.0	52.0	43.6	42.6	23.600
62.5	15.000	49.1	47.1	34.1	33.1	21.500
100	19.300	45.8	43.8	26.5	25.5	20.800
200	28.300	40.9	38.9	12.6	11.6	18.700
250	32.100	39.3	37.3	7.2	6.2	18.000
300	35.600	38.1	36.1	2.5	1.5	17.500
350	38.900	37.1	35.1			17.000
400	42.000	36.3	34.3			16.600
450	45.000	35.5	33.5			16.200
500	47.900	34.8	32.8			15.900
550	50.600	34.2	32.2			15.600

Premise Cable Electrical Table 2:

Freq. (MHz)	Input (Unfitted) Imp. (Ohms)	Fitted Impedance	Min. ELFEXT (dB)	Min. PSELFEXT (dB)
1	100 ± 15	100 ± 15	70.8	67.8
4	100 ± 15	100 ± 15	58.8	55.8
8	100 ± 15	100 ± 15	52.7	49.7
10	100 ± 15	100 ± 15	50.8	47.8
16	100 ± 15	100 ± 15	46.7	43.7
20	100 ± 15	100 ± 15	44.8	41.8
25	100 ± 15	100 ± 15	42.8	39.8
31.25	100 ± 15	100 ± 15	40.9	37.9
62.5	100 ± 15	100 ± 15	34.9	31.9
100	100 ± 15	100 ± 15	30.8	27.8
200	100 ± 22	100 ± 15	24.8	21.8
250	100 ± 32	100 ± 15	22.8	19.8
300	100 ± 32	100 ± 15	21.3	18.3
350	100 ± 32	100 ± 15	19.9	16.9
400	100 ± 32	100 ± 15	18.8	15.8
450	100 ± 32	100 ± 15	17.7	14.7
500	100 ± 32	100 ± 15	16.8	13.8
550	100 ± 32	100 ± 15	16.0	13.0

Premise Cable Electrical Table 4:

Frequency (MHz)	Min. TCL (dB)	Min. ELTCTL (dB)
1.000	40.000	35.000
4.000	40.000	23.000
8.000	40.000	17.000
10.000	40.000	15.000
16.000	38.000	10.900
20.000	37.000	9.000
25.000	36.000	7.100
31.250	35.100	5.100
62.500	32.000	
100.000	30.000	
200.000	27.000	
250.000	26.000	

Notes (Overall)

Notes: Jacket sequentially marked at 2 ft. intervals. Third party Verified to ANSI/TIA-568-C.2, Category 6. Values above 350 MHz are for Engineering Information Only.

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
2412F 0021000	1,000 FT	41.000 LB	RED		CAT6+ 4PR F/UTP CMR REEL
2412F 0031000	1,000 FT	41.000 LB	ORANGE		CAT6+ 4PR F/UTP CMR REEL
2412F 0041000	1,000 FT	41.000 LB	YELLOW		CAT6+ 4PR F/UTP CMR REEL
2412F 0051000	1,000 FT	41.000 LB	GREEN, DARK		CAT6+ 4PR F/UTP CMR REEL
2412F 006A500	500 FT	26.500 LB	BLUE, LIGHT	C	CAT6+ 4PR F/UTP CMR RIB
2412F 0061000	1,000 FT	41.000 LB	BLUE, LIGHT		CAT6+ 4PR F/UTP CMR REEL
2412F 0081000	1,000 FT	41.000 LB	GRAY		CAT6+ 4PR F/UTP CMR REEL

2412F Multi-Conductor - Enhanced Category 6 Nonbonded-Pair ScTP Cable

2412F 009A500	500 FT	26.500 LB	WHITE	C	CAT6+ 4PR F/UTP CMR RIB
2412F 0091000	1,000 FT	41.000 LB	WHITE		CAT6+ 4PR F/UTP CMR REEL
2412F 0101000	1,000 FT	41.000 LB	BLACK		CAT6+ 4PR F/UTP CMR REEL

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 3 Revision Date: 02-28-2014

© 2015 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.