

ORiNOCO® AP-9100R

Outdoor 802.11ac Access Point



Proxim introduces the ORiNOCO® AP- 9100R, a dual radio 802.11ac Access Point designed for outdoor use

ORiNOCO® AP-9100R takes advantage of Proxim's expertise in both Wi-Fi and outdoor systems to deliver a dual radio 802.11ac Access Point ready for outdoor use. ORiNOCO® AP-9100R features MIMO 2x2:2 performance with an aggregate data rate of 1166 Mbps and unparalleled flexibility. In addition, it benefits from the robust and IP67 weatherproofed design of Proxim Tsunami® products with unique features such as dual gigabit Ethernet ports with controllable PoE in and out. Organizations of all sizes encompassing Carriers, Small and Medium Enterprises, Health Care, Governments and Public safety departments, can achieve higher performance than their existing wired and wireless LANs thanks to 802.11ac advantage: significantly higher throughput and longer range.

World Class Performance

ORiNOCO® AP-9100R products enable enterprises of all size to extend their LAN outdoor while providing equivalent performance to their existing Ethernet networks.

- High throughput with dual radio rates of 866 + 300 Mbps
- High power radio delivering up to 30 dBm (2 RF) at 5 GHz
- Twice the throughput of existing typical WLANs
- High reliability for quad play applications
- Dual IPv4 and IPv6 stacks for transparent evolution to tomorrow networks

Highly Secure

ORiNOCO® AP-9100R provides enterprise class security to ensure full protection of sensitive information.

- 802.11i based security with AES 128 encryption and 802.1x Radius based authentication
- Rogue scan listing surrounding devices
- Secure management (SSL, SSH and SNMPv3) preventing unwanted configuration changes
- IP67 rated metal enclosure and surged protect ethernet and antenna ports

Advanced Features

ORiNOCO® AP-9100R is packed with features.

- Dual Gigabit Ethernet ports with PoE out to power other devices such as surveillance cameras or additional radios
- Multi-SSID with VLAN allocation, plus Ethernet port access and trunk mode
- Rogue AP scan reporting unwanted device in the network
- Public HotSpot integration with Home Page redirect and Walled Garden. Firmware upgradable to HotSpot 2.0 v2 (to be released early 2016)

Unparalleled Flexibility and Convenience with Centralized Management

ProximVision™ Advanced supports ORiNOCO® devices giving network architects unparalleled flexibility and control of the units.

- Rapid Network Deployment: automates configuration processes for faster, more efficient deployment of Proxim Wireless networks
- Advanced Configuration Capabilities: gives network managers an option for exhaustive device configuration with a software-based tool
- Greater Ease of Use and Upgradability: supports a greater number of devices than competitively priced solutions and provides the simplest path to configuration and upgrade

Standalone and Controller-Ready

ORiNOCO® AP-9100R offers the advantages of both architectures:

- Standalone operation
- Controller based leveraging ProximVision™ Advanced

PRODUCT MODELS													
AP-9100R	ORINOCO® AP-9100R, MIMO 2x2, 802.11 ac + b/g/n dual radio outdoor Access Point												
INTERFACES													
WIRED ETHERNET	Two auto MDI-X RJ45 10/100/1000Mbps Ethernet - Port #1 with PoE in & Data - Port #2 with PoE out & Data												
WIRELESS PROTOCOL	- Radio #1: 802.11a/n/ac - Radio #2: 802.11b/g/n												
RADIO				Radio #1				Radio #2					
FREQUENCY	5.150 – 5.925 GHz (Subject to Country Regulations)						2.400 – 2.484 (Subject to Country Regulations)						
	802.11ac		802.11n		802.11a		802.11n		802.11g		802.11b		
MIMO	2x2:2		2x2:2		2x2:2		2x2:2		N/A		N/A		
MODULATION	OFDM BPSK-QAM256		OFDM BPSK-QAM64		OFDM BPSK-QAM64		OFDM BPSK - QAM64		OFDM BPSK-QAM64		DSSS DBPSK-CCK		
DATA RATE	Upto 866 Mbps			Upto 300 Mbps			Upto 54 Mbps			Upto 300Mbps		Upto 54Mbps	Up to 11Mbps
	80 MHz	40 MHz	20 MHz	40 MHz	20 MHz	20 MHz	40 MHz	20 MHz	20 MHz	20 MHz	20 MHz		
TX POWER	MCS0: 29	MCS0: 29	MCS0: 30	MCS0: 30	MCS0: 30	6 Mbps: 30		MCS0: 26	MCS0: 26	6 Mbps: 26		1 Mbps: 26	
	MCS9: 24	MCS9: 24	MCS9: 24	MCS7: 25	MCS7: 26	54 Mbps: 27		MCS7: 21	MCS7: 21	54 Mbps: 22		11 Mbps: 26	
RX SENSITIVITY (BER=10 ⁻⁶)	MCS0: -89	MCS0: -93	MCS0: -94	MCS0: -92	MSS0: -95	6 Mbps: -96		MCS0: -92	MCS0: -96	6 Mbps: -96		1 Mbps: -95	
	MCS9: -68	MCS9: -71	MCS8: -71	MCS7: -77	MCS7: -77	54 Mbps: -84		MCS7: -77	MCS7: -79	54 Mbps: -81		11 Mbps: -90	
OTHER	Dynamic Channel Selection (DCS) based on interference detection Dynamic Frequency Selection (DFS) based on radar signature Rogue Scan						Dynamic Channel Selection (DCS) based on interference detection Rogue Scan						
THROUGHPUT				Radio #1				Radio #2					
	Up to 450 Mbps						Up to 150 Mbps						
ANTENNA				Radio #1				Radio #2					
	Two N-type Connectors with built-in Surge Protection Two 7 dBi, omni-directional antenna provided						Two N-type Connectors with built-in Surge Protection Two 5 dBi, omni-directional antenna provided						
MANAGEMENT													
REMOTE	Telnet and SSH, Web GUI and SSL, TFTP, SNMPv3												
SNMP	SNMP v1-v2c-v3, RFC-1213, RFC-1215, RFC-2790, RFC-2571, RFC-3412, RFC-3414, Private MIB												
OTHER	Syslog, SNMP and local time												
NETWORK													
IP STACK	IPv4 and IPv6 simultaneously												
VLAN	802.1Q: Management VLAN. Transparent, Access and Trunk mode. Radius based VLAN assignment												
WIRELESS													
AP-AP COMMUNICATION	WDS with STP loop avoidance												
RF ENVIRONMENT	Rogue Scan												
OTHER	802.11h Spectrum and Transmit Power Management Extensions												
SECURITY													
AUTHENTICATION	Enterprise/802.1x, Personal/ PSK (Pre Shared Key) or Open plus Internal MAC Address Control List												
802.1X SUPPORT	PEAP, LEAP, EAP-FAST, EAP-SIM, EAP-TTLS, EAP-AKA												
ENCRYPTION	802.11i Wireless Security with AES-128, TKIP or WEP												
QoS													
PACKET CLASSIFICATION	802.11e Enhanced Distributed Channel Access, 4 priority queues 802.1p priority, IPTOS												
HOTSPOT													
	Home Page Redirect with configurable URL and Domain based Walled Garden with wild card support												
POWER				INPUT				OUTPUT					
	36 to 57 VDC via Ethernet port1 (Power over Ethernet) 12 VDC via Access port Power should not be provided simultaneously on both ports.						48 to 57 VDC on Ethernet port2 (Power over Ethernet – software controlled) 12 VDC on Access port						
POWER CONSUMPTION													
	32 Watt typical												
ENVIRONMENTAL SPECS													
OPERATING TEMPERATURE	-40° to 60°C (-40° to 140° Fahrenheit)												
STORAGE TEMPERATURE	-50° to 70°C (-58° to 158° Fahrenheit)												
HUMIDITY - IP RATING	100% relative humidity - IP67												
WIND LOADING	180 km/h (112.5 mph)												
PHYSICAL SPECS				DIMENSIONS				WEIGHT					
PACKAGED (per unit)	14.56 x 13.0 x 7.87 in (370 x 331 x 200 mm)						12.12 lbs (5.5 kg)						
UNPACKAGED (per unit)	10.3 x 8.66 x 2.83 in (262 x 220 x 72 mm)						4.85 lbs (2.2 kg) / 5.29 lbs (2.4 kg)						
SAFETY STANDARDS													
	UL 60950, CAN/CSA-C22.2 No. 60950, IEC 60950, EN 60950 (part -1 and -22)												
PACKAGE CONTENTS													
	<ul style="list-style-type: none"> One ORINOCO® AP-9100R with four N-type surge protected connectors Two 2.4 GHz, 5 dBi omni antennas Two 5 GHz, 7 dBi omni antennas One Connector weatherproofing kit (Includes all recommended weatherproofing material)						<ul style="list-style-type: none"> One power injector and country specific power cord One Wall / Pole mounting kit One Grounding kit One Antenna alignment (RJ11) dongle One Quick Installation Guide 						
MTBF and WARRANTY													
	>250 000 hours, 3-year warranty, ServPak Extended Support available.												